




## Platinum Resistance PT100 'Flat Tip' Probe



- General purpose Pt100 probe
- Flattened at tip for improved thermal response
- 2 wire configuration
- Class B, to IEC 751
- 316 stainless steel sheath, 4.0mm diameter x 150mm long
- 1-metre-long 7/0.2mm Teflon® insulated 2 core twisted lead
- Includes 1/8" BSPP brass male compression fitting with locking nut
- Temperature range -50°C to + 250°C

### Specifications

Sensor type:	Pt100 (100 Ohms @ 0°C) to IEC 751, Class B
Construction:	316 stainless steel probe, 4.0mm diameter (6mm max. across flat area of tip) x 150mm long overall
Probe temperature range:	-50°C to +250°C
Extension cable:	1 metre 7/0.2mm Teflon® insulated 2 core twisted leads
Termination:	2-wire tails
Accessories:	1/8" BSPP brass male compression fitting with locknut included

Probe Diameter	Probe Length	Cable Length	Cable Conductors	Order code
4.0mm	150mm	1 metre	7/0.2mm	XF-1098-FAR

### About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

### Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

### Contact Details

Email  
sales@labfacility.com

Website  
www.labfacility.com