

Test pump HP 32-8, 2 to 1000 bar

With 60-L rectangular container



Application:

For hydrostatic testing of parts such as fittings, pipes, pipelines, tanks, gas bottles, test stands and many other high-pressure components.

Execution:

- Test media: clear water, water/oil emulsion, hydraulic oil or low viscosity oil
- With drain valve, pressure gauge and hot-dip galvanised container

Advantage:

- 2-stage pumps with large piston for rapid filling of the system being tested and small piston for building the test pressure



Art. no.	56377 210
Brand	URACA
Manufacturer Part Number	W2854-K1 +ZUBEHÖR
Model	HP 32-8
Bin capacity	60 l
Min./max. pressure	2-1000 bar
Design	Mobile
Connection thread	G 3/8 inch
Form	Rectangular
Feed volume per stroke	32 cm ³
Length x width x height	480 x 330 x 490 mm
Material	Sheet steel
Weight	38 kg
Gross Weight	37.000 kg
Product Group	575