


# ISO Standard [ISO 21287] Compact Cylinder



# ISO Standard [ISO 21287] **Compact Cylinder** Series C55 Ø20, Ø25, Ø32, Ø40, Ø50, Ø63

# **How to Order**



# Applicable Auto Switches/Refer to pages 12 to 17 for further information on auto switches.

	philoadic Auto Contonos/Neier to pages 12 to 17 for infinite information of auto-switches.																
_	Special	Electrical	Indicator light	Wiring	ing Load voltage		age	Auto switch model Electrical entry direction		Lead wire length (m) *			Pre-wired	App	licable		
Typ	function	entry	gigil	(Output)		С	AC		·	0.5 (Nil)	3	5 (Z)	connector		oad		
			<u>-</u>	O sudan			7.0	Perpendicular	In-line	(INII)	(L)	(८)		10			
σ.	=		Yes	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	•	_	_	IC circuit	_		
Reed		Grommet	163	2-wire	24 V	12 V	100 V	A93V	A93	•	•	_	_	_	Relay,		
-	0		_	Z-WIIE		5 V, 12 V	100 V or less	A90V	A90	•	•	_	_	IC circuit	PLC		
				3-wire		5 V		M9NV	M9N	•	•	0	0	IC			
	-			3-wire (PNP)		12 V	12 V	M9PV	M9P	•	•	0	0	circuit			
switch				2-wire		12 V		M9BV	М9В	•	•	0	0	_			
	Diagnostic			3-wire (NPN)		5 V		M9NWV	M9NW	•	•	0	0	IC	Relay,		
state	indication / 2-colour	Grommet	Grommet Yes	3-wire (PNP)	24 V	40.1/	_	M9PWV	M9PW	•	•	0	0	circuit	PLC		
Solids	indication)	er tant our \	II I	11						M9BWV	M9BW	•	•	0	0		
	Water resistant (2-colour indication)			2-wire		12 V		_	М9ВА	_	•	0	_	_			

<sup>\*</sup> Lead wire length symbols: 0.5 m ....... Nil (Example) M9N 3 m ..... L (Example) M9NL

3 m ...... L 5 m ..... Z (Example) M9NZ



<sup>\*</sup> O solid state auto switch is available after receiving an order.



# **⚠** Caution

- Be sure to read before handling. Refer to Best Pneumatics catalogue for Safety Instructions, Actuators and Auto Switches Precautions.
- 2) This product should not be used as a stopper.
- 3 Use the PF thread fittings for this cylinder

# Theoretical Output

-	→ OUT	•	  -   IN

				Unit: N		
Bore size	Operating	Operating pressure (MPa)				
(mm)	direction	0.3	0.5	0.7		
20	IN	71	118	165		
20	OUT	94	157	220		
25	IN	113	189	264		
25	OUT	147	245	344		
32	IN	181	302	422		
32	OUT	241	402	563		
40	IN	317	528	739		
40	OUT	377	628	880		
50	IN	495	825	1150		
30	OUT	589	982	1370		
63	IN	841	1400	1960		
US	OUT	935	1560	2180		

# Mounting Bracket Part No.

Bore size (mm)	Foot	Flange	Single clevis
20	C55-L020	C55-F020	C55-C020
25	C55-L025	C55-F025	C55-C025
32	C55-L032	C55-F032	C55-C032
40	C55-L040	C55-F040	C55-C040
50	C55-L050	C55-F050	C55-C050
63	C55-L063	C55-F063	C55-C063

- Order two foot brackets per cylinder.
- Parts belonging to each bracket are as follows.
   Foot, Flange, Single clevis/Body mounting bolt

# **Specifications**

Туре	Pneumatic (Non-lube)			
Action	Double acting, Single rod			
Fluid	Air			
Proof pressure	1.5 MPa			
Maximum operating pressure	1.0 MPa			
Minimum operating pressure	0.05 MPa			
Ambient and fluid temperature	Without auto switch: -10 to 70°C (No freezing) With auto switch: -10 to 60°C (No freezing)			
Cushion	Rubber bumper on both end			
Stroke length tolerance	+1.0 mm 0			
Mounting	Through-hole/Both ends tapped common			
Piston speed	50 to 500 mm/s			

# **Standard Stroke**

Bore size (mm)	Standard stroke (mm)
20 to 63	5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 60, 80, 100, 125, 150

# **Manufacture of Intermediate Stroke**

Description	Dealing with the stroke by the 1 mm interval by using an exclusive body with the specified stroke				
Part no.	Refer to "How to Order" for the standard model no. (page at left)				
Stroke range	6 to 149				
Example	Part no.: C55B32-47				
Example	Makes 47 stroke tube				

# Weight

497 | 534 | 570 | 607 | 644 | 681 | 718 | 755 | 791

677 | 717 | 757 | 797 | 837 | 877 | 917 | 957 | 997 | 1037 | 1117 | 1277 | 1437

#### Without Auto Swtich Unit: g Cylinder stroke (mm) Bore size (mm)

828 | 902 | 1049 | 1197 | 1381 | 1565

#### With Auto Switch (Built-in magnet) Unit: g Cylinder stroke (mm) Bore size (mm)

Add each weight of auto switches and mounting brackets when mounting an auto switches. Refer to pages 14 to 17 for auto switch weight.




1638 1838

# **Allowable Lateral Load**

# Make sure to operate strictly within the allowable lateral load range to the rod end.


Operation outside of this range may result in shorter service life or damage to the device.



# **Allowable Kinetic Energy**

Make sure to operate strictly within the allowable range of the load weight and maximum speed.


Operation outside of this range may cause excessive impact, which may result in the damage to the device.




<sup>\*</sup> Refer to Model Selection in Best Pneumatics catalogue for details about model selection procedure.


# Construction

# ø**20**, ø**25**



ø32 to ø63






M: Rod end male thread


# **Component Parts**

COIII	ponent raits		
No.	Description	Material	Note
1	Cylinder tube	Aluminum alloy	Hard anodized
2	Piston	Aluminum alloy	Chromated
_	Di-1	Stainless steel	ø20, ø25
3	Piston rod	Carbon steel	ø32 to ø63 Hard chrome plated
	Caller	Aluminum alloy	ø20 to ø40 Anodized
4	Collar	Aluminum alloy casted	ø50, ø63 Painted after chromated
5	Snap ring	Carbon tool steel	Phosphate coated
6	Bumper A	Urethane	
7	Bumper B	Urethane	
_	Dunking	Oil-impregnated sintered alloy	ø20, ø25
8	Bushing	Phosphor bronze alloy	ø32 to ø63
9	Wear ring	Resin	
10	Magnet	_	
11	Rod end nut	Carbon steel	Nickel plated
12	Rod seal	NBR	
13	Piston seal	NBR	
14	Tube gasket	NBR	

# With auto switch (Built-in magnet)



With auto switch (Built-in magnet)



### Replacement Parts: Seal Kit


. topiacomo	ropiacoment i arter coar itii						
Bore size (mm)	Kit no.	Contents					
20	CQ2B20-PS						
25	CQ2B25-PS						
32	CQ2B32-PS	Set of nos.					
40	CQ2B40-PS	above (12), (13), (14)					
50	CQ2B50-PS	6, 6,					
63	CQ2B63-PS						

<sup>\*</sup> Seal kit includes ②, ③, ④. Order the seal kit, based on each bore size.



# **Mounting Bolt**

Should use recommended bolt shown as below table when mounting the cylinder using through-hole.



Note) To install a through-hole type mounting bolt, bore size 20 to 63 mm, make sure to use the flat washer that is provided.

# **Mounting Bolt for C55**


Model	С	D	Mounting bolt		
C(D)55B20-5		45	M4 x 45 ¢		
-10		50	x 50 €		
-15		55	x 55 ℓ		
-20		60	x 60 ℓ		
-25		65	x 65 ℓ		
-30	7.2	70	x 70 ℓ		
-35	-	75	x 75 ℓ		
-40		80	x 80 ℓ		
-45		85	x 85 ℓ		
-50		90	x 90 €		
-60					
-80			der by using		
-100	the OA thread that are provided with the cylinder tube.				
-125					
-150					
C(D)55B25-5		50	M4 x 50 ℓ		
-10		55	x 55 ℓ		
-15		60	x 60 ℓ		
-20		65	x 65 ℓ		
-25	10.2	70	x 70 ℓ		
-30	10.2	75	x 75 ℓ		
-35		80	x 80 ℓ		
-40		85	x 85 ℓ		
-45		90	x 90 ℓ		
-50		95	x 95 ℓ		
-60	Fi 41-		d = =		
-80	Fix the cylinder by using the OA thread that are provided with the cylinder				
-100					
-125	tube.				
-150					

Model   C   D   Mounting bolt		_	_			
10	Model	С	D	Mounting bolt		
-15 -20 -25 -30 -35 -40 -40 -45 -50 -100 -125 -150 -100 -15 -150 -100 -15 -150 -100 -15 -150 -100 -15 -150 -100 -15 -150 -100 -15 -150 -100 -15 -150 -100 -150 -15	C(D)55B32-5		55	M5 x 55 ℓ		
To	-10		60	x 60 ℓ		
-25 -30 -35 -40 -40 -45 -45 -50 -60 -100 -125 -150 -150 -150 -150 -150 -150 -150 -15	-15		65	x 65 ℓ		
Solution	-20		70	x 70 ℓ		
-35   10   85   x 85 \( \cdot \)	-25		75	x 75 ℓ		
-40     -45     -45     -50     -60     -100     -125     -150     -150     -150     -150     -150     -150     -100     -150	-30		80	x 80 ℓ		
-45 -50 -60 -60 -100 -100 -100 -125 -150 -150 -150 -150 -150 -150 -150 -15	-35	10	85	x 85 ℓ		
-50 -60 -60 -110 x 100 ℓ -130 x 130 ℓ -100 -125 -150 -150 -150 -150 -150 -150 -150 -15	-40		90	x 90 ℓ		
-60 -80 -100 -100 -125 -150 -150 -150 -150 -150 -150 -150 -15	-45		95	x 95 ℓ		
-80 -100 -100 -125 -150 -150 -150 -150 -150 -150 -150 -15			100	x 100 ℓ		
-100   150   x 150 ℓ  -125   Fix the cylinder by using the OA thread that are provided with the cylinder tube.  C(D)55B40-5   55   M5 x 55 ℓ  -10   60   x 60 ℓ  -15   65   x 65 ℓ  -20   70   x 70 ℓ  -25   75   x 75 ℓ  -30   80   x 80 ℓ  -35   9   85   x 85 ℓ  -40   90   x 90 ℓ  -45   95   x 95 ℓ  -50   100   x 100 ℓ  -60   110   x 110 ℓ  -80   -100   150   x 150 ℓ  Fix the cylinder by using the OA thread that are provided with the colling to the colling to the cylinder by using the OA thread that are provided with the colling to the cylinder by using the OA thread that are provided with the colling to the cylinder by using the OA thread that are provided with the colling to the cylinder by using the OA thread that are provided with the colling to the cylinder by using the OA thread that are provided with the colling to the cylinder by using the OA thread that are provided with the colling to the cylinder by using the OA thread that are provided with the colling to the cylinder by using the OA thread that are provided with the colling to the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are provided with the cylinder by using the OA thread that are pro			110	x 110 ℓ		
-125 -150  -150  -150  -150  -150  -150  -150  -150  -10  -1	-80		130	x 130 ℓ		
-150 cylinder tube.  C(D)55B40-5 -10 -15 -60 -20 -35 -40 -45 -50 -60 -10 -15 -60 -10 -15 -60 -10 -15 -16 -17 -18 -18 -19 -19 -19 -19 -19 -19 -19 -19 -19 -19	-100		150	x 150 ℓ		
-150 cylinder tube.  C(D)55B40-5 -10 -15 -60 -20 -35 -40 -45 -50 -60 -10 -15 -60 -10 -15 -60 -10 -15 -16 -17 -18 -18 -19 -19 -19 -19 -19 -19 -19 -19 -19 -19	-125	Fix the	ne cylinder by using the OA			
-10 -15 -20 -25 -30 -35 -40 -45 -50 -100 -100 -125 -100 -125 -100 -125 -15 -160 -17 -18 -18 -18 -19 -100 -18 -19 -100 -100 -100 -100 -100 -100 -100	-150	cylinder tube.				
-15 -20 -25 -30 -35 -40 -45 -50 -60 -100 -125 -15 -15 -15 -15 -15 -15 -15 -15 -15 -1	C(D)55B40-5		55	M5 x 55 ℓ		
-20 -25 -30 -35 9 85	-10	1	60	x 60 ℓ		
-25 -30 -35 9 85	-15		65	x 65 ℓ		
-30 -35 9 85	-20		70	x 70 ℓ		
-35 9 85 x 85 \( \ell \) -40 90 x 90 \( \ell \) -45 95 x 95 \( \ell \) -50 100 x 100 \( \ell \) -60 110 x 110 \( \ell \) -80 130 x 130 \( \ell \) -100 150 x 150 \( \ell \) -125 Fix the cylinder by using the OA thread that are provided with the	-25		75	x 75 ℓ		
-40     -45     -50     -60     -80     -100     -125     Fix the cylinder by using the OA thread that are provided with the	-30		80	x 80 ℓ		
-45 -50 -60 -100 -100 -125 -50 -45 -50 -50 -50 -50 -60 -60 -60 -70 -70 -70 -70 -70 -70 -70 -70 -70 -7	-35	9	85	x 85 ℓ		
-50	-40	]	90	x 90 ℓ		
-60	-45		95	x 95 ℓ		
-80   130   x 130 ℓ  -100   150   x 150 ℓ  -125   Fix the cylinder by using the OA thread that are provided with the	-50	]	100	x 100 ℓ		
-100 150 x 150 \(\ell \text{150 } \ell \text{150 } \ell \text{150 } \ell \text{150 } \(\ell \text{150 } \ell \text{150 } \(\ell \text{150 } \ell \text{150 } \text{150 } \ell \text{150 } \ell \text{150 } \ell \text{150 } \text{150 } \ell \text{150 } \text{150 } \ell \text{150 } \tex	-60		110	x 110 ℓ		
-125 Fix the cylinder by using the OA thread that are provided with the	-80		130	x 130 ℓ		
thread that are provided with the	-100		150	x 150 ℓ		
-150 cylinder tube.	-125	Fix the	Fix the cylinder by using the OA			
	-150			novided with the		


Model	С	D	Mounting bolt		
C(D)55B50-5		55	M6 x 55 ℓ		
-10		60	x 60 ℓ		
-15		65	x 65 ℓ		
-20		70	x 70 ℓ		
-25		75	x 75 ℓ		
-30		80	x 80 ℓ		
-35	8.4	85	x 85 ℓ		
-40		90	x 90 ℓ		
-45		95	x 95 ℓ		
-50		100	x 100 ℓ		
-60		110	x 110 ℓ		
-80		130	x 130 ℓ		
-100		150	x 150 ℓ		
-125	Fix the	cylinder	der by using the OA are provided with the		
-150	cylinder tube.				
C(D)55B63-5		60	M6 x 60 ℓ		
-10		65	x 65 ℓ		
-15		70	x 70 ℓ		
-20		75	x 75 ℓ		
-25		80	x 80 ℓ		
-30		85	x 85 ℓ		
-35	9.4	90	x 90 €		
-40		95	x 95 ℓ		
-45		100	x 100 ℓ		
-50		105	x 105 ℓ		
-60		115	x 115 ℓ		
-80		135	x 135 ℓ		
-100		155	x 155 ℓ		
-125	Fix the cylinder by using the OA thread that are provided with the				
-150	cylinde	r tube.			

# **Dimensions**

# ø**20**, ø**25**



Basic Style	9																	(mm)
Bore size (mm)	Α	В	С	D	E	F	н	ı	К	L	М	N	OA	ОВ	Q	RA	RB	Т
20	43	37	10	10	36	5.5	M6	43	8	6	22	4.5	M5	7.5	13	10	5	0.8
25	45	39	10	12	40	5.5	M6	48	10	6	26	4.5	M5	7.5	13	10	5	0.8




Rod End I	Viale 1	hread	b					(mm)
Bore size (mm)	B₁	С	D	Н	H₁	K	L	Х
20	13	14	10	M8	5	8	22	16
25	13	14	12	M8	5	10	22	16




# **Dimensions**

# ø32 to ø63



Basic Style	е																			(mm)
Bore size (mm)	A	В	С	D	Е	F	Н	ı	J	K	L	М	N	OA	ОВ	Q	RA	RB	Т	Z
32	51	44	12	16	46	8.5	M8	59	2	14	7	32.5	5.5	M6	9	14.5	11	5	1	15
40	52	45	12	16	52	9.5	M8	67	3	14	7	38	5.5	M6	9	14.5	11	5	1	17
50	53	45	16	20	64	10.5	M10	82	2	17	8	46.5	6.6	M8	10.5	13.5	11	5	1.6	17
63	57	49	16	20	74	14.5	M10	96	3	17	8	56.5	6.6	M8	10.5	15.5	11	5	1.6	17




Rod End I	Male <sup>*</sup>	Threa	ad					(mm)
Bore size (mm)	Bı	С	D	Н	H₁	К	L	х
32	17	16.5	16	M10 x 1.25	6	14	26	19
40	17	16.5	16	M10 x 1.25	6	14	26	19
50	19	19.5	20	M12 x 1.25	7	17	30	22
63	19	19.5	20	M12 x 1.25	7	17	30	22
	•	•						




# **Mounting Bracket**

# **Foot bracket**




# Flange bracket



											(111111)
Bore size (mm)	L	LD	LH	LT	LX	LZ	М	R	х	Υ	Hexagon socket head cap screw
20	22	7	27	4	22	36	22	8	16	7	M5
25	22	7	29	4	26	40	26	10	16	7	M5
32	24.5	7	33.5	4	32	46	32.5	15	16	7	M6
40	26	10	38	4	36	52	38	17.5	18	9	M6
50	31	10	45	5	45	64	46.5	20	21	9	M8
63	31	10	50	5	50	74	56.5	22.5	21	9	M8

											(111111)
	Bore size (mm)	<b>D</b> <sub>H11</sub>	М	FD	FL	FT	FV	FX	FY	FZ	Hexagon socket head cap screw
	20	16	22	6.6	2.8	8	38	55	_	68	M5
	25	16	26	6.6	2.8	8	38	60	_	73	M5
	32	30	32.5	7	5	10	50	64	32	79	M6
ĺ	40	35	38	9	5	10	55	72	36	90	M6
	50	40	46.5	9	6	12	70	90	45	110	M8
Ī	63	45	56.5	9	6	12	80	100	50	120	M8

# Single clevis bracket



									(mm)
Bore size (mm)	СДнэ	CL	CU	cw	CX-0.2	CZ	М	RR	Hexagon socket head cap screw
20	8	3	12	20	16	35	22	9	M5
25	8	3	12	20	16	40	26	9	M5
32	10	5.5	12	22	26	45	32.5	9.5	M6
40	12	5.5	15	25	28	51	38	12	M6
50	12	6.5	15	27	32	64	46.5	12	M8
63	16	6.5	20	32	40	74	56.5	16	M8



# Proper Auto Switch Mounting Position (Detection at Stroke End) and Its Mounting Height

Reed switch D-M9 D-M9BAL D-M9BAL D-M9 W Ø20, 25

\* Figures in the table below are used as a reference when mounting the auto switches for stroke end detection. In the case of actually setting the auto switches, adjust them after confirming their operation.

(mm)

Auto switch me	odel		D-A9□	]		D-M9 □ D-M9 □			D-M	BAL	
Symbol		Α	В	W	Α	В	W	Α	В	W	Hs
	20	11.5	5.5	3.5(1)	15.5	9.5	-0.5	14.5	8.5	-9.5	22
	25	11.5	7.5	5.5(3)	15.5	11.5	1.5	14.5	10.5	-7.5	24
Bore size	32	15	9	7 (4.5)	19	13	3	18	12	-6	27
(mm)	40	16	9	7 (4.5)	20	13	3	19	12	-6	30
	50	9.5	15.5	13.5(11.5)	13.5	19.5	9.5	12.5	18.5	0.5	36
	63	11.5	17.5	15.5(13.5)	15.5	21.5	11.5	14.5	20.5	2.5	41

The dimension inside ( ) is for D-A93.


Reed switch D-A9□V

Solid state switch

D-M9□V


D-M9□WV


ø**20, 25** 





ø**32, 40, 50, 63** 





\* Figures in the table below are used as a reference when mounting the auto switches for stroke end detection. In the case of actually setting the auto switches, adjust them after confirming their operation.


(mm)

							١ ,
Auto switch mo	odel		D-A9□	]V		D-M9□' D-M9□'	
Symbol		Α	В	Hs	Α	В	Hs
	20	11.5	5.5	22	15.5	9.5	24
	25	11.5	7.5	24	15.5	11.5	26
Bore size	32	15	9	27	19	13	29
(mm)	40	16	9	30	20	13	32
	50	9.5	15.5	36	13.5	19.5	38
	63	11.5	17.5	41	15.5	21.5	43



# The Number of Surfaces and Grooves Where an Auto Switch Can Be Mounted (As Direct Mounting)

The number of the surfaces and grooves where the auto switch can be mounted, by switch type, are shown in the table below.



Switch model		D-A9	], M9□	
Bore size (mm)	(Mounting groove no.)	<b>B</b> (Mounting groove no.)	C (Mounting groove no.)	<b>D</b> (Mounting groove no.)
20	(1)	(2)	(2)	(2)
25	(2)	(2)	(2)	(2)
32	(2)	(2)	(2)	(2)
40	(2)	(2)	(2)	(2)
50	(2)	(2)	(2)	(2)
63	(2)	(2)	(2)	(2)

# **Operating Range**

						(mm)
Auto quitale mandal			Bore	size		
Auto switch model	20	25	32	40	50	63
D-M9□W(V) D-M9BAL	5	5.5	6	6	6	6.5
D-A9□(V)	9	9	9	9	9	10.5
D-M9□(V)	3	3.5	3.5	3.5	3.5	4

<sup>\*</sup> The operating ranges are provided as guidelines including hystereses and are not guaranteed values (assuming approximately ±30% variations). They may vary significantly with ambient environments.

# **Minimum Auto Switch Mounting Stroke**

(mm) Bore size Auto switch model D-M9□WV D-M9BAL D-M9□ D-M9□V D-M9□W D-A9□ A9□V Number of auto switches 2 pcs. 1 pc. 2 pcs. 25,32,40,50 1 pc. 2 pcs. 1 pc.

Besides the models listed in "How to Order," the following auto switches are applicable. Refer to Best Pneumatics for detailed specifications.


Туре	Part no.	Electrical entry	Features
Solid state switch	D-F9G	Crommet (In line)	Normally closed (N.C. = b contact), 3-wire
Solid State Switch	D-F9H	Grommet (In-line)	Normally closed (N.C. = b contact), 2-wire



# **Mounting of Auto Switch**

To mount auto switches, follow the instruction illustrated below.

# ø20 to ø63/Direct mounting



•Use a watchmakers' screwdriver with a handle 5 to 6 mm in diameter when tightening the auto switch mounting screw.


Tightening torque should be set 0.10 to 0.20 N·m.

# **Auto Switch Specifications**

# **Auto Switch Common Specifications**

Туре	Reed switch	Solid state switch		
Leakage current	None	3-wire: 100 μA or less 2-wire: 0.8 mA or less		
Operating time	1.2 ms	1 ms or less		
Impact resistance	300 m/s <sup>2</sup>	1000 m/s <sup>2</sup>		
Insulation resistance	50 $\text{M}\Omega$ or more at 500 VDC Mega (between lead wire and case)			
Withstand voltage	1000 VAC for 1 minute (between lead wire and case)			
Ambient temperature	−10 to 60°C			
Enclosure	IEC529 standard IP67, Immersible construction (JIS C 0920)			

# **Lead Wire Length**



Note 1) Applicable auto switch with 5 m lead wire "Z"

Solid state switch: Manufactured upon receipt of order as standard.


- Note 2) The standard lead wire length of solid state switch with water resistant 2-colour indication type is 3 meters. (Not available 0.5 m)
- Note 3) To designate solid state switches with flexible specifications, add "-61" after the lead wire length.



Note) D-M9□(V) series use flexible lead wire as standard.

# **Auto Switch Hysteresis**

The hysteresis is the difference between the position of the auto switch as it turns "on" and as it turns "off". A part of operating range (one side) includes this hysteresis.



# **Contact Protection Boxes: CD-P11, CD-P12**

#### <Applicable switch model>

D-A9/A9□V

The above auto switches do not have internal contact protection circuit.

- 1. Operating load is an inductive load.
- 2. The length of wiring to the load is 5 m or more.
- 3. The load voltage is 100 VAC.

The contact life may be shortened. (Due to permanent energising conditions.)


# **Specifications**

Part No.	CD-P11		CD-P12
Load voltage	100 VAC	200 VAC	24 VDC
Maximum load current	25 mA	12.5 mA	50 mA


\* Lead wire length — Switch connection side 0.5 m Load connection side 0.5 m



#### Internal Circuits



#### **Dimension**




# Connection

To connect a switch unit to a contact protection box, connect the lead wire from the side of the contact protection box marked SWITCH to the lead wire coming out of the switch unit. Keep the switch as close as possible to the contact protection box, with a lead wire length of no more than 1 meter.




# **Auto Switches Connections and Examples**

# **Basic Wiring**




# **Examples of Connection to PLC (Programmable Logic Controller)**

# Sink input specifications 3-wire, NPN




Source input specifications
 3-wire, PNP




Connect according to the applicable PLC input specifications, as the connection method will vary depending on the PLC input specifications.

2-wire




#### 2-wire




# Connection Examples for AND (Serial) and OR (Parallel)

# 3-wire

# AND connection for NPN output (using relays)




# AND connection for NPN output (performed with switches only)




The indicator lights will light up when both switches are turned ON.

#### **OR connection for NPN output**



ches.

### 2-wire with 2-switch AND connection




When two switches are connected in series, a load may malfunction because the load voltage will decline when in the ON state.

The indicator lights will light up if both of the switches are in the ON state.

Load voltage at ON = Power supply - Internal voltage drop x 2 pcs.
= 24 V - 4 V x 2 pcs.
= 16 V

Example: Power supply is 24 VDC. Internal voltage drop in switch is 4 V.

### 2-wire with 2-switch OR connection



(Solid state)
When two switches are connected in parallel, a malfunction may occur because the load voltage will increase when in the OFF state.

Load voltage at OFF = Leakage current x 2 pcs. x Load impedance = 1 mA x 2 pcs. x 3 k $\Omega$  - 6 V

Example: Load impedance is 3 k $\Omega$ . Leakage current from switch is 1 mA.

Because there is no current leakage, the load voltage will not increase when turned OFF. However, depending on the number of switches in the ON state, the indicator lights may sometimes dim or not light because of the dispersion and reduction of the current flowing to the swit-

(Reed switch)



# **Reed Switch: Direct Mounting Style** D-A90(V)/D-A93(V)/D-A96(V)

# **Grommet Electrical entry direction: In-line**




# **△**Caution

# **Operating Precautions**

Fix the switch with appropriate screw installed on the switch body. If using other screws, switch may be damaged.

# **Auto Switch Internal Circuit**



- Note) 1. Operating load is an induction load.
  - 2. The length of wiring to the load is 5 m or
  - 3. The load voltage is 100 VAC.

Use the contact protection box in any of the above listed situations.

The contact point life may be shortened. (Refer to page 12 for contact protection box.)

# **Auto Switch Specifications**

		PLC: Progr	ammable Logic Controller			
D-A90/D-A90V (without indicator light)						
Auto switch model		D-A90/D-A90V				
Applicable load		IC circuit, Relay, PLC				
Load voltage	24 V AC/DC or less	48 V AC/DC or less	100 V AC/DC or less			
Maximum load current	50 mA	50 mA 40 mA				
Contact protection circuit	None					
Internal resistance	1 Ω or les	1 Ω or less (including lead wire length of 3 m)				
D-A93/D-A93V/D-A96/D-A96V (with indicator light)						
Auto switch model	D-A93/I	D-A93V	D-A96/D-A96V			
Applicable load	Relay	, PLC	IC circuit			
Load voltage	24 VDC 100 VAC		4 to 8 VDC			
Load current range and max. load current	5 to 40 mA	5 to 20 mA	20 mA			
current						

DI C. Drammanahla I ania Cantralla

0.8 V or less

Indicator light Lead wires

Internal voltage

D-A90(V)/D-A93(V) — Oilproof vinyl heavy-duty cord: Ø2.7, 0.18 mm² x 2 cores (Brown, Blue), 0.5 m D-A96(V) — Oilproof vinyl heavy-duty cord: Ø2.7, 0.15 mm² x 3 cores (Brown, Black, Blue), 0.5 m Note 1) Refer to page 12 for reed switch common specifications. Note 2) Refer to page 12 for lead wire lengths.

Red LED lights when ON


D-A93 — 2.4 V or less (to 20 mA)/3 V or less (to 40 mA)

D-A93V — 2.7 V or less

Weight Unit: g

Auto switch model	D-A90	D-A90V	D-A93	D-A93V	D-A96	D-A96V
Lead wire length: 0.5 m	6	6	6	6	8	8
Lead wire length: 3 m	30	30	30	30	41	41

#### **Dimensions** Unit: mm



# Solid State Switch: Direct Mounting Style D-M9N(V)/D-M9P(V)/D-M9B(V) ( €

#### **Grommet**


- 2-wire load current is reduced (2.5 to 40 mA)
- Lead-free
- Using UL certified (style 2844) lead wire.



# **Operating Precautions**

Fix the switch with appropriate screw installed on the switch body. If using other screws, switch may be damaged.

# **Auto Switch Internal Circuit**



# **Auto Switch Specifications**

PLC: Programmable Logic Controller

D-M9□/D-M9□V (with indicator light)						
Auto switch model	D-M9N	D-M9NV	D-M9P	D-M9PV	D-M9B	D-M9BV
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular
Wiring type		3-w	ire		2-v	vire
Output type	N	PN	PN	IP.	_	_
Applicable load		IC circuit, Relay, PLC			24 VDC r	elay, PLC
Power supply voltage	5	5, 12, 24 VDC (4.5 to 28 V)				_
Current consumption	10 mA or less				_	_
Load voltage	28 VD0	28 VDC or less —			24 VDC (10	to 28 VDC)
Load current	40 mA or less 2.5 to 40 n				40 mA	
Internal voltage drop	0.8 V or less 4 V or less				r less	
Leakage current	100 μA or less at 24 VDC 0.8 mA or less				or less	
Indicator light	•		Red LED ligh	nts when ON.		

Lead wires

Oilproof vinyl heavy-duty cord: ø2.7 x 3.2 ellipse, 0.15 mm²,

D-M9B(V) 0.15 mm<sup>2</sup> x 2 cores D-M9N(V), D-M9P(V) 0.15 mm<sup>2</sup> x 3 cores


Note 1) Refer to page 12 for solid state switch common specifications.

Note 2) Refer to page 12 for lead wire lengths.

Weight Unit: g

Auto switch mode	el	D-M9N(V)	D-M9P(V)	D-M9B(V)
	0.5	8	8	7
Lead wire length (m)	3	41	41	38
()	5	68	68	63

# **Dimensions** Unit: mm





# 2-colour Indication Type, Solid State Switch: Direct Mounting Style

# D-F9NW(V)/D-F9PW(V)/D-F9BW(V) ( €


# **Grommet**

# 

# **Operating Precautions**

Fix the switch with appropriate screw installed on the switch body. If using other screws, switch may be damaged.

#### **Auto Switch Internal Circuit**



# **Auto Switch Specifications**

D-F9 W/D-F9 WV (with indicator light

**D-F9NWV** 

Perpendicular

3-wire

D-F9NW

In-line

light)				
D-F9PW	D-F9PWV	D-F9BW	D-F9BWV	
In-line	Perpendicular	In-line	Perpendicular	
)		2-wire		
PNP			_	
ay, PLC		24 VDC	elay, PLC	
5 to 28 VD	C)		_	

PLC: Programmable Logic Controller

Output type	NPN	PNP	_	
Applicable load	IC circuit, F	24 VDC relay, PLC		
Power supply voltage	5, 12, 24 VDC	_		
Current consumption	10 mA	10 mA or less		
Load voltage	28 VDC or less	_	24 VDC (10 to 28 VDC)	
Load current	40 mA or less	80 mA or less	5 to 40 mA	
Internal voltage drop	1.5 V or less (0.8 V or less at 10 mA load current)	0.8 V or less	4 V or less	
Leakage current	100 uA or les	100 uA or less at 24 VDC		

Operating position ..... Red LED lights when ON. Indicator light Optimum operating position ...... Green LED lights when ON.

Auto switch model

Electrical entry direction

Wiring type

Oilproof vinyl heavy-duty cord: Ø2.7, 0.15 mm<sup>2</sup> x 3 cores (Brown, Black, Blue), 0.18 mm<sup>2</sup> x 2 cores (Brown, Blue), 0.5 m

Note 1) Refer to page 12 for solid state switch common specifications.


Note 2) Refer to page 12 for lead wire lengths.

#### Weight Unit: g

Auto switch mode	el	D-F9NW(V)	D-F9PW(V)	D-F9BW(V)
	0.5	7	7	7
Lead wire length (m)	3	34	34	32
(111)	5	56	56	52

# **Dimensions**

Unit: mm





# Water Resistant 2-colour Indication Type Solid State Switch: Direct Mounting Style D-M9BAL

### **Grommet**

# Water (coolant) resistant type



# 

# **Operating Precautions**

- 1. Please consult with SMC if using coolant liquid other than water based solution.
- Fix the switch with appropriate screw installed on the switch body. If using other screws, switch may be damaged.

# **Auto Switch Specifications**

	PLC: Programable Logic Controller
D-M9BAL (with indica	ator light)
Auto switch model	D-M9BAL
Wiring type	2-wire
Output type	_
Applicable load	24 VDC relay, PLC
Power supply voltage	_
Current consumption	_
Load voltage	24 VDC (10 to 28 VDC)
Load current	5 to 30 mA
Internal voltage drop	5 V or less
Leakage current	1 mA or less at 24 VDC
Indicator light	Operating position Red LED lights when ON. Optimum operating position Green LED lights when ON.


Lead wires

Oilproof vinyl heavy-duty cord: ø2.7, 2 cores (Brown, Blue), 0.18 mm², 0.5 m Note 1) Refer to page 12 for solid state switch common specifications. Note 2) Refer to page 12 for lead wire lengths.

Weight Unit: g


Auto Switch Mode	el	D-M9BA
	0.5	_
Lead wire length (m)	3	37
(,	5	57

# **Auto Switch Internal Circuit**



# **Dimensions**

Unit: mm



17