



# ALFRA BLECHLOCHER® MONOCUT®

Ø in mm	Max. Material- stärke in mm (S235)	Größe Metrisch	Größe PG	Größe Inch	Größe Conduit & Pipe Size					
						Stempel und Matrize		passende Zugbolzen	passende Zugschraube	passende Zugschraube mit Kugellager
						Zugschraube mit Kugellager	Zugschraube			
Art.-Nr.										
12,7	2,0	M 12	7	1/2"	0.500	-	01002	01001		
14,3	2,0	-	-	9/16"	0.563	-	01014	01013		
15,2	2,0	-	9	-	0.598	-	01006	01005		
16,0	2,0	-	-	-	0.630	-	01016	01015		
16,2	2,0	M 16	-	-	0.638	-	01010	01009		
17,5	2,0	-	-	11/16"	0.689	-	01018	01017		
18,6	2,0	-	11	-	0.732	-	01022	01021		
19,0	2,0	-	-	3/4"	0.748	-	01026	01025	01335	
20,0	2,0	-	-	-	0.787	-	01030	01029		
20,4	2,0	M 20	13	-	0.803	-	01034	01033	01339	
20,6	2,0	-	-	13/16"	0.811	-	01038	01037		
22,0	2,0	-	-	-	0.866	-	01042	01041		
22,5	2,0	-	16	7/8"	0.886	1/2"	01046	01045		
23,8	2,0	-	-	15/16"	0.937	-	01050	01049		
25,0	2,0	-	-	-	0.984	-	01054	01053		
25,4	2,0	M 25	-	1"	1.000	-	01058	01057		
27,0	2,0	-	-	1-1/16"	1.063	-	01078	01077	01336	
28,3	2,0	-	21	-	1.114	3/4"	01070	01069		
28,3	3,0	-	21	-	1.114	3/4"	01074	01073	01337	
28,6	2,0	-	-	1-1/8"	1.126	-	01080	01079		
30,1	2,0	-	-	-	1.185	-	01086	01085		
30,5	2,0	-	-	1-7/32"	1.201	-	01094	01093	01336	
31,7	2,0	-	-	1-1/4"	1.248	-	01102	01101	01339	
32,5	2,0	M 32	-	-	1.280	-	01106	01105		
33,4	2,0	-	-	1-5/16"	1.315	-	01110	01109		
34,6	3,0	-	-	1-11/32"	1.362	1"	01118	01117	01337	
35,0	2,0	-	-	1-3/8"	1.378	-	01122	01121	01336	
35,0	3,0	-	-	1-3/8"	1.378	-	01126	01125	01339	
37,0	3,0	-	29	-	1.457	-	01130	01129		
38,0	3,0	-	-	1-1/2"	1.496	-	01134	01133		
40,5	3,0	M 40	-	-	1.594	-	01150	01149		
41,3	3,0	-	-	1-5/8"	1.626	-	01154	01153	01337	
42,8	3,0	-	-	-	1.685	-	01158	01157		
43,2	3,0	-	-	1-11/16"	1.701	1 1/4"	01162	01161		
44,5	3,0	-	-	1-3/4"	1.752	-	01164	01163		
47,0	3,0	-	36	-	1.850	-	01166	01165		
47,6	3,0	-	-	1-7/8"	1.874	-	01182	01181	01338	
49,6	3,0	-	-	1-15/16"	1.953	1 1/2"	01170	01169		
50,5	3,0	M 50	-	-	1.988	-	01178	01177		
54,0	3,0	-	42	2-1/8"	2.126	-	01190	01189		
57,2	3,0	-	-	2-1/4"	2.252	-	01194	01193	01341	
60,0	3,0	-	48	-	2.362	-	01202	01201		
61,5	3,0	-	-	2-3/8"	2.421	2"	01206	01205		
63,5	3,0	M 63	-	2-1/2"	2.500	-	01210	01209		
66,7	3,0	-	-	2-5/8"	2.626	-	01214	01213		
Ab ø 68,0 mm empfehlen wir den Einsatz von Hydraulikgeräten.										
68,0	3,0	-	-	-	2.677	-	01242	01241		
70,0	3,0	-	-	2-3/4"	2.756	-	01222	01221		
70,6	3,0	-	-	-	2.780	-	01220	01219		
74,0	3,0	-	-	2-7/8"	2.913	2 1/2"	01234	01233	01338	
75,5	3,0	M 75	-	2-7/8"	2.972	-	01226	01225	01341	
76,2	3,0	-	-	3"	3.000	-	01230	01229		
80,0	3,0	-	-	3-1/8"	3.150	-	01238	01237		
82,0	3,0	-	-	-	3.228	-	01246	01245		
Ab 89,0 mm ist generell der Einsatz von Hydraulikgeräten erforderlich.								Notwendiges Zubehör:		
						Stempel	Matrize	Zugbolzen	Sonder- zugschraube	Konter- mutter
89,0	3,0	-	-	3-1/2"	3.504	3"	01251	01252		
92,0	3,0	-	-	3-5/8"	3.622	-	01253	01254		
100,5	3,0	-	-	-	3.957	-	01257	01258	01398	
115,5	3,0	-	-	4-1/2"	4.547	4"	01265	01266	01398L	
120,0	3,0	-	-	-	4.724	-	01267	01268	01419	