



### Product Information

Product Category	MICROWAVES
Unit Barcode	5016368055021
Outer Carton Barcode	
Commodity Code	8516500090
Country of Origin	CHINA
Primary Colour	STAINLESS STEEL
Finish	STAINLESS STEEL
Primary Material	STAINLESS STEEL
Warranty	2
Self Assembly	NO
Perishable Item	NO
Hazardous Item	NO

### General Product Specification

Voltage	230
Frequency	50
Wattage	900
Rated Current	10.42
Fuse Rating	20
Plug Type	BS 1363
Cable Diameter	1.5
Cable Length	1
Class	CLASS I
Conformity Markings	CE+UKCA

### Packaging & Shipping Information

Product Dimensions H x W x D (mm)	326	520	497
Packaged Dimensions H x W x D (mm)	382	583	544
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			18.43
Unit Packaged Weight (Kg)			20.4
Carton Weight (Kg)			
EPS (Kg)	0.443	PPT Exempt Plastic (Kg)	
Other Plastic (Kg)	0.028	Card / Paper (Kg)	1.801
Aluminium (Kg)		Steel (Kg)	0.011

### Category Specific Technical Information

Cavity Capacity	30	Freestanding or Built-in	FREESTANDING
Cavity Depth	348	Grill Function	YES
Cavity Height	242	Grill Output Power	1100
Cavity Material	STAINLESS STEEL	Housing Colour	GREY
Cavity Width	332	Interior Light	YES
Control Panel Lock	NO	Inverter Technology	NO
Control Type	DIALS & BUTTONS	MAFF Rating	YES
Convection Cooking Function	YES	Max Timer Value	95
Convection Output Power	2500	Microwave Output Power	900
Defrost Function	YES	Number of Auto Cooking Programmes	10
Digital Display	YES	Number of Microwave Power Levels	5
Door Hinge Position	LEFT	Turntable Diameter	315
Flatbed	NO	Turntable On/Off Function	NO