#### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1. PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: 38916 DRAPER LIQUID PTFE

APPLICATIONS: SEALANT

SUPPLIER: Draper Tools Ltd

Draper Tools Ltd Hursley Road Chandlers Ford Eastleigh Hampshire SO53 1YF

Draper Helpline +44 (0) 2380 494344

# SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

#### Classification

#### Physical hazards

Not Classified

#### Health hazards

Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 Skin Sens. 1 - H317 STOT SE 3 - H335

#### **Environmental hazards**

Not Classified

#### 2.2. Label elements

#### Pictogram



Signal word

Warning

Hazard statements

H315 Causes skin irritation.

H317 May cause an allergic skin reaction. H319 Causes serious eye irritation. H335 May cause respiratory irritation.

#### Precautionary statements

P261 Avoid breathing vapour/spray.

P264 Wash contaminated skin thoroughly after handling.

P271 Use only outdoors or in a well-ventilated area.

P272 Contaminated work clothing should not be allowed out of the workplace.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P302+P352 IF ON SKIN: Wash with plenty of water.

P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove

contact lenses, if present and easy to do. Continue rinsing.

P312 Call a POISON CENTER/doctor if you feel unwell. P321 Specific treatment (see medical advice on this label).

P332+P313 If skin irritation occurs: Get medical advice/attention.

P333+P313 If skin irritation or rash occurs: Get medical advice/attention.

P337+P313 If eye irritation persists: Get medical advice/attention.

P362+P364 Take off contaminated clothing and wash it before reuse.

P403+P233 Store in a well-ventilated place. Keep container tightly closed.

P405 Store locked up.

P501 Dispose of contents/container in accordance with national regulations.

Ethoxylated Bisphenol A Dimethacrylate, 2-hydroxypropyl methacrylate, 1-Acetyl-2phenylhydrazine

#### Contains

#### 2.3. Other hazards

#### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

# Ethoxylated Bisphenol A Dimethacrylate

30-60%

CAS number: 41637-38-1 EC number: -

# Classification

Skin Irrit. 2 - H315

Eye Irrit. 2 - H319

Skin Sens. 1 - H317 STOT SE 3 - H335

#### Polyethylene Glycol 200 Dimethacrylate

10-30%

CAS number: 26570-48-9 EC number: -

#### Classification

Skin Irrit. 2 - H315

Eye Irrit. 2 - H319

Classification (67/548/EEC or 1999/45/EC)

Classification (67/548/EEC or 1999/45/EC)

#### 2-hydroxypropyl methacrylate

10-30%

CAS number: 923-26-2 EC number: 213-090-3

#### Classification Eye Irrit. 2 - H319

Skin Sens. 1 - H317

Classification (67/548/EEC or 1999/45/EC)

# a,a-dimethylbenzyl hydroperoxide <1%</td> CAS number: 80-15-9 EC number: 201-254-7 Classification Classification (67/548/EEC or 1999/45/EC) Org. Perox. E - H242 Acute Tox. 4 - H302 Acute Tox. 4 - H312 Acute Tox. 3 - H331 Skin Corr. 1B - H314 Eye Dam. 1 - H318 STOT SE 3 - H335 STOT RE 2 - H373

# 1-Acetyl-2-phenylhydrazine CAS number: 114-83-0 EC number: — Classification Acute Tox. 3 - H301 Skin Irrit. 2 - H315 Eye Irrit. 2 - H319

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

#### SECTION 4: First aid measures

Skin Sens. 1 - H317 STOT SE 3 - H335

Aquatic Chronic 2 - H411

# 4.1. Description of first aid measures

#### Inhalation

Move affected person to fresh air at once. Get medical attention if any discomfort continues.

#### Ingestion

Rinse mouth thoroughly with water. Give plenty of water to drink. Do not induce vomiting. Get medical attention.

#### Skin contact

Wash skin thoroughly with soap and water. Get medical attention. Remove contaminated clothing.

#### Eye contact

Rinse immediately with plenty of water. Continue to rinse for at least 15 minutes and get medical attention.

# 4.2. Most important symptoms and effects, both acute and delayed

#### Inhalation

May cause respiratory system irritation.

#### Skin contact

May cause sensitisation by skin contact.

# 4.3. Indication of any immediate medical attention and special treatment needed

#### Notes for the doctor

Treat symptomatically.

#### SECTION 5: Firefighting measures

# 5.1. Extinguishing media

#### Suitable extinguishing media

Extinguish with foam, carbon dioxide or dry powder.

#### Unsuitable extinguishing media

Do not use water jet as an extinguisher, as this will spread the fire.

# 5.2. Special hazards arising from the substance or mixture

#### Hazardous combustion products

Oxides of carbon. Oxides of nitrogen. Irritating gases or vapours.

#### 5.3. Advice for firefighters

# Special protective equipment for firefighters

Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

#### SECTION 6: Accidental release measures

# 6.1. Personal precautions, protective equipment and emergency procedures

#### Personal precautions

Avoid contact with skin and eyes. Provide adequate ventilation.

#### 6.2. Environmental precautions

#### **Environmental precautions**

Avoid discharge into drains or watercourses or onto the ground.

# 6.3. Methods and material for containment and cleaning up

#### Methods for cleaning up

Absorb spillage with sand or other inert absorbent. Collect and place in suitable waste disposal containers and seal securely.

#### 6.4. Reference to other sections

#### Reference to other sections

For personal protection, see Section 8. For waste disposal, see Section 13.

#### SECTION 7: Handling and storage

# 7.1. Precautions for safe handling

#### Usage precautions

Use only in well-ventilated areas. Do not eat, drink or smoke when using this product. Wash hands and any other contaminated areas of the body with soap and water before leaving the work site.

#### 7.2. Conditions for safe storage, including any incompatibilities

#### Storage precautions

Store at temperatures not exceeding 38°C. Do not use containers made of the following materials: Rusty Steel. Tin. Aluminium. Mild steel. Copper.

#### 7.3. Specific end use(s)

#### Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

# SECTION 8: Exposure Controls/personal protection

#### 8.1. Control parameters

#### Occupational exposure limits

#### 8.2. Exposure controls

#### Eye/face protection

Wear eye protection.

#### Hand protection

Wear protective gloves made of the following material: Nitrile rubber. Polyethylene. Neoprene. Do NOT use Polyvinyl chloride (PVC). Rubber (natural, latex).

#### Hygiene measures

Wash hands thoroughly after handling.

#### Respiratory protection

If ventilation is inadequate, suitable respiratory protection must be worn.

#### **SECTION 9: Physical and Chemical Properties**

# 9.1. Information on basic physical and chemical properties

#### Appearance

Paste.

#### Colour

Yellow.

#### Odour

Sweetish.

#### Odour threshold

Not available.

#### pH

pH (concentrated solution): -3-5

#### Melting point

Not available.

#### Initial boiling point and range

Not available.

#### **Evaporation rate**

Not applicable.

#### Upper/lower flammability or explosive limits

Not available.

#### Vapour pressure

-0.1 mm Hg @ 20°C

#### Vapour density

Not available.

#### Solubility(ies)

Slightly soluble in water. Miscible with the following materials: Organic solvents.

#### Partition coefficient

Not available.

#### Auto-ignition temperature

Not available.

#### **Decomposition Temperature**

Not available.

#### **Explosive properties**

Not available.

#### Oxidising properties

Not available.

#### 9.2. Other information

# Other information

None.

#### SECTION 10: Stability and reactivity

#### 10.1. Reactivity

There are no known reactivity hazards associated with this product.

#### 10.2. Chemical stability

#### Stability

Stable at normal ambient temperatures and when used as recommended.

#### 10.3. Possibility of hazardous reactions

Under normal conditions of storage and use, no hazardous reactions will occur. Polymerises easily with evolution of heat.

#### 10.4. Conditions to avoid

There are no known conditions that are likely to result in a hazardous situation. Avoid exposure to high temperatures or direct sunlight.

#### 10.5. Incompatible materials

#### Materials to avoid

Oxidising agents. Avoid contact with the following materials: Mild Steel Rusty Steel Tin Aluminium.

#### 10.6. Hazardous decomposition products

Heating may generate the following products: Carbon.

#### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

#### Toxicological effects

No information available.

#### Acute toxicity - oral

#### ATE oral (mg/kg)

54,607.47274869

#### Acute toxicity - demal

#### ATE dermal (mg/kg)

110000.0

#### Acute toxicity - inhalation

#### ATE inhalation (vapours mg/l)

306.4351379

#### Inhalation

May cause respiratory system irritation.

#### Ingestion

May cause irritation.

#### Skin contact

Skin irritation should not occur when used as recommended.

#### SECTION 12: Ecological Information

#### **Ecotoxicity**

There are no data on the ecotoxicity of this product.

#### 12.1. Toxicity

Low

#### 12.2. Persistence and degradability

#### Persistence and degradability

The product is more than 80% biodegradable.

#### 12.3. Bioaccumulative potential

No data available on bioaccumulation.

#### Partition coefficient

Not available.

### 12.4. Mobility in soil

#### Mobility

Not considered mobile.

# 12.5. Results of PBT and vPvB assessment

This product does not contain any substances classified as PBT or vPvB.

#### 12.6. Other adverse effects

Not available.

# SECTION 13: Disposal considerations

# 13.1. Waste treatment methods

#### General information

Dispose of waste product or used containers in accordance with local regulations

#### Disposal methods

Dispose of waste product or used containers in accordance with local regulations

#### Waste class

08 04 09

#### SECTION 14: Transport information

#### General

The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

#### 14.1. UN number

Not applicable.

# 14.2. UN proper shipping name

Not applicable.

# 14.3. Transport hazard class(es)

No transport warning sign required.

#### 14.4. Packing group

Not applicable.

#### 14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

# 14.6. Special precautions for user

Not applicable.

# 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

# SECTION 15: Regulatory information

# 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### **EU** legislation

Regulation (EC) No 1907/2006 of the European Parliament and of the council of 18 December 2006 concerning the Registration, evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC, including amendments. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

# 15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

#### SECTION 16: Other information

SDS number

4806

Hazard statements in full

H242 Heating may cause a fire.

H301 Toxic if swallowed.

H302 Harmful if swallowed.

H312 Harmful in contact with skin.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H331 Toxic if inhaled.

H335 May cause respiratory irritation.

H373 May cause damage to organs through prolonged or repeated exposure.

H411 Toxic to aquatic life with long lasting effects.