


# PK7520



## Pressure switch with intuitive switch point setting

PK-400-SFG14-QSPKG/US/ /W



### 1 Sealing



#### Product characteristics

Output signal	switching signal
Measuring range	0...400 bar
Process connection	threaded connection G 1/4 external thread internal thread M5

#### Application

Application	for industrial applications
Media	liquids and gases
Medium temperature [°C]	-25...80
Pressure rating	600 bar
Min. bursting pressure	1600 bar
Type of pressure	relative pressure

#### Electrical data

Operating voltage [V]	9.6..32 DC
Current consumption [mA]	< 25
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes

#### Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2
------------------------------	------------------------------

# PK7520



## Pressure switch with intuitive switch point setting

PK-400-SFG14-QSPKG/US/ /W

Outputs		
Total number of outputs		2
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		2
Output function		normally open
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	500
Switching frequency DC	[Hz]	100
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Measuring range		0...400 bar      0...5800 psi
Set point SP		12...400 bar      174...5800 psi
Hysteresis		8 bar      116 psi
Accuracy / deviations		
Switch point accuracy [% of the final value]		< ± 2,5; (Setting accuracy)
Repeatability [% of the final value]		< ± 0,5; (with temperature fluctuations < 10 K)
Characteristics deviation [% of the final value]		< ± 1,5 (BFSL) / < ± 2,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)
Temperature drift per 10 K		< ± 0,5
Software / programming		
Adjustment of the switch point		setting rings
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67
Tests / approvals		
EMC		DIN EN 61000-6-2 DIN EN 61000-6-3
Shock resistance		DIN IEC 68-2-27      50 g (11 ms)
Vibration resistance		DIN IEC 68-2-6      20 g (10...2000 Hz)
MTTF	[years]	668
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request

# PK7520



## Pressure switch with intuitive switch point setting

PK-400-SFG14-QSPKG/US/ /W

### Mechanical data

Weight	[g]	94.5
Materials		PBT; PC; FKM; stainless steel (1.4404 / 316L)
Materials (wetted parts)		stainless steel (1.4404 / 316L); FKM
Min. pressure cycles		50 million
Tightening torque	[Nm]	25
Process connection		threaded connection G 1/4 external thread internal thread M5
Restrictor element integrated		no (can be retrofitted)

### Displays / operating elements

Display	switching status	2 x LED, yellow
With scale		yes

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Connector: 1 x M12



### Connection

