



Figure similar

SIMATIC S7-400, ANALOG INPUT SM 431, 8AI; 16 BIT  
RESOLUTION, U/I/THERMOEL., OPTIC. ISOLATED W. 1 POINT  
PER COMMON, DIAGN., ALARM, 20 MS MODULE UPDATE

Input current	
from load voltage L+ (without load), max.	400 mA
from backplane bus 5 V DC, max.	1 200 mA
Power losses	
Power loss, typ.	4.6 W
Hardware configuration	
Slots	
• Required slots	1
Analog inputs	
Number of analog inputs	8
• For voltage/current measurement	8
permissible input voltage for voltage input (destruction limit), max.	35 V; 35 V continuous, 75 V for max. 1 s (mark to space ratio 1:20)
permissible input current for current input (destruction limit), max.	32 mA
Input ranges	
• Voltage	Yes
• Current	Yes
• Thermocouple	Yes
• Resistance thermometer	No
• Resistance	No
Input ranges (rated values), voltages	
• 1 V to 5 V	Yes
• -1 V to +1 V	Yes

• -10 V to +10 V	Yes
• -100 mV to +100 mV	Yes
• -2.5 V to +2.5 V	Yes
• -20 mV to +20 mV	Yes
• -250 mV to +250 mV	Yes
• -5 V to +5 V	Yes
• -50 mV to +50 mV	Yes
• -500 mV to +500 mV	Yes
• -80 mV to +80 mV	Yes
<b>Input ranges (rated values), currents</b>	
• 0 to 20 mA	Yes
• -10 mA to +10 mA	Yes
• -20 mA to +20 mA	Yes
• -3.2 mA to +3.2 mA	Yes
• 4 mA to 20 mA	Yes
• Input resistance (4 mA to 20 mA)	50 Ω
• -5 mA to +5 mA	Yes
<b>Input ranges (rated values), thermoelements</b>	
• Type B	Yes
• Type E	Yes
• Type J	Yes
• Type K	Yes
• Type L	Yes
• Type N	Yes
• Type R	Yes
• Type S	Yes
• Type T	Yes
• Type U	Yes
<b>Thermocouple (TC)</b>	
Temperature compensation	
— internal temperature compensation	Yes
— external temperature compensation with compensations socket	Yes
— dynamic reference temperature value	Yes
<b>Characteristic linearization</b>	
• Parameterizable	Yes
— for thermocouples	Type B, E, J, K, L, N, R, S, T, U
<b>Cable length</b>	
• shielded, max.	200 m
<b>Analog value creation</b>	
Integration and conversion time/resolution per channel	

<ul style="list-style-type: none"> <li>• Resolution with overrange (bit including sign), max.</li> <li>• Integration time, parameterizable</li> <li>• Basic conversion time (ms)</li> <li>• Integration time (ms)</li> <li>• Basic conversion time, including integration time (ms)           <ul style="list-style-type: none"> <li>— additional conversion time for wire break monitoring and resistance measurement</li> </ul> </li> </ul>	16 bit  Yes  10 / 16,7 / 20 / 100  2,5 / 16,7 / 20 / 100  1 ms (module)
---	---

Encoder	
Connection of signal encoders	
<ul style="list-style-type: none"> <li>• for current measurement as 4-wire transducer</li> <li>• for resistance measurement with four-wire connection</li> </ul>	
Errors/accuracies	
Operational limit in overall temperature range	
<ul style="list-style-type: none"> <li>• Voltage, relative to input area, (+/-)</li> <li>• Current, relative to input area, (+/-)</li> </ul>	0.3 %  0.5 %
Basic error limit (operational limit at 25 °C)	
<ul style="list-style-type: none"> <li>• Voltage, relative to input area, (+/-)</li> <li>• Current, relative to input area, (+/-)</li> </ul>	0.1 %  0.17 %
Interrupts/diagnostics/status information	
Alarms	
<ul style="list-style-type: none"> <li>• Diagnostic alarm</li> <li>• Limit value alarm</li> </ul>	Yes; Parameterizable  Yes
Diagnostic messages	
<ul style="list-style-type: none"> <li>• Diagnostics</li> </ul>	Yes
Galvanic isolation	
Galvanic isolation analog inputs	
<ul style="list-style-type: none"> <li>• Galvanic isolation analog inputs</li> <li>• between the channels</li> </ul>	Yes; internal/external  Yes
Permissible potential difference	
between the inputs (UCM)	120 V AC
Isolation	
Isolation checked with	1500 V DC
Dimensions	
Width	25 mm
Height	290 mm
Depth	210 mm

**Weights**

Weight, approx.

650 g

**last modified:**

14.03.2015