

## SSSC clamp holder, positive, right-hand

for facing and longitudinal turning using SC indexable inserts

**ATORN**<sup>®</sup>

### Application

for face and longitudinal turning with SC indexable insert 90°

### Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, tip angle 90°, clearance angle 7°

### Advantage

- sturdy geometry for use in challenging conditions
- positive body geometry ensures low cutting forces
- excellent surface quality for medium infeed and finishing



<b>Art. no.</b>	<b>17834 202</b>
<b>ISO name</b>	SSSC R/L 1616 H09 IK G1/8
<b>Shaft height</b>	16 mm
<b>Shank width</b>	16 mm
<b>Length</b>	100 mm
<b>Length of head</b>	20 mm
<b>Programming size</b>	20 mm
<b>Suitable for indexable inserts</b>	SC.. 09T3..
<b>Tool design</b>	Left

### EAN-Code

4050293449815