Cartridge Fuse, 6.3x32 mm, 400-500 VAC, 400 VDC, 1-32 A, High Breaking Capacity up to 3500 A





# UL 248-14 · 500 VAC · 400 VDC · Time-Lag T

#### See below:

#### **Approvals and Compliances**

#### **Description**

- 6.3 x 32 mm fuses for primary protection
- 16 rated currents from 0.5 A to 32 A

## **Unique Selling Proposition**

- High rated voltages up to 500 VAC / 400 VDC
- High breaking capacity up to 3500 A
- Suitable for pulse-shaped continuous currents
- Useable for commercial cooking appliances according UL 197

#### **Applications**

- 3-phase applications
- DC applications
- Photovoltaic
- Frequency converter
- Power electronics
- Commercial cooking appliances

## References

Pigtail Type SHT 6.3x32 Pigtail

### Weblinks

pdf data sheet, html datasheet, General Product Information, Distributor-Stock-Check, Detailed request for product

Application Note Primary Protection in Equipmentwith further information on increased Pulse Strength and their test conditions according to international standards see Impulse Withstand Voltage

#### **Technical Data**

Rated Voltage	500 VAC, 63 - 400 VDC - 400 VDC
Rated current	0.5 - 32A
Breaking Capacity	3500 A - 20 kA
Characteristic	Time-Lag T
Mounting	Fuseholder / Clip
Admissible Ambient Air Temp.	-40 °C to 85 °C
Climatic Category	40/085/21 acc. to IEC 60068-1
Material: Tube	Ceramics
Material: Endcaps	Nickel-Plated Copper Alloy
Material: Axial Leads	Tin-Plated Copper
Unit Weight	2.84 g
Storage Conditions	0°C to 60°C, max. 70% r.h.
Product Marking	Type, Rated current, Rated Voltage, Characteristic, Breaking capacity, Approvals

## **Approvals and Compliances**

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

## **Approvals**

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: SHT 6.3x32

Approval Logo Certificates Certification Body Description

UL Approvals UL UR File Number: E41599

## **Product standards**

Product standards that are referenced

Organization	Design	Standard	Description
<b>(h</b> )	Designed according to	UL 248-14	Low voltage fuses - Part 14: Additional fuses

UL 248-14 Designed according to

> CSA22.2 No. 248.14 Designed according to Low-Voltage Fuses - Part 14: Supplemental Fuses

## **Application standards**

Application standards where the product can be used

Organization Standard Description Design

IEC/UL 62368-1 Designed for applications acc. Audio/video, information and communication technology equipment - Part <u>IEC</u> 1: Safety requirements


## Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
UK CA	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
RoHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
<b>©</b>	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

# Dimension [mm]






# **Pre-Arcing Time**

Rated Current In	1.0 x In min.	1.5 x In min.	2.1 x ln max.	2.75 x In min.	2.75 x In max.	4.0 x In min.	4.0 x In max.	10.0 x In min.	10.0 x In max.
0.5 A - 10 A	-	60 min	30 min	400 ms	80 s	95 ms	5 s	10 ms	300 ms
12.5 A - 32 A	4 h	-	30 min	400 ms	80 s	95 ms	5 s	10 ms	300 ms

## **Time-Current-Curves**



## **All Variants**

_	Order Number		M-11: 121 40 0 I	Power Dissipation	V-H D 4.0.1	D	D-tIV-It	Data d Vallana	Rated Current [A]
	Order Number	c <b>711</b> 'us	Melting I <sup>2</sup> t 10.0 I <sub>n</sub> typ. [A <sup>2</sup> s]	1.5 I <sub>n</sub> max. [mW]	Voltage Drop 1.0 I <sub>n</sub> max. [mV]	Breaking Capacity	Rated Voltage [VDC]	Rated Voltage [VAC]	nated Current [A]
	8020.5008	•	0.46	600	470	1)	400	500	0.5
	8020.5008.G	•	0.46	600	470	1)	400	500	0.5
	8020.5011	•	1.55	900	350	1)	400	500	1
	8020.5011.G	•	1.55	900	350	1)	400	500	1
	8020.5012	•	3.15	1000	300	1)	400	500	1.25
	8020.5012.G	•	3.15	1000	300	1)	400	500	1.25
	8020.5013	•	5.4	1100	200	1)	400	500	1.6
	8020.5013.G	•	5.4	1100	200	1)	400	500	1.6
	8020.5014	•	10.5	1200	180	1)	400	500	2
	8020.5014.G	•	10.5	1200	180	1)	400	500	2
	8020.5015	•	20	1300	160	1)	400	500	2.5
	8020.5015.G	•	20	1300	160	1)	400	500	2.5
	8020.5016	•	39	1400	150	1)	400	500	3.15
	8020.5016.G	•	39	1400	150	1)	400	500	3.15
	8020.5017	•	71.4	1500	140	1)	400	500	4
	8020.5017.G	•	71.4	1500	140	1)	400	500	4
	8020.5018	•	271	2200	135	2)	400	500	5
	8020.5018.G	•	271	2200	135	2)	400	500	5
	8020.5019	•	225	2200	110	2)	400	500	6.3
	8020.5019.G	•	225	2200	110	2)	400	500	6.3
	8020.5020	•	285	2600	110	2)	400	500	8
	8020.5020.G	•	285	2600	110	2)	400	500	8
	8020.5021	•	700	3000	110	3)	400	500	10
	8020.5021.G	•	700	3000	110	3)	400	500	10
	8020.5022	•	710	5000	120	4)	400	400	12.5
	8020.5022.G	•	710	5000	120	4)	400	400	12.5
	8020.5023	•	1400	5700	130	4)	400	400	16
	8020.5023.G	•	1400	5700	130	4)	400	400	16

Order Number	<b>71</b> 0	Melting I <sup>2</sup> t 10.0 I <sub>n</sub> typ. [A <sup>2</sup> s] <sub>c</sub>	Power Dissipation 1.5 I <sub>n</sub> max. [mW]	Voltage Drop 1.0 I <sub>n</sub> max. [mV]	Breaking Capacity	Rated Voltage [VDC]	Rated Voltage [VAC]	Rated Current [A]
8020.5024	•	4000	6000	100	5)	63	400	20
8020.5024.G	•	4000	6000	100	5)	63	400	20
8020.5025	•	5400	8000	100	5)	63	400	25
8020.5025.G	•	5400	8000	100	5)	63	400	25
8020.5026	•	8750	10500	110	5)	63	400	32
8020.5026.G	•	8750	10500	110	5)	63	400	32

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

1) 1500 A @ 500 VAC,  $\cos \varphi = 0.99 - 1$ 

1500 A @ 250 VAC,  $\cos \phi = 0.7 - 0.8$ 

10 kA @ 125 VAC,  $\cos\phi$  = 0.7 - 0.8

1500 A @ 400 VDC

20 kA @ 63 VDC

2) 1500 A @ 500 VAC,  $\cos \varphi = 0.99 - 1$ 

3500 A @ 250 VAC,  $\cos \phi = 0.7$  - 0.8

10 kA @ 125 VAC,  $\cos \phi = 0.7$  - 0.8

1000 A @ 400 VDC

20 kA @ 63 VDC

3) 1500 A @ 500 VAC,  $\cos \varphi = 0.99 - 1$ 

1500 A @ 250 VAC,  $\cos\phi$  = 0.7 - 0.8

10 kA @ 125 VAC,  $\cos \phi = 0.7 - 0.8$ 

1000 A @ 400 VDC

20 kA @ 63 VDC

4) 1500 A @ 400 VAC,  $\cos \varphi = 0.99 - 1$ 

1000 A @ 250 VAC,  $\cos \phi = 0.7$  - 0.8

10 kA @ 125 VAC,  $\cos\,\phi$  = 0.7 - 0.8

1000 A @ 400 VDC

20 kA @ 63 VDC

5) 1500 A @ 400 VAC,  $\cos \phi = 0.99$  - 1

1000 A @ 250 VAC,  $\cos \phi = 0.7$  - 0.8

10 kA @ 125 VAC,  $\cos \phi = 0.7 - 0.8$ 

20 kA @ 63 VDC

**Packaging Unit** 

xxxx.xxxx xxxx.xxxx.G Small Box Pack (10 pcs.) Bulk (1000 pcs.)