

## Shrink-fit chuck, 3 degrees

Long, slim design

**ATORN**<sup>®</sup>

### Application

For clamping cutters and drills with straight shanks in h6 tolerance. Suitable for heavy-duty machining and all high-power applications. Suitable for inductive, contact and hot air shrinking devices.



### Version

- guaranteed maximum concentricity 0.003 mm
- shrink grip and shrink release of HM and HSS tools
- hardness 52 + 2 HRC
- maximum coolant pressure 80 bar
- Glass bead blasted

### Advantage

- Slimline design, extremely low interference contour
- High transmittable torques
- High positioning and repeat accuracy
- Ideal for high rotation speeds

<b>Art. no.</b>	<b>23427 358</b>
<b>Clamping diameter</b>	10 mm
<b>Tapered diameter</b>	16 mm
<b>Outer diameter</b>	28 mm
<b>Projecting length</b>	200 mm
<b>Max. clamp in depth</b>	41 mm
<b>Suitable for thread</b>	M8 x 1
<b>Width across flats</b>	3 mm
<b>Max. adjustment travel</b>	10 mm
<b>Balancing quality</b>	G 2.5 at 25 rpm

### EAN-Code

405029344033 1