

TWS LED Light Module (Steady Light)



RND 430-00079 (24V)
RND 430-00082 (240V)

RND 430-00078 (24V)

RND 430-00080 (24V)
RND 430-00083 (240V)

RND 430-00081 (24V)
RND 430-00084 (240V)

Modulo luminoso a led.

Led luminous module.
Module lumineux à LED
LED-Lichtmodul
Módulo de luz LED

CUPOLA DOME DOME HAUBE CÚPULA	PC								
GHIERA RING BAGUE RING CONTERA	PC								
GRUPPO OTTICO LUMINOUS SOURCE SOURCE LUMINEUSE LICHTQUELLE FUENTE DE LUZ	N°12 LED								
COLORI DISPONIBILI AVAILABLE COLOURS COULEURS DISPONIBLES VERFÜGBARE FARBEN COLORES DISPONIBLES									
TENSIONE DI ALIMENTAZIONE VOLTAGE TENSION SPANNUNG TENSIÓN	24 Vdc/Vac - 240Vac								
SERVIZIO OPERATION FONCTIONNEMENT BETRIEBSART FUNCIONAMIENTO	∞								
CORRENTE NOMINALE CURRENT CONSUMPTION CONSOMMATION DE COURANT STROMAUFNAHME CONSUMO DE CORRIENTE	<table border="1"> <thead> <tr> <th></th> <th>24 Vdc</th> <th>24 Vac</th> <th>240Vac</th> </tr> </thead> <tbody> <tr> <th>mA</th> <td>65</td> <td>85</td> <td>35</td> </tr> </tbody> </table>		24 Vdc	24 Vac	240Vac	mA	65	85	35
	24 Vdc	24 Vac	240Vac						
mA	65	85	35						
RESA LUMINOSA LIGHT OUTPUT RENDEMENT LUMINEUX LICHT LEISTUNG SALIDA DE LUZ									
MODALITA' LUCE LIGHT EFFECT EFFET LUMINEUX LICHTEFFEKT EFECTO LUMINOSO	Fissa Steady Fixe Dauerlicht Luz fija								
GRADO IP IP RATING DEGRE IP SCHUTZART GRADO IP	IP66								

TWS LED Light Module (Steady Light)



TEMPERATURA DI FUNZIONAMENTO

OPERATING TEMPERATURE
TEMPERATURE DE SERVICE BETRIEBSTEMPERATUR
TEMPERATURA DE FUNCIONAMIENTO

-30°C+50°C

VIBRAZIONI

VIBRATIONS
VIBRATIONS
VIBRATIONEN
VIBRACIONES

INDUSTRIAL CEI 60068-2-6 SINE

CERTIFICAZIONI, OMOLOGAZIONI

CERTIFICATIONS, APPROVALS CERTIFICACIONES,
HOMOLOGATIONS PRODUKTZERTIFIKATE,
ZULASSUNGEN CERTIFICADOS, HOMOLOGACIONES

CE, UKCA

FISSAGGIO

MOUNTING
FIXATION
FIXIERUNG
FIJACIÓN

Tramite ghiera

Ring
Bague
Ring
Contera

DISEGNO

TECHNICAL DRAWING
DESSIN
TECHNISCHE ZEICHNUNG
DIBUJO TECNICO

