

ESD shelf trolley with 4 load areas

Load area sizes 850 x 500 and 1000 x 600 mm

fetra
Transportgeräte

Application:

For transporting non-stacking goods and materials, for continuous use in industrial applications. Electrically conductive design.

Version:

- Steel tube and profile steel welded, bolted construction
- Shelves made of electrically conductive wooden plate in accordance with DIN 68765, light grey.
- 1 fixed insert shelf

Advantage:

- Reliable dissipation of electric charges thanks to continuously conductive structure
- Robust design and high load capacity ensure a long service life even when used for high industrial loads
- Multiple load areas provide ample storage space for non-stacking goods and crates
- FETRA plug-and-screw design allows trolleys and accessories to be altered easily
- Large high-quality rollers for good running properties



Art. no.	50268 722
Load-carrying capacity	500 kg
Load-carrying capacity of loading surfaces	50 kg
Colour	Slate grey RAL 7015
Material of loading surface	Wood, electroconductive
Number of loading surfaces	4
Loading surface size	850 x 500 mm
Loading surface length	850 mm
Loading-surface width	500 mm
Length	1019 mm
Width	509 mm
Height	1511 mm
Length x width x height	1019 x 509 x 1511 mm
Surface	Powder-coated
Loading-surface height	235 mm
Loading-surface height 2	635 mm
Loading-surface height 3	1035 mm
Loading-surface height 4	1435 mm
Made in	Germany
EN standard	1757-3
With wheel lock	Yes
Wheel diameter	160 mm
Material of wheel	TPE-ESD
Wheel width	40 mm
Total stop optional	Yes
Number of fixed rollers	2
Number of steering rollers	2

EAN-Code

4017976092003