



NCP1681: Totem Pole Continuous Conduction Mode (CCM) / Multi-mode (CrM-CCM) Power Factor Correction Controller



[Request Datasheet](#)



[Product Overview](#)

[» View Material Composition](#)

[» Product Change Notification](#)

[☆ Mark as Favorite](#)

The NCP1681 is a PFC controller IC designed to drive the bridgeless totem-pole PFC topology. The bridgeless totem-pole PFC is a power factor correction architecture that consists of a fast switching leg driven at the PWM switching frequency and a second leg that operates at the AC line frequency. This topology eliminates the diode bridge present at the input of a conventional PFC circuit, allowing significant improvement in the power stage efficiency. The controller can be configured to operate in Continuous Conduction Mode (CCM) or Multi-Mode (CrM-CCM) operation.

Features

- Totem Pole PFC Topology Eliminates Input Diode Bridge
- Continuous Conduction Mode (CCM) Operation At High Power Level
- Optional Multi-mode Operation With CCM at High Power & CrM at Medium Power Level
- Frequency Foldback in DCM With 25 kHz Minimum Frequency
- Skip Mode in Very Light Load Condition
- Novel Current Sense Scheme
- Digital Voltage Loop Compensation
- AC Line Monitoring Circuit & AC Phase Detection
- Near Unity Power Factor in All Operating Modes
- PFC OK Indicator

Benefits

- Enables High Efficiency & Compact Design
- Optimized Efficiency For High Power Design
- Optimized Performance Across Power Levels
- Prevents Operation in Audible Range
- Complies with Energy Efficiency Regulatory Standards
- Cycle-by-Cycle Current Limit Without Hall Effect Sensor
- Simplifies Design & Reduces External Components
- Simplifies Design & Reduces External Components
- Complies with Energy Efficiency Regulatory Standards
- Allows Communication with Downstream Converter to Optimize System Performance





- Networking Power
- Gaming Console Power Supplies
- UHD TV Power Supplies
- Industrial Power Supplies

Technical Documentation & Design Resources

[White Papers \(1\)](#)

[Videos \(1\)](#)

[Package Drawings \(1\)](#)

▼ [Availability & Samples](#)

▶ [Specifications](#)

Product	Status	Compliance	Description	Package		
				Type	Case Outline	Type
NCP1681AAD2R2G	Active <small>NEW</small>	Pb-free ----- Halide free	NCP1681, Totem Pole Continuous Conduction Mode (CCM) Power Factor Correction Controller	SOIC20 NB LESS PIN 17 & 19	751EZ	1
NCP1681ABD2R2G	Active <small>NEW</small>	Pb-free ----- Halide free	NCP1681, Totem Pole Continuous Conduction Mode (CCM) Power Factor Correction Controller	SOIC20 NB LESS PIN 17 & 19	751EZ	1
NCP1681BAD2R2G	Active <small>NEW</small>	Pb-free ----- Halide free	NCP1681, Totem Pole Multi-mode (CrM-CCM) Power Factor Correction Controller	SOIC20 NB LESS PIN 17 & 19	751EZ	1





[Clear List](#)

Support

[Technical Documentation](#)


[Design Resources & Documents](#)

[Technical Support](#)

[Sales Support](#)

Featured Video

[Power Factor Improvement Methods with Their Advantages & Disadvantages](#)



[More Videos ...](#)

About onsemi

[Ecosystem Partners](#)

[Leadership](#)

[Quality and Reliability](#)

[Intellectual Property](#)

[Corporate Fact Sheet](#)

[Locations](#)

Investor Relations

[Events](#)

[Governance](#)

[Financials](#)

[Stock Info](#)

[News](#)

[Resources](#)





[In The News](#)

[Blog](#)

[COVID-19 Business Updates](#)

[Image Library](#)

[Media Contacts](#)

[Experienced Careers](#)

[Early Careers](#)

[Internships](#)

[Who We Are](#)

[Where We Are](#)

[Career Benefits](#)



Connect with us



Language ▾

[Do Not Sell My Personal Information](#) | [Terms of Sale](#) | [Accessibility](#) |
[Cookie Policy](#) | [Privacy](#) | [Terms of Use](#) | [Subscribe](#) | [Site Map](#)

© Copyright 1999-2021 Semiconductor Components Industries, LLC

