

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 630
Brand	AMF
Manufacturer Part Number	85787
DIN	787
Thread dimension	M16
Groove width	18 mm
Length excluding head	80 mm
Outer diameter	17.7 mm
Thread length	55 mm
Length of head	28 mm
Head height	10 mm
Gross Weight	0.288 kg
Product Group	260

EAN

4020772085780