

Electronic micrometer

ABS Digimatic QuickMike

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- carbide-tipped measuring faces
- IP65
- ABS function
- ON/OFF
- Non-rotating spindle
- HOLD (measured value storage)
- Origin (measurement presetting)

Advantage:

- Faster movement
- IP65

Delivery:

Includes box, set standard (25 mm or more), battery



Art. no.	32017 647
Brand	MITUTOYO
Manufacturer Part Number	293-679-20
Display	Digital
Min./max. length measuring range in inches	3-4.2 in
Digit increment	0.00005 in
Measuring surface diameter	6.35 mm
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	No
Digit height	10 mm
Functions	ABS function, Hold-function (AE lock), On/Off, Preset function, Origin (Dimension preset), Absolute function
Min./max. measurement force	5-12 N
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Measuring spindle increments	10 mm
Calibration Group	D
Gross Weight	1.190 kg
Product Group	3MA

EAN

4946368736761