

4-Kbit (512 \times 8) Serial (I²C) F-RAM

Features

- 4-Kbit ferroelectric random access memory (F-RAM) logically organized as 512 x 8
 - ☐ High-endurance 100 trillion (10¹⁴) read/writes
 - □ 151-year data retention (See the Data Retention and Endurance table)
 - ¬ NoDelay™ writes
 - □ Advanced high-reliability ferroelectric process
- Fast 2-wire Serial interface (I²C)
 - □ Up to 1-MHz frequency
 - □ Direct hardware replacement for serial (I²C) EEPROM
 - □ Supports legacy timings for 100 kHz and 400 kHz
- Low power consumption
 - □ 100 µA active current at 100 kHz
 - □ 4 µA (typ) standby current
- Voltage operation: V_{DD} = 4.5 V to 5.5 V
- AEC-Q100 grade 3 qualified
- Industrial temperature: -40 °C to +85 °C
- 8-pin small outline integrated circuit (SOIC) package
- Restriction of hazardous substances (RoHS) compliant

Functional Description

The FM24C04B is a 4-Kbit nonvolatile memory employing an advanced ferroelectric process. A ferroelectric random access memory or F-RAM is nonvolatile and performs reads and writes similar to a RAM. It provides reliable data retention for 151 years while eliminating the complexities, overhead, and system-level reliability problems caused by EEPROM and other nonvolatile memories.


Unlike EEPROM, the FM24C04B performs write operations at bus speed. No write delays are incurred. Data is written to the memory array immediately after each byte is successfully transferred to the device. The next bus cycle can commence without the need for data polling. In addition, the product offers substantial write endurance compared with other nonvolatile memories. Also, F-RAM exhibits much lower power during writes than EEPROM since write operations do not require an internally elevated power supply voltage for write circuits. The FM24C04B is capable of supporting 10¹⁴ read/write cycles, or 100 million times more write cycles than EEPROM.

These capabilities make the FM24C04B ideal for nonvolatile memory applications, requiring frequent or rapid writes. Examples range from data logging, where the number of write cycles may be critical, to demanding industrial controls where the long write time of EEPROM can cause data loss. The combination of features allows more frequent data writing with less overhead for the system.

The FM24C04B provides substantial benefits to users of serial ($\rm I^2C$) EEPROM as a hardware drop-in replacement. The device specifications are AEC-Q100 qualified and guaranteed over an industrial temperature range of –40 °C to +85 °C.

For a complete list of related documentation, click here.

Logic Block Diagram





Contents


Pinout	3
Pin Definitions	3
Functional Overview	
Memory Architecture	4
I2C Interface	
STOP Condition (P)	4
START Condition (S)	
Data/Address Transfer	
Acknowledge/No-acknowledge	
Slave Device Address	
Addressing Overview (Word Address)	
Data Transfer	
Memory Operation	6
Write Operation	
Read Operation	
Endurance	8
Maximum Ratings	
Operating Range	
DC Electrical Characteristics	
Data Retention and Endurance	10

Capacitance	10
Thermal Resistance	
AC Test Loads and Waveforms	10
AC Test Conditions	10
AC Switching Characteristics	11
Power Cycle Timing	12
Ordering Information	13
Ordering Code Definitions	13
Package Diagram	
Acronyms	15
Document Conventions	15
Units of Measure	15
Document History Page	16
Sales, Solutions, and Legal Information	18
Worldwide Sales and Design Support	18
Products	18
PSoC® Solutions	18
Cypress Developer Community	18
Technical Support	18



Pinout

Figure 1. 8-pin SOIC pinout



Pin Definitions

Pin Name	I/O Type	Description
A2-A1	Input	Device Select Address 2–1 . These pins are used to select one of up to 4 devices of the same type on the same I ² C bus. To select the device, the address value on the three pins must match the corresponding bits contained in the slave address. The address pins are pulled down internally.
SDA	Input/Output	Serial Data/Address . This is a bi-directional pin for the I ² C interface. It is open-drain and is intended to be wire-AND'd with other devices on the I ² C bus. The input buffer incorporates a Schmitt trigger for noise immunity and the output driver includes slope control for falling edges. An external pull-up resistor is required.
SCL	Input	Serial Clock . The serial clock pin for the I ² C interface. Data is clocked out of the device on the falling edge, and into the device on the rising edge. The SCL input also incorporates a Schmitt trigger input for noise immunity.
WP	Input	Write Protect . When tied to V_{DD} , addresses in the entire memory map will be write-protected. When WP is connected to ground, all addresses are write enabled. This pin is pulled down internally.
V _{SS}	Power supply	Ground for the device. Must be connected to the ground of the system.
V _{DD}	Power supply	Power supply input to the device.



Functional Overview

The FM24C04B is a serial F-RAM memory. The memory array is logically organized as 512 × 8 bits and is accessed using an industry-standard $\rm I^2C$ interface. The functional operation of the F-RAM is similar to serial ($\rm I^2C$) EEPROM. The major difference between the FM24C04B and a serial ($\rm I^2C$) EEPROM with the same pinout is the F-RAM's superior write performance, high endurance, and low power consumption.

Memory Architecture

When accessing the FM24C04B, the user addresses 512 locations of eight data bits each. These eight data bits are shifted in or out serially. The addresses are accessed using the $\rm I^2C$ protocol, which includes a slave address (to distinguish other non-memory devices), a page address bit, and a word address. The word address consists of 8-bits that specify one of the 256 addresses. The page address is 1-bit and so there are 2 pages of 256 locations. The complete address of 9-bits specifies each byte address uniquely.

The access time for the memory operation is essentially zero, beyond the time needed for the serial protocol. That is, the memory is read or written at the speed of the I²C bus. Unlike a serial (I²C) EEPROM, it is not necessary to poll the device for a ready condition because writes occur at bus speed. By the time a new bus transaction can be shifted into the device, a write

operation is complete. This is explained in more detail in the interface section.

Note that the FM24C04B contains no power management circuits other than a simple internal power-on reset. It is the user's responsibility to ensure that V_{DD} is within data sheet tolerances to prevent incorrect operation.

I²C Interface

The FM24C04B employs a bi-directional I^2C bus protocol using few pins or board space. Figure 2 illustrates a typical system configuration using the FM24C04B in a microcontroller-based system. The industry standard I^2C bus is familiar to many users but is described in this section.

By convention, any device that is sending data onto the bus is the transmitter while the target device for this data is the receiver. The device that is controlling the bus is the master. The master is responsible for generating the clock signal for all operations. Any device on the bus that is being controlled is a slave. The FM24C04B is always a slave device.

The bus protocol is controlled by transition states in the SDA and SCL signals. There are four conditions including START, STOP, data bit, or acknowledge. Figure 3 on page 5 and Figure 4 on page 5 illustrates the signal conditions that specify the four states. Detailed timing diagrams are shown in the electrical specifications section.




Figure 2. System Configuration using Serial (I²C) nvSRAM

STOP Condition (P)

A STOP condition is indicated when the bus master drives SDA from LOW to HIGH while the SCL signal is HIGH. All operations using the FM24C04B should end with a STOP condition. If an operation is in progress when a STOP is asserted, the operation will be aborted. The master must have control of SDA in order to assert a STOP condition.

START Condition (S)

A START condition is indicated when the bus master drives SDA from HIGH to LOW while the SCL signal is HIGH. All commands should be preceded by a START condition. An operation in progress can be aborted by asserting a START condition at any time. Aborting an operation using the START condition will ready the FM24C04B for a new operation.

If during operation the power supply drops below the specified V_{DD} minimum, the system should issue a START condition prior to performing another operation.



Figure 3. START and STOP Conditions





Figure 4. Data Transfer on the I²C Bus



Data/Address Transfer

All data transfers (including addresses) take place while the SCL signal is HIGH. Except under the three conditions described above, the SDA signal should not change while SCL is HIGH.


Acknowledge/No-acknowledge

The acknowledge takes place after the 8th data bit has been transferred in any transaction. During this state the transmitter should release the SDA bus to allow the receiver to drive it. The receiver drives the SDA signal LOW to acknowledge receipt of the byte. If the receiver does not drive SDA LOW, the condition is a no-acknowledge and the operation is aborted.

The receiver would fail to acknowledge for two distinct reasons. First is that a byte transfer fails. In this case, the no-acknowledge ceases the current operation so that the device can be addressed again. This allows the last byte to be recovered in the event of a communication error.

Second and most common, the receiver does not acknowledge to deliberately end an operation. For example, during a read operation, the FM24C04B will continue to place data onto the bus as long as the receiver sends acknowledges (and clocks). When a read operation is complete and no more data is needed, the receiver must not acknowledge the last byte. If the receiver acknowledges the last byte, this will cause the FM24C04B to attempt to drive the bus on the next clock while the master is sending a new command such as STOP.

Figure 5. Acknowledge on the I²C Bus






Slave Device Address

The first byte that the FM24C04B expects after a START condition is the slave address. As shown in Figure 6, the slave address contains the device type or slave ID, the device select address bits, a page select bit, and a bit that specifies if the transaction is a read or a write.

Bits 7-4 are the device type (slave ID) and should be set to 1010b for the FM24C04B. These bits allow other function types to reside on the I 2 C bus within an identical address range. Bits 3-2 are the device select address bits. They must match the corresponding value on the external address pins to select the device. Up to four FM24C04B devices can reside on the same I 2 C bus by assigning a different address to each. Bit 1 is the page select bit. It specifies the 256-byte block of memory that is targeted for the current operation. Bit 0 is the read/write bit (R/W). R/W = '1' indicates a read operation and R/W = '0' indicates a write operation.

Figure 6. Memory Slave Device Address



Addressing Overview (Word Address)

After the FM24C04B (as receiver) acknowledges the slave address, the master can place the word address on the bus for a write operation. The word address is the lower 8-bits of the address to be combined with the 1-bit page select to specify exactly the byte to be written. The complete 9-bit address is latched internally. No word address occurs for a read operation. Reads always use the lower 8-bits that are held internally in the address latch and the 9th address bit is part of the slave address. Reads always begin at the address following the previous access. A random read address can be loaded by doing a write operation as explained below.

After transmission of each data byte, just prior to the acknowledge, the FM24C04B increments the internal address latch. This allows the next sequential byte to be accessed with no additional addressing. After the last address (1FFh) is reached, the address latch will roll over to 000h. There is no limit to the number of bytes that can be accessed with a single read or write operation.

Data Transfer

After the address bytes have been transmitted, data transfer between the bus master and the FM24C04B can begin. For a read operation the FM24C04B will place 8 data bits on the bus

then wait for an acknowledge from the master. If the acknowledge occurs, the FM24C04B will transfer the next sequential byte. If the acknowledge is not sent, the FM24C04B will end the read operation. For a write operation, the FM24C04B will accept 8 data bits from the master then send an acknowledge. All data transfer occurs MSB (most significant bit) first.

Memory Operation

The FM24C04B is designed to operate in a manner very similar to other I²C interface memory products. The major differences result from the higher performance write capability of F-RAM technology. These improvements result in some differences between the FM24C04B and a similar configuration EEPROM during writes. The complete operation for both writes and reads is explained below.

Write Operation

All writes begin with a slave address, then a word address. The bus master indicates a write operation by setting the LSB of the slave address (R/W bit) to a '0'. After addressing, the bus master sends each byte of data to the memory and the memory generates an acknowledge condition. Any number of sequential bytes may be written. If the end of the address range is reached internally, the address counter will wrap from 1FFh to 000h.

Unlike other nonvolatile memory technologies, there is no effective write delay with F-RAM. Since the read and write access times of the underlying memory are the same, the user experiences no delay through the bus. The entire memory cycle occurs in less time than a single bus clock. Therefore, any operation including read or write can occur immediately following a write. Acknowledge polling, a technique used with EEPROMs to determine if a write is complete is unnecessary and will always return a ready condition.

Internally, an actual memory write occurs after the 8th data bit is transferred. It will be complete before the acknowledge is sent. Therefore, if the user desires to abort a write without altering the memory contents, this should be done using START or STOP condition prior to the 8th data bit. The FM24C04B uses no page buffering.

The memory array can be write-protected using the WP pin. Setting the WP pin to a HIGH condition (V_{DD}) will write-protect all addresses. The FM24C04B will not acknowledge data bytes that are written to protected addresses. In addition, the address counter will not increment if writes are attempted to these addresses. Setting WP to a LOW state (V_{SS}) will disable the write protect. WP is pulled down internally.

Figure 7 and Figure 8 on page 7 below illustrate a single-byte and multiple-byte write cycles.







Figure 8. Multi-Byte Write



Read Operation

There are two basic types of read operations. They are current address read and selective address read. In a current address read, the FM24C04B uses the internal address latch to supply the lower 8 address bits. In a selective read, the user performs a procedure to set these lower address bits to a specific value.

Current Address & Sequential Read

As mentioned above the FM24C04B uses an internal latch to supply the lower 8 address bits for a read operation. A current address read uses the existing value in the address latch as a starting place for the read operation. The system reads from the address immediately following that of the last operation.

To perform a current address read, the bus master supplies a slave address with the LSB set to a '1'. This indicates that a read operation is requested. The page select bit in the slave address specifies the block of memory that is used for the read operation. After receiving the complete slave address, the FM24C04B will begin shifting out data from the current address on the next clock. The current address is the bit from the slave address combined with the 8-bits that were in the internal address latch.

Beginning with the current address, the bus master can read any number of bytes. Thus, a sequential read is simply a current address read with multiple byte transfers. After each byte the internal address counter will be incremented.

Note Each time the bus master acknowledges a byte, this indicates that the FM24C04B should read out the next sequential byte.

There are four ways to properly terminate a read operation. Failing to properly terminate the read will most likely create a bus contention as the FM24C04B attempts to read out additional data onto the bus. The four valid methods are:

- The bus master issues a no-acknowledge in the 9th clock cycle and a STOP in the 10th clock cycle. This is illustrated in the diagrams below. This is preferred.
- 2. The bus master issues a no-acknowledge in the 9th clock cycle and a START in the 10th.
- 3. The bus master issues a STOP in the 9th clock cycle.
- 4. The bus master issues a START in the 9th clock cycle.

If the internal address reaches 1FFh, it will wrap around to 000h on the next read cycle. Figure 9 and Figure 10 below show the proper operation for current address reads.

Figure 9. Current Address Read





Figure 10. Sequential Read






Selective (Random) Read

There is a simple technique that allows a user to select a random address location as the starting point for a read operation. This involves using the first two bytes of a write operation to set the internal address followed by subsequent read operations.

To perform a selective read, the bus master sends out the slave address with the LSB (R/W) set to 0. This specifies a write

operation. According to the write protocol, the bus master then sends the word address byte that is loaded into the internal address latch. After the FM24C04B acknowledges the word address, the bus master issues a START condition. This simultaneously aborts the write operation and allows the read command to be issued with the slave address LSB set to a '1'. The operation is now a current address read.

Figure 11. Selective (Random) Read



Endurance

The FM24C04B internally operates with a read and restore mechanism. Therefore, endurance cycles are applied for each read or write cycle. The memory architecture is based on an array of rows and columns. Each read or write access causes an endurance cycle for an entire row. In the FM24C04B, a row is

64 bits wide. Every 8-byte boundary marks the beginning of a new row. Endurance can be optimized by ensuring frequently accessed data is located in different rows. Regardless, F-RAM read and write endurance is effectively unlimited at the 1-MHz I²C speed. Even at 3000 accesses per second to the same row, 10 years time will elapse before 1 trillion endurance cycles occur.



Maximum Ratings

Exceeding maximum ratings may shorten the useful life of the device. These user guidelines are not tested.

de vices a vice galacimico di caricatica.
Storage temperature55 °C to +125 °C
Maximum accumulated storage time At 125 °C ambient temperature
Ambient temperature with power applied–55 °C to +125 °C
Supply voltage on V_{DD} relative to V_{SS} –1.0 V to +7.0 V
Input voltage -1.0 V to + 7.0 V and $\text{V}_{\text{IN}} < \text{V}_{\text{DD}}$ + 1.0 V
DC voltage applied to outputs in High-Z state0.5 V to V_{DD} + 0.5 V
Transient voltage (< 20 ns) on any pin to ground potential2.0 V to V _{DD} + 2.0 V

Package power
dissipation capability (T _A = 25 °C)1.0 W
Surface mount lead
soldering temperature (10 seconds)+260°C
Electrostatic Discharge Voltage [1]
Human Body Model (AEC-Q100-002 Rev. E) 2 kV
Charged Device Model (AEC-Q100-011 Rev. B)500 V
Latch-up current> 140 mA
* Exception: The "V $_{\rm IN}$ < V $_{\rm DD}$ + 1.0 V" restriction does not apply to the SCL and SDA inputs.

Operating Range

Range	Ambient Temperature (T _A)	V _{DD}
Industrial	–40 °C to +85 °C	4.5 V to 5.5 V

DC Electrical Characteristics

Over the Operating Range

Parameter	Description	Test Cond	itions	Min	Typ [2]	Max	Unit
V_{DD}	Power supply			4.5	5.0	5.5	V
I _{DD}	Average V _{DD} current	SCL toggling	f _{SCL} = 100 kHz	_	-	100	μΑ
		between V _{DD} – 0.3 V and V _{SS} ,	f _{SCL} = 400 kHz	_	_	200	μΑ
		other inputs V_{SS} or $V_{DD} = 0.3 \text{ V}$.	f _{SCL} = 1 MHz	_	-	400	μА
I _{SB}	Standby current	$SCL = SDA = V_{DD}$. All or V_{DD} . Stop commar		_	4	10	μА
I _{LI}	Input leakage current (Except WP and A2–A1)	$V_{SS} \le V_{IN} \le V_{DD}$		-1	-	+1	μА
	Input leakage current (for WP and A2–A1)	$V_{SS} \le V_{IN} \le V_{DD}$		-1	_	+100	μА
I _{LO}	Output leakage current	$V_{SS} \le V_{IN} \le V_{DD}$		-1	-	+1	μΑ
V _{IH}	Input HIGH voltage			$0.7 \times V_{DD}$	-	V _{DD} + 0.3	V
V_{IL}	Input LOW voltage			- 0.3	_	$0.3 \times V_{DD}$	V
V_{OL}	Output LOW voltage	$I_{OL} = 3 \text{ mA}$		_	-	0.4	V
R _{in} ^[3]	Input resistance (WP, A2-A1)	For V _{IN} = V _{IL (Max)}		40	_	-	kΩ
		For V _{IN} = V _{IH (Min)}		1	-	-	МΩ
V _{HYS} ^[4]	Input Hysteresis			$0.05 \times V_{DD}$	_	_	V

Notes

Electrostatic Discharge voltages specified in the datasheet are the JEDEC standard limits used for qualifying the device. To know the maximum value device passes for, please refer to the device qualification report available on the website.
 Typical values are at 25 °C, V_{DD} = V_{DD} (typ). Not 100% tested.
 The input pull-down circuit is strong (40 kΩ) when the input voltage is below V_{IL} and weak (1 MΩ) when the input voltage is above V_{IH}.
 These parameters are guaranteed by design and are not tested.



Data Retention and Endurance

Parameter	Description	Test condition	Min	Max	Unit
T_{DR}	Data retention	T _A = 85 °C	10	_	Years
		T _A = 75 °C	38	_	
		T _A = 65 °C	151	_	
NV _C	Endurance	Over operating temperature	10 ¹⁴	_	Cycles

Capacitance


Parameter [5]	Description	Test Conditions	Max	Unit
Co	Output pin capacitance (SDA)	$T_A = 25 ^{\circ}\text{C}, f = 1 \text{MHz}, V_{DD} = V_{DD}(\text{typ})$	8	pF
C _I	Input pin capacitance		6	pF

Thermal Resistance

Parameter [5]	Description	Test Conditions	8-pin SOIC	Unit
Θ_{JA}	,	Test conditions follow standard test methods and procedures for measuring thermal impedance, per	147	°C/W
$\Theta_{\sf JC}$	Thermal resistance (junction to case)	EIA/JESD51.	47	°C/W

AC Test Loads and Waveforms

Figure 12. AC Test Loads and Waveforms



AC Test Conditions

Input pulse levels	10% and 90% of V _{DD}
Input rise and fall times	10 ns
Input and output timing reference leve	ls0.5 x V _{DD}
Output load capacitance	100 pF

Note

Document Number: 001-84446 Rev. *L

^{5.} These parameters are guaranteed by design and are not tested.




AC Switching Characteristics

Over the Operating Range

Param	eter ^[6]								
Cypress Parameter	Alt. Parameter	Description		Max	Min	Max	Min	Max	Unit
f _{SCL} ^[7]		SCL clock frequency	_	0.1	-	0.4	_	1.0	MHz
t _{SU; STA}		Start condition setup for repeated Start	4.7	_	0.6	_	0.25	_	μs
t _{HD;STA}		Start condition hold time	4.0	_	0.6	_	0.25	_	μs
t_{LOW}		Clock LOW period	4.7	_	1.3	_	0.6	_	μs
t _{HIGH}		Clock HIGH period	4.0	_	0.6	_	0.4	_	μs
t _{SU;DAT}	t _{SU;DATA}	Data in setup	250	_	100	_	100	_	ns
t _{HD;DAT}	t _{HD;DATA}	Data in hold	0	_	0	_	0	_	ns
t _{DH}		Data output hold (from SCL @ V _{IL})	0	_	0	-	0	-	ns
t _R ^[8]	t _r	Input rise time	_	1000	_	300	-	300	ns
t _F ^[8]	t _f	Input fall time	_	300	-	300	-	100	ns
t _{SU;STO}		STOP condition setup	4.0	-	0.6	-	0.25	-	μs
t _{AA}	t _{VD;DATA}	SCL LOW to SDA Data Out Valid	_	3	_	0.9	-	0.55	μs
t _{BUF}		Bus free before new transmission	4.7	_	1.3	_	0.5	_	μs
t _{SP}		Noise suppression time constant on SCL, SDA	_	50	_	50	_	50	ns

Figure 13. Read Bus Timing Diagram



Notes

- Test conditions assume signal transition time of 10 ns or less, timing reference levels of $V_{DD}/2$, input pulse levels of 0 to $V_{DD}(typ)$, and output loading of the specified I_{OL} and load capacitance shown in Figure 12.

 The speed-related specifications are guaranteed characteristic points along a continuous curve of operation from DC to f_{SCL} (max).
- 8. These parameters are guaranteed by design and are not tested.




Power Cycle Timing

Over the Operating Range

Parameter	Description	Min	Max	Unit
t _{PU}	Power-up V _{DD} (min) to first access (START condition)	1	-	ms
t _{PD}	Last access (STOP condition) to power-down (V _{DD} (min))	0	_	μs
t _{VR} ^[9, 10]	V _{DD} power-up ramp rate	30	_	μs/V
t _{VF} ^[9, 10]	V _{DD} power-down ramp rate	30	_	μs/V

Figure 15. Power Cycle Timing



Notes

^{9.} Slope measured at any point on the $\ensuremath{V_{DD}}$ waveform.

^{10.} Guaranteed by design.




Ordering Information

Ordering Code	Package Diagram	Package Type	Operating Range
FM24C04B-G	51-85066	8-pin SOIC	-40 °C to +85 °C
FM24C04B-GTR			

All these parts are Pb-free. Contact your local Cypress sales representative for availability of these parts.

Ordering Code Definitions








Package Diagram

Figure 16. 8-pin SOIC (150 Mils) Package Outline, 51-85066

- 1. DIMENSIONS IN INCHES[MM] $\frac{\text{MIN.}}{\text{MAX.}}$
- PIN 1 ID IS OPTIONAL,
 ROUND ON SINGLE LEADFRAME
 RECTANGULAR ON MATRIX LEADFRAME
- 3. REFERENCE JEDEC MS-012
- 4. PACKAGE WEIGHT 0.07gms







51-85066 *H



Acronyms

Acronym	Description		
ACK	Acknowledge		
AEC	Automotive Electronics Council		
CMOS	Complementary Metal Oxide Semiconductor		
EIA	Electronic Industries Alliance		
I ² C	Inter-Integrated Circuit		
I/O	Input/Output		
JEDEC	Joint Electron Devices Engineering Council		
LSB	Least Significant Bit		
MSB	Most Significant Bit		
NACK	No Acknowledge		
RoHS	Restriction of Hazardous Substances		
R/W	Read/Write		
SCL	Serial Clock Line		
SDA	Serial Data Access		
SOIC	Small Outline Integrated Circuit		
WP	Write Protect		

Document Conventions

Units of Measure

Symbol	Unit of Measure		
°C	degree Celsius		
Hz	hertz		
Kb	kilobit		
kHz	kilohertz		
kΩ	kilohm		
MHz	megahertz		
ΜΩ	megaohm		
μΑ	microampere		
μS	microsecond		
mA	milliampere		
ms	millisecond		
ns	nanosecond		
Ω	ohm		
%	percent		
pF	picofarad		
V	volt		
W	watt		



Document History Page

Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change
**	3902082	GVCH	02/25/2013	New spec.
*A	3924523	GVCH	03/07/2013	Updated Power Cycle Timing: Changed minimum value of t _{PU} parameter from 10 ms to 1 ms.
*B	3996669	GVCH	05/13/2013	Added Appendix A - Errata for FM24C04B.
*C	4045469	GVCH	06/30/2013	All errata items are fixed and the errata is removed.
*D	4283418	GVCH	02/19/2014	Converted to Cypress standard format. Changed endurance value from 10 ¹² to 10 ¹⁴ cycles. Updated Maximum Ratings: - Removed Moisture Sensitivity Level (MSL) Added junction temperature and latch up current. Updated DC Electrical Characteristics: Added Input leakage current (I _{LI}) for WP and A2-A1. Updated Data Retention and Endurance. Added Thermal Resistance. Removed Package Marking Scheme (top mark). Completing Sunset Review.
*E	4272607	GVCH	03/12/2014	Updated AC Switching Characteristics: Fixed typo (Replaced "ns" with " μ s" in "Unit" column for $t_{SU:STA}$, $t_{HD:STA}$, t_{LOW} t_{HIGH} , $t_{SU:STO}$, t_{AA} and t_{BUF} parameters).
*F	4343617	GVCH	04/21/2014	Updated DC Electrical Characteristics: Fixed typo (Replaced "C" with "V" in "Unit" column for V _{OL} parameter).
*G	4566147	GVCH	11/10/2014	Updated Functional Description: Added "For a complete list of related documentation, click here." at the end.
*H	4584924	GVCH	12/02/2014	Updated Features: Added "AEC-Q100 grade 3 qualified" information. Updated Functional Description: Added "AEC-Q100 grade 3 qualified" information.
*	4782742	GVCH	06/01/2015	Updated Ordering Information: Fixed Typo (Replaced "001-85066" with "51-85066" in "Package Diagram column). Updated Package Diagram: spec 51-85066 – Changed revision from *F to *G. Updated to new template.
*J	4874535	ZSK / PSR	08/06/2015	Updated Maximum Ratings: Removed "Maximum junction temperature". Added "Maximum accumulated storage time". Added "Ambient temperature with power applied".
*K	5606370	GVCH	01/27/2017	Updated Maximum Ratings: Updated Electrostatic Discharge Voltage (in compliance with AEC-Q100 standard): Changed value of "Human Body Model" from 3 kV to 2 kV. Changed value of "Charged Device Model" from 1.25 kV to 500 V. Removed "Machine Model" related information. Updated Package Diagram: spec 51-85066 – Changed revision from *G to *H. Updated to new template. Completing Sunset Review.



Document History Page (continued)

Document Title: FM24C04B, 4-Kbit (512 × 8) Serial (I ² C) F-RAM Document Number: 001-84446				
Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change
*L	5700082	GVCH	04/19/2017	Updated Maximum Ratings: Added Note 1 and referred the same note in "Electrostatic Discharge Voltage". Updated to new template.



Sales, Solutions, and Legal Information

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at Cypress Locations.

Products

ARM® Cortex® Microcontrollers

Automotive

Clocks & Buffers

Interface

Internet of Things

Memory

Cypress.com/automotive

cypress.com/clocks

cypress.com/interface

cypress.com/iot

cypress.com/memory

Microcontrollers cypress.com/mcu
PSoC cypress.com/psoc
Power Management ICs cypress.com/pmic

Touch Sensing cypress.com/touch
USB Controllers cypress.com/usb
Wireless Connectivity cypress.com/wireless

PSoC® Solutions

PSoC 1 | PSoC 3 | PSoC 4 | PSoC 5LP

Cypress Developer Community

Forums | WICED IOT Forums | Projects | Video | Blogs | Training | Components

Technical Support

cypress.com/support

© Cypress Semiconductor Corporation, 2013–2017. This document is the property of Cypress Semiconductor Corporation and its subsidiaries, including Spansion LLC ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any licensee under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software in binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is provided.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. Cypress products are not designed, intended, or authorized for use as critical components in systems designed or intended for the operation of weapons, weapons systems, nuclear installations, life-support devices or systems, other medical devices or systems (including resuscitation equipment and surgical implants), pollution control or hazardous substances management, or other uses where the failure of the device or system could cause personal injury, death, or property damage ("Unintended Uses"). A critical component is any component of a device or system whose failure to perform can be reasonably expected to cause the failure of the device or system, or to affect its safety or effectiveness. Cypress is not liable, in whole or in part, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from or related to all Unintended Uses of Cypress products. You shall indemnify and hold Cypress harmless from and against all claims, costs, damages, and other liabilities, including claims for personal injury or death, arising from or related to any Unintended Uses of Cypress products.

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit cypress.com. Other names and brands may be claimed as property of their respective owners.

Document Number: 001-84446 Rev. *L Revised April 19, 2017 Page 18 of 18