


MVK I/O COMPACT MODULE, METAL

CANopen, 16 dig. In / Diag

Digital inputs/outputs
D18 (D18)

For connection cables please see chapter "Connection Technology" All housings are fully potted

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals**More Info****Input**

Sensor supply US	24 V DC (EN 61131-2), max. 200 mA (M12 female), short-circuit and overload protected
------------------	--

Type	for 3-wire sensors or mechanical switches, PNP, (EN 61131-2)
------	--

Connections

Fieldbus	M12, A-coded, 5-pole
----------	----------------------

Sensor-system/actuator supply	7/8", 5-pole, 2 × max. 9 A
-------------------------------	----------------------------

I/O ports	M12, A-coded, 5-pole
-----------	----------------------

Fieldbus

Operating voltage	24 V DC (EN 61131-2)
-------------------	----------------------

Operating modes	Polling; change of state; Cyclic
-----------------	----------------------------------

Transfer rate	max. 1 Mbit/s with switchable terminal resistors
---------------	--

Addressing	Rotary switch 1...99
------------	----------------------

General data

Protection	IP67
------------	------

Mounting method	2-hole screw mounting
-----------------	-----------------------

Temperature range	0...+55 °C (storage temperature -20...+70 °C)
-------------------	---

Dimensions H × W × D	42×63×225 mm
----------------------	--------------

Parameterization

PIN 4	Input
-------	-------

PIN 2	Input/diagnostic
-------	------------------

Diagnostic

Communication status	via LED
----------------------	---------

Diagnostic via LED	per module and channel
--------------------	------------------------

Diagnostic via BUS	per module and channel
--------------------	------------------------

Monitoring - under voltage	yes
----------------------------	-----

Monitoring - no voltage	yes
-------------------------	-----

Short circuit and overload	yes
----------------------------	-----

Actuator warning	per channel via LED and BUS
------------------	-----------------------------

Cable break	per port
-------------	----------

Commercial data

country of origin	DE
-------------------	----

customs tariff number	85176200
-----------------------	----------

minimum order quantity	1
------------------------	---