

SITOR FUSE-LINK 50A, AC 1000V, FOR 6QG11



Figure similar

Model		
product brand name		SETRON
Design of an identification indicator		others
Design of the switching contact		Non-corroding, silver-plated
Design of the fuse link		Fuses for special applications
General technical data		
Size of fuse system / acc. to DIN EN 60269-1		others
Operating class of the fuse link		gR
circuit-breaker / Design		3NE
Switching capacity		
Switching capacity current		
<ul style="list-style-type: none"> <li>acc. to IEC 60947-2 / Rated value</li> </ul>	kA	100
Dissipation		
Active power loss		
<ul style="list-style-type: none"> <li>for rated value of the current / with AC / in hot operating state / per pole</li> </ul>	W	20
Electricity		
rated current I <sub>n</sub> / IEC, DIN/VDE / at 40 Cel	A	50
Current / with AC / Rated value	A	50
Mechanical Design		
mounting position		Any, preferably vertical
Environmental conditions		
Ambient temperature		

- minimum
- maximum

°C	-20
°C	50

### Certificates

#### Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F  
F

#### General Product Approval

#### Declaration of Conformity



### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NE41175>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3NE41175/all>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NE41175](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE41175)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015