

## Push broach

for universal use for steel, cast metal and non-ferrous metals up to max. 35 HRC

### Application:

For producing dimensionally accurate and precisely centred keyways in accordance with DIN 6885, for lever, spindle and hydraulic presses in the material groups for steel, cast iron and non-ferrous metals up to max. HRC 35 in individual part and series production.

### Execution:

- precision-ground HSS, with supports

### Advantage:

- high-quality cutting material, precision-ground to ensure long service life and high degree of precision
- user-friendly handling without significant set-up times



<b>Art. no.</b>	<b>19205 006</b>
<b>Workpiece slot width</b>	6 mm
<b>Suitable for wedge width</b>	6 mm
<b>Suitable for wedge thickness</b>	6 mm
<b>Length</b>	302 mm
<b>Min./max. room length</b>	10-64 mm
<b>Number of openings</b>	2 PCS
<b>Clearing force</b>	8.6 kN
<b>Gross Weight</b>	0.335 kg
<b>Product Group</b>	181