

3-point internal micrometer

IMICRO



Application:

For high-precision measurement of through-bores, even at high measuring depths.

Execution:

- Measuring faces made of hardened steel
- Friction coupling for consistent, repeatable measuring force
- Self-centring and self-aligning

Advantage:

- Ground step taper for high precision
- Insensitive to influence of body heat from the user's hand and fluctuations in ambient temperature
- The only 3-point internal micrometer working on the Abbe principle

Delivery:

In cardboard box



Art. no.	31695 125
Brand	TESA
Manufacturer Part Number	00812601
Min./max. length measuring range	100-125 mm
Measuring depth	81 mm
Error limit	6 µm
Vernier scale	0.01 mm
Measuring spindle increments	0.5 mm
Calibration Group	I
DIN	863
Calibration Group Description	Internal micrometers (3 point)
Gross Weight	2.895 kg
Product Group	362

EAN

7630041108248