




**DIL SOCKETS „THROUGH HOLE“**  
**ID: 004** MP-ULP ultra low profile

Series 103



**TECHNICAL DATA**

Pitch	2,54 mm
Insulating Material	high temp. thermoplast UL94V-0
Contact Material	Brass/BeCu
Rated Current	1 Amp.
Rated Voltage	100 V <sub>RMS</sub> /150 V <sub>DC</sub>
Breakdown Voltage	min. 1000 V <sub>RMS</sub>
Operating Temperature	-55°C bis +125°C
Maximum Soldering Temperature	260°C for 10 seconds



Code	Poles	A	B	C	D
06.3	6	7,54	10,08	7,62	4,00
08.3	8	10,08	10,08	7,62	4,00
14.3	14	17,70	10,08	7,62	4,00
16.3	16	20,24	10,08	7,62	4,00
18.3	18	22,78	10,08	7,62	4,00
20.3	20	25,32	10,08	7,62	4,00
24.3	24	30,48	10,08	7,62	4,00
24.6	24	30,40	17,70	15,24	11,10
28.6	28	35,48	17,70	15,24	11,10
32.6	32	40,56	17,70	15,24	11,10
40.6	40	50,72	17,70	15,24	11,10

All dimensions in mm.  
 Other dimensions upon request.

MP-ULP XX.Y SXX U

Code: see table

- XX: TG = sleeve: Sn / clip: Au
- GG = sleeve: Au / clip: Au
- TG OM = without center bar
- TG 8 = sleeve: Sn / clip: 0,75µm Au

U: RoHS-compliant with high temp. plastic