

Solid carbide torus milling cutter

2 cutting edges, ULTRA DC-coated

ATORN®



Application

Torus milling cutter for process reliability in machining graphite, GRP and CRP.

Version

- High-tech CVD diamond coating
- Coating thickness 10+2 µm
- With clearance
- Concentricity 0.005 mm

Advantage

- Wear-resistant, crystalline diamond coating
- Optimised, highly accurate geometry

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
													95						

Art. no.	16661 216
Cutting material	VHM
Surface	ULTRA DC
Type	N
Number of cutting edges	2 PCS
Twist angle	30°
Tool holding device	HA parallel shank
Overall length	Long
Cutting edge diameter	6 mm
Cutting edge length	6 mm
Clearance length	40 mm
Length	90 mm
Clearance diameter	5.9 mm
Shaft diameter	6 mm
Edge radius	0.5 mm
fz graphite	0.045 mm

EAN-Code

4050293403565