

DCKN insert holder, negative right

For facing with CN indexable insert



Application:

For facing and longitudinal turning with CN indexable insert, 80°

Execution:

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type C, pitch angle 75°, tip angle 80°, clearance angle 0°

Advantage:

- Universal application for facing and longitudinal turning with high feed depths and unfavourable conditions
- Negative body geometry ensures good stability and absorption of force for large cutting depths
- Wide adjustment range: Suitable for both finishing and rough machining
- Adjustable clamp minimises vibrations and ensures favourable power transmission

Art. no.	17684 056
Brand	WIDIA
Manufacturer Part Number	5697856
ISO name	DCKN R/L 2020 K12
Knife edge length	12 mm
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Programming size	25 mm
Suitable for indexable inserts	CC.. 09T3..
Tool design	Right
Length of head	32 mm
Gross Weight	0.433 kg
Product Group	1XG

EAN

4050841508186