

## SVLC clamp holder, positive

for copy, longitudinal face lathing with VC indexable insert

**ATORN**<sup>®</sup>

### Application

for copy, longitudinal and face turning with VC indexable insert, 35°

### Version

- precision-manufactured steel support, bronzed, hardened, type V, working angle 95°, tip angle 35°, clearance angle 7°

### Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces
- excellent surface quality for medium infeed and finishing
- Very good surface quality for medium infeed and finishing



<b>Art. no.</b>	<b>17836 264</b>
<b>ISO name</b>	SVLC R/L 0808 D07
<b>Shaft height</b>	8 mm
<b>Shank width</b>	8 mm
<b>Length</b>	60 mm
<b>Length of head</b>	15 mm
<b>Programming size</b>	10 mm
<b>Suitable for indexable inserts</b>	VC.. 0702..
<b>Tool design</b>	Left

### EAN-Code

4050293543964