

## Electronic micrometer head

0–25 mm, Digimatic, 12 mm stem, with clamping nut and spherical spindle

Mitutoyo

### Application:

For integration in measuring and pre-adjustment devices and for use as setting and control elements in machine tools

### Execution:

- LCD digit size 7.5 mm
- Drive arbour with clamping nut
- spherical spindle
- 12 mm shank



<b>Art. no.</b>	<b>32017 639</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	350-284-30
<b>Display</b>	Digital
<b>Min./max. length measuring range</b>	0-25 mm
<b>Digit increment</b>	0.001 mm
<b>Measuring surface diameter</b>	6.35 mm
<b>Measuring arrangement</b>	Spherical (SR4)
<b>Clamp in shank diameter</b>	12 mm
<b>Clamping shank length</b>	11 mm
<b>Coupling design</b>	Slide coupling
<b>Measuring spindle increments</b>	0.5 mm
<b>Spindle clamping</b>	Yes
<b>Functions</b>	ABS function, Automatic switch-off, Preset function, Hold-function (AE lock)
<b>IP protection class</b>	IP 65
<b>Design</b>	Metric
<b>Digit height</b>	7.5 mm
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	SR44
<b>Data transmission type</b>	DIGIMATIC
<b>Calibration Group</b>	DE
<b>Gross Weight</b>	0.300 kg
<b>Product Group</b>	3MA

### EAN

494636869604 1