



Figure similar

SIMATIC S7-300, COUNTER MODULE FM 350-2, 8 CHANNELS, 20 KHZ, 24V ENCODER FOR COUNTING, MEASURING FREQUENCIES, SPEED MEASUREMENT, PERIOD DURATION MEASUREMENT AND PROPORTIONING INCL. CONFIG. PACKAGE AND ELECTRONIC DOCU ON CD

Supply voltage

Aux. voltage 1L+, load voltage 2L+

• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V

Input current

from load voltage L+ (without load), max.	150 mA
from backplane bus 5 V DC, max.	100 mA

Encoder supply

Type of output voltage	NAMUR-encoder supply: 8.2 V +/-2%
short-circuit protection	Yes

Output current

• nominal	200 mA
-----------	--------

Power losses

Power loss, typ.	10 W
------------------	------

Digital inputs

Number of digital inputs	8
Functions	1 each for gate start/ gate stop

Input voltage

• for signal "0"	-3 to +5V
• for signal "1"	11 to 30.2 V

Input current

• for signal "0", max. (permissible quiescent current)	2 mA
• for signal "1", typ.	9 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— at "0" to "1", max.	50 µs
Cable length	
• shielded, max.	100 m
Digital outputs	
Number of digital outputs	8
short-circuit protection	Yes
Limitation of inductive shutdown voltage to	L+ (-40 V)
Output voltage	
• for signal "1", min.	L+ (-0.8 V)
Output current	
• for signal "1" rated value	0.5 A
• for signal "0" residual current, max.	0.5 mA
Output delay with resistive load	
• "0" to "1", max.	300 µs
Switching frequency	
• with resistive load, max.	500 Hz
• with inductive load, max.	0.5 Hz
Aggregate current of outputs (per group)	
horizontal installation	
— up to 40 °C, max.	4 A
— up to 60 °C, max.	2 A
all other mounting positions	
— up to 40 °C, max.	2 A
Cable length	
• shielded, max.	600 m
• Unshielded, max.	100 m
Encoder	
Connectable encoders	
• Incremental encoder (asymmetrical)	Yes
• 24 V initiator	Yes
• 24 V directional element	Yes
• NAMUR encoder	Yes
• 2-wire sensor	Yes
NAMUR encoder	
• Number of NAMUR inputs	8
• Input signal	to DIN 19 234

• Input current for signal "0", max.	1.2 mA
• Input current for signal "1", min.	2.1 mA
• Input delay, max.	50 µs
• Input frequency, max.	20 kHz
• Cable length, shielded, max.	100 m

Interrupts/diagnostics/status information

Alarms

• Diagnostic alarm	Yes; Parameterizable
• Hardware interrupt	Yes; Parameterizable

Diagnostic messages

• Diagnostic functions	Yes; Diagnostic information readable
------------------------	--------------------------------------

Diagnostics indication LED

• Group error SF (red)	Yes
------------------------	-----

Counter input 24 V

• Number	8; 32 bit or +/-31 bit
• Input voltage, for signal "0"	-3 to +5V
• Input voltage, for signal "1"	11 to 30.2 V
• Input current, for signal "0", max. (permissible quiescent current)	2 mA
• Input current, for signal "1", typ.	9 mA
• Input delay, max.	50 µs
• Counting frequency, max.	20 kHz; Incremental encoder: 10 kHz
• Cable length, max.	100 m

Galvanic isolation

Galvanic isolation digital inputs

• between the channels and the backplane bus	Yes; and shielding
• between the channels and the backplane bus (NAMUR)	yes, against backplane bus and shielding

Galvanic isolation digital outputs

• between the channels and the backplane bus	Yes; and shielding
--	--------------------

Galvanic isolation counter

• between the channels and the backplane bus	Yes; and shielding
--	--------------------

Connection method

required front connector	1x 40-pin
--------------------------	-----------

Dimensions

Width	80 mm
Height	125 mm
Depth	120 mm

Weights

Weight, approx.	460 g
-----------------	-------

last modified:

12.03.2015