ROLINE Industrial Mini Converter, 10/100TX - 100FX (SC)

Product No. 21.13.1147

NI INIT

Manufacturer ROLINE

Manufacturer No. 21.13.1147

EAN (single piece) 7611990197026



- Support full wire speed copper-to-fiber media conversion for 10/100Mbit/s speed and media types
- Supports auto-negotiation 10/100Mbps or forced mode on the copper port
- Auto-MDI/MDIX on the copper port
- Provides Link Fault Pass Through function
- Transparent conversion to 802.1Q VLAN tagged packets
- Provides Far End Fault function on FX (fiber) port
- The optimal latency for 100Mbit/s to 100Mbit/s conversion
- Low power consumption
- Power: Input: +4.5 50 VDC, Consumption: 1.6 W@ 7.5 V, 1.6 W@ 12 V, 2 W@ 48 V
- Supports DIN rail mounting
- Compact design for easy installation in enclosure and chassis
- Supports wide operating temperature range
- Industrial-rated emission and immunity performance
- DC Input via terminal block or DC power jack
- Dimensions: 34 x 49 x 56 mm (WxDxH)
- Operating Temperature: 20 °C +70 °C
- As according power supply unit we recommend 21.13.1226 or

Technical specifications

Manufacturer ROLINE

Product group Network converters

Product type	Media Converter
Colour	black