






STRAIGHT PLUG CLAMP TYPE CABLE 5/50 S

PAGE 1/2 ISSUE 1446 V SERIES BNC-HT / PART NUMBER R316007000 MHV











COMPONENTS	MATERIALS	PLATING (μm)
Body	BRASS	NICKEL 2
Center contact	BRASS	SILVER
Outer contact	-	-
Insulator	PTFE	
Gasket	-	
Others parts	BRASS	NICKEL2
-	-	-
-	-	-



Technical Data Sheet

STRAIGHT PLUG CLAMP TYPE CABLE 5/50 S

PAGE 2/2	ISSUE 1446 V	SERIES BNC-HT / MHV	PART NUMBER R316007000
-----------------	---------------------	------------------------	-------------------------------

PACKAGING

100	Contact us	Contact us
Standard	Unit	Other

ELECTRICAL CHARACTERISTICS

Impedance 50 Frequency 0-2 GHz **VSWR** 1.2 0.2000 x F(GHz) Maxi Insertion loss √F(GHz) dB Maxi RF leakage - F(GHz)) dB Maxi - (Voltage rating Veff Maxi Dielectric withstanding voltage 6000* Veff mini Insulation resistance $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention Axial force - Mating End NA N mini Axial force - Opposite end NA N mini N.cm mini Torque

Recommended torque

Mating N.cm Panel nut N.cm Clamp nut 150 N.cm A/F clamp nut 9.5000 mm

Mating life 500 Cycles mini 18.1700 g

Weight

ENVIRONMENTAL

Operating temperature -55/+155 $^{\circ}C$ Hermetic seal Atm.cm3/s Panel leakage

SPECIFICATION

CABLE ASSEMBLY

Stripping	а	b	С	d	е	f
mm	2.5	14.7	0	0	11.5	0

Assembly instruction: Clamp 03

Recommended cable(s)

RG 58 KX 15 RG 141

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

Cable retention

- pull off 90 N mini - torque NA N.cm

TOOLING

Part Number	Description	Hexagon

OTHER CHARACTERISTICS

*Test frequency at 60Hz; 10 KVeff for mated pair