

DISCONNECTION TERMINAL BLOCK 4 MM², 6,2 MM WIDTH GREY WITH PLUG

Model		
Type of longitudinal separation		pluggable
Type of lateral separation		without
Design of terminal / Terminal levels internally linked		No
General technical data		
Insulation material		thermoplastic
Terminal contact spacing	mm	6.2
Protection class		
Combustibility class acc. to UL 94		V0
Main circuit		
Operating voltage / Rated value	V	400
Operating current / Rated value	A	20
Appearance		
Color		grey
Product details		
Product component		
<ul style="list-style-type: none"> • required / connection plate • Test socket 		<ul style="list-style-type: none"> Yes No
Number		
Number of terminal levels		1
Number of terminal points / per terminal level		2
Connections		
Connectable conductor cross-section / stranded		
<ul style="list-style-type: none"> • minimum • maximum 	<ul style="list-style-type: none"> mm² mm² 	<ul style="list-style-type: none"> 0.25 4
Connectable conductor cross-section		
<ul style="list-style-type: none"> • solid <ul style="list-style-type: none"> — minimum — maximum • finely stranded <ul style="list-style-type: none"> — with core end processing / minimum — with core end processing / maximum — without core end processing / minimum 	<ul style="list-style-type: none"> mm² mm² mm² mm² mm² mm² 	<ul style="list-style-type: none"> 0.2 6 0.25 4 0.2

— without core end processing / maximum	mm ²	4
Type of electrical connection		
<ul style="list-style-type: none"> • 1 • 2 		Plug-in terminal connection plug terminal connection
Position / of the terminal		top

Mechanical Design		
Height / with lowest-profile installation	mm	36.5
Length	mm	54
Mounting type		DIN rail 35 mm
Material / of the insulating body		Thermoplast

General Product Approval	Declaration of Conformity
--------------------------	---------------------------



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8WH60006AG00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8WH60006AG00/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8WH60006AG00

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified: 11.03.2015