

## Short drill chuck

In accordance with ISO 7388-1 (DIN 69871); self-clamping

**ORION**<sup>®</sup>

### Application:

For drilling and centring.

### Execution:

- Precision version.
- Clamping force increases automatically and proportionally to the torque.

### Advantage:

- Quick clamping via clamping sleeve, with two clamping surfaces for doubling the clamping force with a wrench.
- In the event that the spindle stops suddenly, loosening of the cutting tool is prevented.

### Delivery:

1x short drill chuck in accordance with ISO 7388-1 (DIN 69871) self-clamping; incl. wrench.



<b>Art. no.</b>	<b>23050 750</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	23050750
<b>Tool holding device</b>	SK 50
<b>Min./max. clamping width</b>	3-16 mm
<b>Projecting length</b>	90 mm
<b>Outer diameter</b>	57 mm
<b>Coolant supply</b>	No
<b>Balancing quality</b>	G 6.3 at 12 rpm
<b>Gross Weight</b>	3.891 kg
<b>Product Group</b>	295

### EAN

4039247893256