1-2118909-4 V ACTIVE

TE Internal #: 1-2118909-4


Antenna, Bluetooth / ZigBee / WLAN, Adhesive, Cable Assembly,

MHF Compatible, Cable Length 200 mm [7.874 in]

View on TE.com >



Antennas



Wireless Application: Bluetooth, WLAN, ZigBee

Mounting Retention Type: Adhesive

Antenna Connection Type: Cable Assembly
Antenna Connector Type: MHF Compatible

Cable Length: 200 mm [7.874 in]

Antenna Connection Type

Features

Product Type Features

Antenna Connector Type	MHF Compatible
Configuration Features	
Band Type	Triple Band
Antenna Protocol	WLAN
Number of Ports	1
Antenna Style	Embedded
Antenna Type	PCB
Electrical Characteristics	
Impedance	50 Ω

Cable Assembly

Signal Characteristics

Active Antenna

Frequency Band	2400 – 2500 MHz, 5150 – 5875 MHz, 5925 – 7125 MHz
Gain (Max)	4.3 dB

No



Body Features

Product Weight	1.79 g[.063 oz]
Mechanical Attachment	
Region	Global
Polarization	Linear
Mounting Retention Type	Adhesive
Dimensions	
Cable Length	200 mm[7.874 in]
Product Length	40 mm[7.874 in]
Product Width	8 mm[.314 in]

Usage Conditions

Product Height

Application by Region	Bluetooth - Global - 2400 – 2500 MHz,
	WLAN - Global - 2400 – 2483.5 MHz, WLAN
	- Global - 5150 – 5875 MHz, WLAN - Global
	- 5925 – 7125 MHz

1 mm[.039 in]

Operation/Application

Wireless Standard	802.11 a/b/g/n/ac/ad/ax, Bluetooth,
	ZigBee & Wi-Fi

Industry Standards

Wireless Application	Bluetooth, WLAN, ZigBee
----------------------	-------------------------

Packaging Features

Packaging Method	Bag & Box	
------------------	-----------	--

Other

Precision Level	Standard

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JUN 2020

(209)

SVHC > Threshold:

Not Yet Reviewed

Halogen Content Low Bromine/Chlorine - Br and Cl < 900

ppm per homogenous material. Also BFR

/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



Customers Also Bought





Documents

Product Drawings
PCB Ant, MHF, 200mm, Wi-Fi 6E Triple

English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2118909-4_2.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2118909-4_2.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2118909-4_2.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

Wi-Fi 6E TRIPLE BAND EMBEDDED ANTENNA

English

Product Specifications

Product Specification

English