

testo

Committing to the future

Pocket-Sized Professional Measurement Technology

Measuring instruments for heating, air conditioning and ventilation

NEW!



Testo, the leading manufacturer of portable measurement technology, provides pocket-sized measuring instruments for fast and tough everyday use:

- Air temperature and infrared surface temperature
- Air humidity and temperature
- Material moisture, air humidity and temperature
- Differential pressure
- Absolute pressure
- rpm
- Light intensity
- Air flow velocity, temperature, humidity

Sensors which fulfil the highest demands, such as Testo's own patented humidity sensor, guarantee reliable and stable measurement results.

All instruments are very handy, small and easy to use. The backlit display and the Auto-Off function complete the instrument.

Always included:

Protective cap, wrist strap and belt holder – indispensable additions for practical use.

Great technology can be this small!

testo 810

Air temperature and infrared surface temperature in one instrument

- IR measurement with 1-point laser measurement spot marking and 6:1 optics
- Air temperature measurement
- Display of differential temperature e.g. between window and air
- Hold function and max./min. values

testo 610

Air humidity and temperature

- Long-term drift-free Testo humidity sensor
- 2.5 %RH accuracy with calibration protocol
- Incl. dewpoint calculation and wet bulb
- Hold function and max./min. values

testo 606-1/2

Material moisture, air humidity and temperature

- Precise measurement of wood moisture thanks to stored characteristics curves for e.g. beech, spruce, larch, oak, pine, maple
- Air temperature and humidity for monitoring drying processes
- Characteristics curves for cement screed, concrete, plaster, anhydrite screed, cement mortar, lime mortar, brick
- Hold function
- Auto-test function

testo 410-1/-2

Air flow velocity, temperature and humidity

- Integrated measurement with 40 mm vane
- Timed mean value calculation
- Hold function and min./max. values
- Windchill calculation for outdoor areas

Surface temperature	
Measuring range:	-30 to 300 °C
Resolution:	0.1 °C
Accuracy:	±2.0 °C (-30 to +100 °C) ± 2% of m.v. (remaining range)
Optics:	6:1
<u>Air temperature</u>	
Measuring range:	-10 to 50 °C
Resolution:	0.1 °C
Accuracy :	± 0.5 °C
Units:	°C/F
Oper. temp.:	-10 to 50 °C
Battery type:	Alkaline (2 x AAA)
Battery life:	50 h. (average, without display illumination)
Dimensions	
(incl. protective cap):	119 x 46 x 25 mm

Temperature	
Measuring range:	-10 to 50 °C
Resolution:	0.1 °C
Accuracy:	± 0.5 °C
Units:	°C/F
<u>Humidity</u>	
Measuring range:	0 to 100 %RH
Resolution:	0.1 %RH
Accuracy:	± 2.5 %RH (5 to 95 %RH)
Units:	%RH, wet bulb, dewpoint
Oper. temp.:	10 to 50 °C
Battery type:	Alkaline (2 x AAA)
Battery life:	200 h. (average, without display illumination)
Dimensions	
(incl. protective cap):	119 x 46 x 25 mm

Material moisture	
Measuring range:	0 to 90%
Resolution:	0.1
Accuracy:	± 1% (conductivity)
<u>Air humidity</u> (606-2 only)	
Measuring range:	0 to 100%RH
Resolution:	0.1%RH
Accuracy:	± 2.5%RH (5 to 95%RH)
Units:	%RH, wet bulb, dewpoint
<u>Air temperature</u> (606-2 only)	
Measuring range:	-10 to 50 °C
Resolution:	0.1°C
Accuracy:	± 0.5 °C
Units:	°C/F
Oper. temp.:	-10 to 50 °C
Battery type:	Alkaline (2 x AAA)
Battery life:	606-1: 200 h. 606-2: 130 h. (average, without display illumination)
Dimensions	
(incl. protective cap):	119 x 46 x 25 mm

Flow velocity	
Measuring range:	0.4 to 20 m/s
Resolution:	0.1 m/s
Accuracy:	± (0.2 m/s + 2% of m.v.)
Units:	m/s, km/h, fpm, mph, knots, perceived temperature °C/F (windchill), Beaufort
<u>Temperature</u>	
Measuring range:	-10 to 50 °C
Resolution:	0.1 °C
Accuracy:	± 0.5 °C
Units:	°C/F
<u>Humidity</u> (testo 410-2 only)	
Measuring range:	0 to 100 %RH
Resolution:	0.1 %RH
Accuracy:	± 2.5 %RH (5 to 95 %RH)
Units:	%RH, wet bulb, dewpoint
Oper. temp.:	-10 to 50 °C
Battery type:	Alkaline (2 x AAA)
Battery life:	testo 410-1: 100 h. testo 410-2: 60 h. (average, without display illumination)
Dimensions	
(incl. protective cap):	133 x 46 x 25 mm

Included in delivery:	
Calibration protocol	· Wrist strap
Belt holder	· Protective cap · Batteries

Order no. 0560 0610
606-1: Order no. 0560 6060 606-2: Order no. 0560 6062

Included in delivery:	
Calibration protocol	· Wrist strap
Belt holder	· Protective cap · Batteries

Order no. 0560 4101
410-1: Order no. 0560 4102

· 50 YEARS OF TESTO



- More innovative than ever
- 50 innovations in the anniversary year

INNOVATION 2007

testo 510

Differential pressure
0 to 100 hPa



- Possibility of display in Pascal over entire measuring range
- Temperature compensation
- Magnets on the rear allow free-hand work
- Flow velocity measurement with Pitot tube
- Air density compensation

testo 511

Absolute pressure,
barometric pressure, altitude



- Absolute pressure ±3 hPa
- Calculation of barometric air pressure
- Barometric altitude measurement

testo 460

rpm, optical



- Optical rpm measurement with LED measurement spot marking
- Max./min. values

testo 540

Light
intensity



- Sensor is adjusted to the spectral sensitivity of the eye
- Hold function for easy measurement value readout
- Max./min. values

Pressure

Measuring range: 0 to 100 hPa
Resolution: 0.01 hPa
Accuracy: ± 0.03 hPa
(0 to 0.30 hPa)
± 0.05 hPa
(0.31 to 1.00 hPa)
± (0.1 hPa + 1.5% of m.v.)
(1.01 hPa to 100 hPa)

Units: hPa, mbar, Pa,
mmH₂O, mmHg,
inH₂O, inHg, psi,
m/s, fpm

Oper. temp.: 0 to 50 °C
Battery type: Alkaline (2 x AAA)
Battery life: 500 h. (average, without
display illumination)

Dimensions
(incl. protective cap): 119 x 46 x 25 mm

Pressure

Measuring range: 300 to 1,200 hPa
Resolution: 0.1 hPa
Accuracy: ± 3.0 hPa
Units: hPa, mbar, Pa, mmH₂O,
mmHg, inH₂O, inHg, psi,
m, ft

Oper. temp.: 0 to 50 °C
Battery type: Alkaline (2 x AAA)
Battery life: 500 h. (average, without
display illumination)

Dimensions
(incl. protective cap): 119 x 46 x 25 mm

rpm

Measuring range: 100 to 29,999 rpm
Resolution: 0.1 rpm
(100 to 999.9 rpm)
1 rpm
(1,000 to 29,999 rpm)
Accuracy: ± (0.02 % of m.v.) + 1 digit
Units: rpm, rps
Oper. temp.: 0 to 50 °C
Battery type: Alkaline (2 x AAA)
Battery life: 20 Std. (average, without
display illumination)

Dimensions
(incl. protective cap): 119 x 46 x 25 mm

Light intensity

Measuring range: 0 to 99,999 Lux
1 Lux (0 to 19,999 Lux)
10 Lux
(20,000 to 99,999 Lux)
Accuracy: ± 3% (compared to
reference)
Units: Lux, Footcandle
Oper. temp.: 0 to 50 °C
Battery type: Alkaline (2 x AAA)
Battery life: 20 Std. (average, without
display illumination)

Dimensions
(incl. protective cap): 133 x 46 x 25 mm

Included in delivery:

Calibration protocol · Wrist strap
Belt holder · Protective cap · Batteries

Order no. 0560 0510

Included in delivery:

Calibration protocol · Wrist strap
Belt holder · Protective cap · Batteries

Order no. 0560 0511

Included in delivery:

Calibration protocol · Wrist strap
Belt holder · Protective cap · Batteries

Order no. 0560 0460

Included in delivery:

Calibration protocol · Wrist strap
Belt holder · Protective cap · Batteries

Order no. 0560 0540





Pocket-Sized Professional Measurement Technology



Subject to change without notice.

- 50 YEARS OF TESTO
- More innovative than ever
- 50 innovations in the anniversary year

INNOVATION 2007



0981 1564/dk/R/Q/02.2007