



Figure similar

SUPPORT F. STAND-ALONE INSTALLATION FOR
3RU21/3RB30/3RB31 SZ. S2, STAND-ALONE
INSTALLATION MAIN CIRCUIT: SCREW TERMINAL

General technical data:

product brand name		SIRIUS
Product designation		individual mount
Size of overload relay		S2
Ambient temperature		
• during storage	°C	-50 ... +80
• during operation	°C	-20 ... +70

Installation/ mounting/ dimensions:

Mounting type		screw and snap-on mounting onto 35 mm standard mounting rail
Width	mm	55
Height	mm	105
Depth	mm	111

Connections/ Terminals:

Type of electrical connection		screw-type terminals
• for main current circuit		
Type of connectable conductor cross-section		
• for main contacts		
— solid		1x (1 ... 10 mm ²)
— stranded		1x (2.5 ... 50 mm ²)
— finely stranded		
— with core end processing		1x (1 ... 35 mm ²)
• for AWG conductors		
— for main contacts		1x (18 ... 1)

Certificates/ approvals:

General Product Approval	Test Certificates	other
--------------------------	-------------------	-------



[Type Test Certificates/Test Report](#)

[Environmental Confirmations](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RU29363AA01>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RU29363AA01/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RU29363AA01&lang=en>





last modified:

09.03.2015