

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Trade name : Machine Dishwash
Product code : CAT1001

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Industrial use, Professional use
Use of the substance/mixture : Dish wash concentrate

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Supplier

Crown Supplies Ltd
UNIT 3
VULCAN ROAD NORTH
NR6 6AQ Norwich - UK
T 01603 403 333 - F 01603 403 362
sales@crownsupplies.co.uk - www.crownsupplies.co.uk

1.4. Emergency telephone number

Emergency number : 01603 403 333
NORMAL OFFICE HOURS

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

| | |
|---|------|
| Skin corrosion/irritation, Category 1 | H314 |
| Serious eye damage/eye irritation, Category 1 | H318 |
| Hazardous to the aquatic environment — Chronic Hazard, Category 3 | H412 |

Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

May be corrosive to metals. Causes severe skin burns and eye damage. Causes serious eye damage. Harmful to aquatic life with long lasting effects.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS05

Signal word (CLP) :

Danger

Contains :

potassium hydroxide; caustic potash; sodium hypochlorite, solution... % Cl active;
ETIDRONIC ACID; phosphonic acid

Hazard statements (CLP) :

H314 - Causes severe skin burns and eye damage.
H412 - Harmful to aquatic life with long lasting effects.

Machine Dishwash

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Precautionary statements (CLP) : P280 - Wear protective gloves, protective clothing, eye protection.
P301+P330+P331+P310 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting. Immediately call a doctor.
P303+P361+P353+P310 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.. Immediately call a doctor.
P305+P351+P338+P310 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a doctor.

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

| Name | Product identifier | % | Classification according to Regulation (EC) No. 1272/2008 [CLP] |
|--|--|-------------|---|
| potassium hydroxide; caustic potash | CAS-No.: 1310-58-3 EC-No.: 215-181-3 EC Index-No.: 019-002-00-8 REACH-no: 01-2119487136-33-XXXX | ≥ 10 – < 30 | Acute Tox. 4 (Oral), H302 Skin Corr. 1A, H314 |
| trisodium nitrilotriacetate | CAS-No.: 5064-31-3 EC-No.: 225-768-6 EC Index-No.: 607-620-00-6 | ≥ 0.5 – < 5 | Acute Tox. 4 (Oral), H302 Eye Irrit. 2, H319 Carc. 2, H351 |
| sodium hypochlorite, solution... % Cl active | CAS-No.: 7681-52-9 EC-No.: 231-668-3 EC Index-No.: 017-011-00-1 REACH-no: 01-2119488154-34 | < 0.5 | Skin Corr. 1B, H314 Eye Dam. 1, H318 Aquatic Acute 1, H400 (M=1) Aquatic Chronic 1, H410 (M=1) |

Specific concentration limits: see section 16

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general : Call a physician immediately.
First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact : Rinse skin with water/shower. Take off immediately all contaminated clothing. Call a physician immediately.
First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Call a physician immediately.
First-aid measures after ingestion : Rinse mouth. Do not induce vomiting. Call a physician immediately.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after skin contact : Burns.
Symptoms/effects after eye contact : Serious damage to eyes.
Symptoms/effects after ingestion : Burns.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

Machine Dishwash

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released.

5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area. Avoid contact with skin and eyes. Do not breathe dust/fume/gas/mist/vapours/spray.

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Take up liquid spill into absorbent material.
Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Avoid contact with skin and eyes. Do not breathe dust/fume/gas/mist/vapours/spray. Wear personal protective equipment.
Hygiene measures : Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in corrosive resistant container with a resistant inner liner. Keep only in original container. Store locked up. Store in a well-ventilated place. Keep cool.
Incompatible products : Oxidizing agent. Strong acids.
Incompatible materials : Metals. acids.

7.3. Specific end use(s)

No additional information available

Machine Dishwash

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1. National occupational exposure and biological limit values

| potassium hydroxide; caustic potash (1310-58-3) | |
|---|---------------------------------------|
| United Kingdom - Occupational Exposure Limits | |
| Local name | Potassium hydroxide |
| WEL STEL (OEL STEL) | 2 mg/m ³ |
| Regulatory reference | EH40/2005 (Fourth edition, 2020). HSE |

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

8.2.2. Personal protection equipment

Personal protective equipment symbol(s):



8.2.2.1. Eye and face protection

Eye protection:

Safety glasses

| Eye protection | | | |
|--------------------------------|----------------------|--|----------|
| Type | Field of application | Characteristics | Standard |
| Safety glasses, Safety goggles | Droplet | clear, Direct-ventilated, Plastic, With side shields | |

8.2.2.2. Skin protection

Skin and body protection:

Wear suitable protective clothing

| Skin and body protection | |
|--------------------------|----------|
| Type | Standard |
| Safety shoes | |

Hand protection:

Protective gloves

Machine Dishwash

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

| Hand protection | | | | | |
|-------------------|----------------------|------------|----------------|-------------|----------|
| Type | Material | Permeation | Thickness (mm) | Penetration | Standard |
| Disposable gloves | Nitrile rubber (NBR) | | | | |

| Other skin protection Materials for protective clothing | | |
|--|----------------|----------|
| Condition | Material | Standard |
| Good resistance: | Natural fibres | |

8.2.2.3. Respiratory protection

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Environmental exposure controls:

Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

| | |
|---|---------------------|
| Physical state | : Liquid |
| Colour | : No data available |
| Odour | : No data available |
| Odour threshold | : No data available |
| pH | : 13 – 14 |
| Relative evaporation rate (butylacetate=1) | : No data available |
| Melting point | : Not applicable |
| Freezing point | : No data available |
| Boiling point | : No data available |
| Flash point | : No data available |
| Auto-ignition temperature | : No data available |
| Decomposition temperature | : No data available |
| Flammability (solid, gas) | : Not applicable |
| Vapour pressure | : No data available |
| Relative vapour density at 20 °C | : No data available |
| Relative density | : 1.13 |
| Density | : 1.12 – 1.14 |
| Solubility | : No data available |
| Partition coefficient n-octanol/water (Log Pow) | : No data available |
| Viscosity, kinematic | : No data available |
| Viscosity, dynamic | : No data available |
| Explosive properties | : No data available |
| Oxidising properties | : No data available |
| Explosive limits | : No data available |

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

Machine Dishwash

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

metals.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

sodium hypochlorite, solution... % Cl active (7681-52-9)

| | |
|-----------------------|---------------------------|
| LD50 oral | 2900 – 3400 mg/kg (mouse) |
| LD50 dermal rabbit | > 2000 mg/kg |
| LD50, Inhalation, rat | > 10.5 mg/l |

Skin corrosion/irritation : Causes severe skin burns.
pH: 13 – 14
Serious eye damage/irritation : Causes serious eye damage.
pH: 13 – 14
Respiratory or skin sensitisation : Not classified
Germ cell mutagenicity : Not classified
Carcinogenicity : Not classified
Reproductive toxicity : Not classified
STOT-single exposure : Not classified
STOT-repeated exposure : Not classified
Aspiration hazard : Not classified

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : Harmful to aquatic life with long lasting effects.
Hazardous to the aquatic environment, short-term (acute) : Not classified
Hazardous to the aquatic environment, long-term (chronic) : Harmful to aquatic life with long lasting effects.
Not rapidly degradable

sodium hypochlorite, solution... % Cl active (7681-52-9)

| | |
|---------------------|--------------------------------------|
| LC50 - Fish [1] | 0.22 – 0.62 mg/l Pimephales promelas |
| EC50, Daphnia magna | 2.1 mg/l (96 Hours) |
| EC50, algae | 28 mg/l (24 Hours) |

Machine Dishwash

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available






SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

| ADR | IMDG | IATA | ADN | RID |
|---|---|---|---|---|
| 14.1. UN number | | | | |
| UN 1814 | UN 1814 | UN 1814 | UN 1814 | UN 1814 |
| 14.2. UN proper shipping name | | | | |
| POTASSIUM HYDROXIDE SOLUTION | POTASSIUM HYDROXIDE SOLUTION | Potassium hydroxide solution | POTASSIUM HYDROXIDE SOLUTION | POTASSIUM HYDROXIDE SOLUTION |
| Transport document description | | | | |
| UN 1814 POTASSIUM HYDROXIDE SOLUTION, 8, III, (E) | UN 1814 POTASSIUM HYDROXIDE SOLUTION, 8, III | UN 1814 Potassium hydroxide solution, 8, III | UN 1814 POTASSIUM HYDROXIDE SOLUTION, 8, III | UN 1814 POTASSIUM HYDROXIDE SOLUTION, 8, III |
| 14.3. Transport hazard class(es) | | | | |
| 8 | 8 | 8 | 8 | 8 |
|  |  |  |  |  |
| 14.4. Packing group | | | | |
| III | III | III | III | III |
| 14.5. Environmental hazards | | | | |
| Dangerous for the environment: No | Dangerous for the environment: No Marine pollutant: No | Dangerous for the environment: No | Dangerous for the environment: No | Dangerous for the environment: No |
| No supplementary information available | | | | |


Machine Dishwash

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

14.6. Special precautions for user

Overland transport

| | |
|---|---|
| Classification code (ADR) | : C5 |
| Limited quantities (ADR) | : 5I |
| Excepted quantities (ADR) | : E1 |
| Packing instructions (ADR) | : P001, IBC03, LP01, R001 |
| Mixed packing provisions (ADR) | : MP19 |
| Portable tank and bulk container instructions (ADR) | : T4 |
| Portable tank and bulk container special provisions (ADR) | : TP1 |
| Tank code (ADR) | : L4BN |
| Vehicle for tank carriage | : AT |
| Transport category (ADR) | : 3 |
| Special provisions for carriage - Packages (ADR) | : V12 |
| Hazard identification number (Kemler No.) | : 80 |
| Orange plates | :  |
| Tunnel restriction code (ADR) | : E |
| EAC code | : 2R |

Transport by sea

| | |
|------------------------------------|--|
| Special provisions (IMDG) | : 223 |
| Limited quantities (IMDG) | : 5 L |
| Excepted quantities (IMDG) | : E1 |
| Packing instructions (IMDG) | : P001, LP01 |
| IBC packing instructions (IMDG) | : IBC03 |
| Tank instructions (IMDG) | : T4 |
| Tank special provisions (IMDG) | : TP1 |
| EmS-No. (Fire) | : F-A |
| EmS-No. (Spillage) | : S-B |
| Stowage category (IMDG) | : A |
| Segregation (IMDG) | : SGG18, SG35 |
| Properties and observations (IMDG) | : Colourless liquid. Reacts with ammonium salts, evolving ammonia gas. Reacts with ammonium salts, evolving ammonia gas. Causes burns to skin, eyes and mucous membranes. Reacts violently with acids. |

Air transport

| | |
|--|------------|
| PCA Excepted quantities (IATA) | : E1 |
| PCA Limited quantities (IATA) | : Y841 |
| PCA limited quantity max net quantity (IATA) | : 1L |
| PCA packing instructions (IATA) | : 852 |
| PCA max net quantity (IATA) | : 5L |
| CAO packing instructions (IATA) | : 856 |
| CAO max net quantity (IATA) | : 60L |
| Special provisions (IATA) | : A3, A803 |
| ERG code (IATA) | : 8L |

Inland waterway transport

| | |
|-----------------------------------|----------|
| Classification code (ADN) | : C5 |
| Limited quantities (ADN) | : 5 L |
| Excepted quantities (ADN) | : E1 |
| Equipment required (ADN) | : PP, EP |
| Number of blue cones/lights (ADN) | : 0 |

Rail transport

| | |
|----------------------------|---------------------------|
| Classification code (RID) | : C5 |
| Limited quantities (RID) | : 5L |
| Excepted quantities (RID) | : E1 |
| Packing instructions (RID) | : P001, IBC03, LP01, R001 |

Machine Dishwash

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

| | |
|---|--------|
| Mixed packing provisions (RID) | : MP19 |
| Portable tank and bulk container instructions (RID) | : T4 |
| Portable tank and bulk container special provisions (RID) | : TP1 |
| Tank codes for RID tanks (RID) | : L4BN |
| Special provisions for RID tanks (RID) | : TU42 |
| Transport category (RID) | : 3 |
| Special provisions for carriage – Packages (RID) | : W12 |
| Colis express (express parcels) (RID) | : CE8 |
| Hazard identification number (RID) | : 80 |

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

Other information, restriction and prohibition regulations : Labelling Regulation EC 1272/2008 (CLP). Safety Data Sheet prepared in accordance with REACH Commission Regulation (EU) No 2015/830 (which amends Regulation (EC) No 453/2010 & 1907/2006).

15.1.2. National regulations

France

Occupational diseases

| Code | Description |
|-------|--|
| RG 65 | Eczematiform lesions of allergic mechanism |

Germany

Employment restrictions : Observe restrictions according Act on the Protection of Working Mothers (MuSchG)
Observe restrictions according Act on the Protection of Young People in Employment (JArbSchG)

Water hazard class (WGK) : WGK 1, Slightly hazardous to water (Classification according to AwSV, Annex 1)

Hazardous Incident Ordinance (12. BImSchV) : Is not subject of the Hazardous Incident Ordinance (12. BImSchV)

Netherlands

SZW-lijst van kankerverwekkende stoffen : None of the components are listed

SZW-lijst van mutagene stoffen : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Borstvoeding : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Vruchtbaarheid : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Ontwikkeling : None of the components are listed

Denmark

Danish National Regulations : Young people below the age of 18 years are not allowed to use the product
The requirements from the Danish Working Environment Authorities regarding work with carcinogens must be followed during use and disposal

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

Machine Dishwash

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 16: Other information

| Full text of H- and EUH-statements | |
|------------------------------------|---|
| Acute Tox. 4 (Oral) | Acute toxicity (oral), Category 4 |
| Aquatic Acute 1 | Hazardous to the aquatic environment — Acute Hazard, Category 1 |
| Aquatic Chronic 1 | Hazardous to the aquatic environment — Chronic Hazard, Category 1 |
| Carc. 2 | Carcinogenicity, Category 2 |
| EUH031 | |
| Eye Dam. 1 | Serious eye damage/eye irritation, Category 1 |
| Eye Irrit. 2 | Serious eye damage/eye irritation, Category 2 |
| Skin Corr. 1A | Skin corrosion/irritation, Category 1, Sub-Category 1A |
| Skin Corr. 1B | Skin corrosion/irritation, Category 1, Sub-Category 1B |
| Skin Irrit. 2 | Skin corrosion/irritation, Category 2 |
| H302 | Harmful if swallowed. |
| H314 | Causes severe skin burns and eye damage. |
| H315 | Causes skin irritation. |
| H318 | Causes serious eye damage. |
| H319 | Causes serious eye irritation. |
| H351 | Suspected of causing cancer. |
| H400 | Very toxic to aquatic life. |
| H410 | Very toxic to aquatic life with long lasting effects. |
| H412 | Harmful to aquatic life with long lasting effects. |

| Name | Product identifier | Specific concentration limits |
|--|--|---|
| potassium hydroxide; caustic potash | CAS-No.: 1310-58-3 EC-No.: 215-181-3 EC Index-No.: 019-002-00-8 REACH-no: 01-2119487136-33-XXXX | (0.5 ≤ C < 2) Skin Irrit. 2, H315 (0.5 ≤ C < 2) Eye Irrit. 2, H319 (2 ≤ C < 5) Skin Corr. 1B, H314 (5 ≤ C ≤ 100) Skin Corr. 1A, H314 |
| trisodium nitrilotriacetate | CAS-No.: 5064-31-3 EC-No.: 225-768-6 EC Index-No.: 607-620-00-6 | (5 ≤ C ≤ 100) Carc. 2, H351 |
| sodium hypochlorite, solution... % Cl active | CAS-No.: 7681-52-9 EC-No.: 231-668-3 EC Index-No.: 017-011-00-1 REACH-no: 01-2119488154-34 | (5 ≤ C ≤ 100) EUH031 |

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.