Connection Cable
M12 × 1; 8-pin - RJ45; 8-pin

ZCYV001
Part Number

Technical Data

Mechanical Data	
Connection 1	Plug, straight
Connection mode 1	M12 × 1, 8-pin
Connection 2	Plug, straight
Connection mode 2	RJ45, 8-pin
Cable Length	2 m
Outside diameter (d)	6,4 mm
Wire cross-section	0,14 mm²
Degree of Protection	IP67
Temperature Range	-25...60 °C
Cable Jacket Material	PUR
Material Wire Insulation	PE
Material Sleeve Nut	CuZn, nickel-plated
Category	CAT 5E
Screened	yes
Halogen-free	yes
Packaging unit	1 Piece
Connection Diagram No.	**S63**
Connection Equipment No.	**88**

- **Plug M12 × 1, straight**
- **Plug RJ45, 8-pin**

Legend

+	Supply Voltage +	PT	Platinum measuring resistor	EN$_{A RS422}$	Encoder A/Ā (TTL)
−	Supply Voltage 0 V	nc	not connected	EN$_{B RS422}$	Encoder B/B̄ (TTL)
~	Supply Voltage (AC Voltage)	U	Test Input	EN$_A$	Encoder A
A	Switching Output (NO)	Ū	Test Input inverted	EN$_B$	Encoder B
Ā	Switching Output (NC)	W	Trigger Input	A$_{MIN}$	Digital output MIN
V	Contamination/Error Output (NO)	W−	Ground for the Trigger Input	A$_{MAX}$	Digital output MAX
V̄	Contamination/Error Output (NC)	O	Analog Output	A$_{OK}$	Digital output OK
E	Input (analog or digital)	O−	Ground for the Analog Output	SY In	Synchronization In
T	Teach Input	BZ	Block Discharge	SY OUT	Synchronization OUT
Z	Time Delay (activation)	A$_{MV}$	Valve Output	0$_{LT}$	Brightness output
S	Shielding	a	Valve Control Output +	M	Maintenance
RxD	Interface Receive Path	b	Valve Control Output 0 V	rsv	reserved
TxD	Interface Send Path	SY	Synchronization		Wire Colors according to IEC 60757
RDY	Ready	SY−	Ground for the Synchronization	BK	Black
GND	Ground	E+	Receiver-Line	BN	Brown
CL	Clock	S+	Emitter-Line	RD	Red
E/A	Output/Input programmable	÷	Grounding	OG	Orange
⊕ IO-Link		SnR	Switching Distance Reduction	YE	Yellow
PoE	Power over Ethernet	Rx+/−	Ethernet Receive Path	GN	Green
IN	Safety Input	Tx+/−	Ethernet Send Path	BU	Blue
OSSD	Safety Output	Bus	Interfaces-Bus A(+)/B(−)	VT	Violet
Signal	Signal Output	La	Emitted Light disengageable	GY	Grey
BI_D+/−	Ethernet Gigabit bidirect. data line (A-D)	Mag	Magnet activation	WH	White
EN$_{0 RS422}$	Encoder 0-pulse 0-0̄ (TTL)	RES	Input confirmation	PK	Pink
		EDM	Contactor Monitoring	GNYE	Green/Yellow

Specifications are subject to change without notice