

Releasable Cable Tie

multicomp PRO

Natural



Black




Features

- One piece releasable cable ties
- Ideally suited for servicing/replacement or prototyping work
- These ties, which are easily assembled by hand or with pliers, remain securely locked until intentionally released by operating the finger catch
- Operating temperature -40 to +85°C

Specifications

Cable Tie Length	: 125mm
Cable Tie Width	: 7.6mm
Material	: Nylon 6.6
Tensile Strength N/m ²	: 0N/mm ²
Cable Bundle Dia	: 30mm
Operating Temperature	: -40°C to + 85°C
Tensile Strength	: 22kg
Packaging	: 100 per Pack

Diagram



Length (L)	Width (W)
125mm	7.6mm

Part Number Table

Description	Colour	Part Number
Cable Tie, Releasable, Nylon 6.6	Natural	PP002073
	Black	PP002080

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO