

Roughing cutter, HSSE Co 8

4 cutting edges, TiCN-coated

ORION[®]

Application:

End mill for universal use when plunge milling, groove milling and keyway cutting as well as face milling and peripheral milling.



Execution:

- HSSE Co 8
- fine roughing teeth
- centre cutting (over diameter 20 mm without centre cutting)
- TiCN coating for long service life
- straight shank in accordance with DIN 1835 B

Art. no.	15300 130
Brand	ORION
Manufacturer Part Number	15300130
Cutting material	HSSE Co8
Surface	TiCN
Type	HR
Number of cutting edges	4 PCS
Twist angle	30°
Edge protection chamfer length	0.2 mm
Tool holding device	HB parallel shank
Construction length	Long
Cutting edge diameter	13 mm
Cutting edge length	53 mm
Length	110 mm
Shank diameter	12 mm
fz steel 1300	0.07 mm
Gross Weight	0.017 kg
Product Group	106

EAN

4039247094929