

## SVJC clamp holder for lathes, positive

For longitudinal and copy turning using VC indexable inserts

**ATORN**<sup>®</sup>

### Application

For longitudinal and copy turning using VC 35° indexable inserts



### Version

- Precision-made steel support, bronzed, hardened, type V, pitch angle 93°, tip angle 35°, clearance angle 7°

<b>Art. no.</b>	<b>17829 100</b>
<b>ISO name</b>	SVJC R/L 0808 X11-A
<b>Shaft height</b>	8 mm
<b>Shank width</b>	8 mm
<b>Length</b>	115 mm
<b>Programming size</b>	8 mm
<b>Suitable for indexable inserts</b>	VC.. 1103..
<b>Tool design</b>	Right
<b>DIN</b>	4983

### EAN-Code

4050293693041