



SIMATIC S7-1500, DIGITAL INPUT MODULE DI16 X AC230V, 16 CHANNELS IN GROUPS OF 4; INPUT DELAY 20MS; INPUT TYPE 1 (IEC 61131)

Figure similar

Product type designation	
<b>General information</b>	
HW functional status	E01
Firmware version	V2.0.0
<b>Product function</b>	
• I&M data	Yes; I&M0 to I&M3
<b>Engineering with</b>	
• STEP 7 TIA Portal can be configured/integrated as of version	V12 / V12
• STEP 7 can be configured/integrated as of version	V5.5 SP3 / -
• PROFIBUS as of GSD version/GSD revision	V1.0 / V5.1
• PROFINET as of GSD version/GSD revision	V2.3 / -
<b>Operating mode</b>	
• MSI	Yes
<b>Power</b>	
Power available from the backplane bus	1 W
<b>Power losses</b>	
Power loss, typ.	4.9 W
<b>Digital inputs</b>	
Number of digital inputs	16
m/p-reading	p-reading
Input characteristic curve in accordance with IEC 61131, type 1	Yes

Input voltage	
• Type of input voltage	AC
• Rated value (AC)	230 V
• for signal "0"	0V AC to 40V AC
• for signal "1"	79 to 264 V AC
Input current	
• for signal "1", typ.	11 mA; At 230 V AC and 5.5 mA at 120 V AC
Input delay (for rated value of input voltage)	
for standard inputs	
— Parameterizable	No
— at "0" to "1", max.	25 ms
— at "1" to "0", max.	25 ms
for interrupt inputs	
— Parameterizable	No
Cable length	
• shielded, max.	1 000 m
• Unshielded, max.	600 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
— Permissible quiescent current (2-wire sensor), max.	2 mA
Isochronous mode	
Isochronous operation (application synchronized up to terminal)	No
Interrupts/diagnostics/status information	
Alarms	
• Diagnostic alarm	No
• Hardware interrupt	No
Diagnostic messages	
• Monitoring the supply voltage	No
• Wire break	No
• Short circuit	No
• Fuse blown	No
Diagnostics indication LED	
• RUN LED	Yes; Green LED
• ERROR LED	Yes; Red LED
• Monitoring of the supply voltage (PWR-LED)	No
• Channel status display	Yes; Green LED
• for channel diagnostics	No
• for module diagnostics	Yes; Red LED

## Galvanic isolation

### Electrical isolation channels

- |  |     |
|--|-----|
| • between the channels                       | No  |
| • between the channels, in groups of         | 4   |
| • between the channels and the backplane bus | Yes |

## Permissible potential difference

between different circuits	250 V AC between the channels and the backplane bus; 500 V AC between the channels
----------------------------	--

## Isolation

Isolation checked with	2500 V DC
------------------------	-----------

## Decentralized operation

Prioritized startup	Yes
---------------------	-----

## Dimensions

Width	35 mm
Height	147 mm
Depth	129 mm

## Weights

Weight, approx.	300 g
-----------------	-------

<b>last modified:</b>	12.03.2015
-----------------------	------------