

## ETST665

**Article Number:** 904-00020

**Electrical Tape, Thickness 7.0 mil, PVC, Green, 10 Rolls/pkg**



Download spec sheet

### Base Data

**Local Order Number** ETST665

**Type** ETST66

**Color** Green (GN)

- Features and Benefits**
- PVC Tape is ideal for general purpose electrical applications.
  - Heavy duty tape is comfortable and has exceptional surface and adhesive characteristics.
  - Fast, easy and economical way to color coding, cable splicing, terminating and wire insulating.

**Product Description** Electrical tapes are heavy duty vinyl and ideal for general purpose applications. Tape provides a fast, easy and economical way to cable splicing, terminating, wire insulating, and more. These comfortable high quality tapes have exceptional surface and adhesive characteristics. Tape is applied by overlapping each layer 50% and using tension. After the tape is adhered, the memory of the tape returns, tightening the seal and making the taped area even more waterproof.

**Short Description** Electrical Tape, Thickness 7.0 mil, PVC, Green, 10 Rolls/pkg

### Product Dimensions

**Length L (Imperial)** 66.0 ft

**Length L (Metric)** 20.12 m

**Width W (Imperial)** 0.75 "

**Width W (Metric)** 19.05 mm

**Thickness T (Imperial)** 7.0 mil

### Logistics and Packaging

**Quantity Per** reel

**Package Quantity** 10

**Package Quantity (Metric)** 10

**Carton Quantity** 200

### Material and Specifications

**Material** Flexible Polyvinyl Chloride (PVC)

**Material Shortcut** PVC

**US MILSPEC** MIL-1-7798-A

**Adhesion** 16 oz./inch

**Operating Temperature** +20°F to 176°F (-7°C to +80°C)

**UL Listed (US and Canada)** No

**UL Listed (US)** Yes

**UL Recognized (US and Canada)** No

UL Recognized (US) Yes

---

© HellemannTyton 2015