

XL50™

LED FLASHLIGHT

Introducing the New MAGLITE® XL50™ LED Flashlight.

- Easy to use
- Powerful Projecting LED Beam

Features a push-button tail cap switch with simple on-off function and **3 Selectable Modes**



- 1 Quick Click High Power**
...Turn off with a single click
- 2 Quick Clicks 25% Power**
...Turn off with a single click
- 3 Quick Clicks Emergency Safety Strobe**
...Turn off with a single click

Colors subject to availability:
Black, Red, Silver, Blue, and Gray

Blister Hang Pack



Presentation Box




The Maglite® XL50™ LED flashlight also features:

- Compact, Pocket Size design (Every Day Carry)
- "Spot-to-Flood" Adjustable LED Beam
- Durable, Rugged, Machined Aluminum Case
- Anodized for Corrosion Resistance and Durability
- Intelligent Energy Source Management - Continuously Monitors the Balance Between High Brightness and Efficient Power Usage Allowing for Prolonged Battery Life
- Powered by three (3) AAA alkaline batteries (included)
- Individually Serial Numbered

Specifications:

- Length: 4.8" (121.92 mm)
- Barrel Diameter: 1" (25.4 mm)
- Head Diameter: 1" (25.4 mm)
- Weight with Batteries: 3.68 oz. (104 g)



The package image is a mockup for illustrative purposes only. Package graphics are in development and subject to change.

* All specifications shown are approximate. For concept purposes only. May be different at shipment.

MAGLITE®
FLASHLIGHTS

©2010 MAG INSTRUMENT, INC. • 2001 South Hellman Ave., P.O. Box 50600, Ontario, California U.S.A. 91761, Tel. (909)947-1006 • www.maglite.com

The distinctive shapes, styles and overall appearances of all Mag Instrument® flashlights, and the circumferential inscriptions extending around the heads of all Mag Instrument® flashlights, are trademarks of Mag Instrument, Inc. The circumferential inscription on the head of every flashlight signifies that it is an original MAG® flashlight and part of the MAG® family of flashlights.

415-000-641 REV 10/10