Regulation EC No 1907/2006 Art.31

Creationdate: 18.03.20 Version: 3.0 Productname: AMBERKLENE ME20 Ref.Nr.: UDS000543 3 20200318 (EN) Replaces: UDS000543 20170629

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

AMBERKLENE ME20

Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Heavy duty

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd. Wylds Road **Castlefield Industrial Estate TA6 4DD Bridgwater Somerset United Kingdom**

Tel.: +44 1278 727200 Fax.: +44 1278 425644 E-mail: hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Aerosols, category 1

Extremely flammable aerosol.

Pressurised container: May burst if heated.

Classification is based on test data.

Health: Specific target organ toxicity - single exposure, category 3

May cause respiratory irritation.

Specific target organ toxicity - single exposure, category 3

May cause drowsiness or dizziness.

Classification based on calculation method.

Environment: Hazardous to the aquatic environment, chronic category 2

Toxic to aquatic life with long lasting effects.

Classification based on calculation method.



Regulation EC No 1907/2006 Art.31

Creationdate: 18.03.20 Version: 3.0 Productname: AMBERKLENE ME20 Ref.Nr.: UDS000543 3 20200318 (EN) Replaces: UDS000543 20170629

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier: Contains:

Hydrocarbons, C9, aromatics

Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics

Hazard pictogram(s):

Signal word: Danger

Hazard statement(s): H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated.

H335: May cause respiratory irritation. H336: May cause drowsiness or dizziness. H411: Toxic to aquatic life with long lasting effects.

Precautionary statement(s): P102: Keep out of reach of children.

P210: Keep away from heat, hot surfaces, sparks, open flames and other

ignition sources. No smoking.

P211: Do not spray on an open flame or other ignition source.

P251: Do not pierce or burn, even after use.

P261: Avoid breathing dust/fume/gas/mist/vapours/spray. P271: Use only outdoors or in a well-ventilated area.

P410/412: Protect from sunlight. Do not expose to temperatures exceeding

50°C/122°F.

P501-2: Dispose of contents/container to an authorised waste collection point.

Supplemental Hazard

Repeated exposure may cause skin dryness or cracking. information:

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS- nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons, C9, aromatics	01- 2119455851- 35	-	(918- 668-5)	10- 50	Flam. Liq. 3, STOT SE 3, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H226,H335,H336,H304,H411	Q
(2-methoxymethylethoxy)propanol	01- 2119450011- 60	34590- 94-8	252- 104-2	10- 30	-	-	A
Hydrocarbons, C9-C11, n-alkanes,	01-	-	(919-	10-	Flam. Lig. 3. Asp.	H226.H304.H336	B.Q



Regulation EC No 1907/2006 Art.31

18.03.20 Version: 3.0 Creationdate: Productname: AMBERKLENE ME20 Ref.Nr.: UDS000543 3 20200318 (EN) Replaces: UDS000543 20170629

isoalkanes, cyclics, < 2% aromatics	2119463258- 33		857-5)	30	Tox. 1, STOT SE 3		
carbon dioxide	-	124-38- 9	204- 696-9	1-5	Press. Gas	H280	A,G
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	01- 2119485926- 20	68512- 91-4	270- 990-9	1-5	Press. Gas, Flam. Gas 1	H280,H220	K,G
Explanation notes							
A : substance with Community workplace exposure limit							

B: substance with national established workplace exposure limit

G: exempted from the obligation to register in accordance with art.2(7) of REACH Regulation No 1907/2006

K: not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

Q: The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

If substance has got into eyes, immediately wash out with plenty of water Contact with eyes:

Seek medical attention if irritation persists

Contact with skin: Wash with water and soap.

Seek medical attention if irritation persists

Inhalation: Fresh air, keep warm and at rest.

Seek medical attention if ill effects occur

If swallowed do not induce vomiting because of risk of aspiration into the Ingestion:

lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation: Irritating to respiratory system.

Excessive inhalation of solvent vapours may give rise to nausea, headaches

and dizziness

Ingestion: After vomiting of swallowed product aspiration into lungs is likely. Solvents

may induce chemical pneumonia.

Symptoms: sore throat, abdominal pain, nausea, vomiting

Skin contact: May cause irritation.

Symptoms: redness and pain

Eye contact: Irritating to eyes.

Symptoms: redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice: If you feel unwell, seek medical advice (show the label where possible

If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media



Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater, Somerset, TA6 4DD
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Regulation EC No 1907/2006 Art.31

 Productname :
 AMBERKLENE ME20
 Creationdate :
 18.03.20 Version : 3.0

 Ref.Nr.:
 UDS000543_3_20200318 (EN)
 Replaces:
 UDS000543_20170629

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C Forms hazardous decomposition products CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources Ensure adequate ventilation Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition

Take precautionary measures against static discharges

Equipment should be earthed

Use explosion-proof electrical/ventilating/lighting/.../equipment.

Use only non-sparking tools.

Do not breathe aerosols or vapours.

Ensure adequate ventilation

Avoid contact with skin and eyes.

Wash thoroughly after use

Wear protective gloves/protective clothing/eye protection/face protection.



Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Regulation EC No 1907/2006 Art.31

Productname: AMBERKLENE ME20 Creationdate: 18.03.20 Version: 3.0 Ref.Nr.: Replaces: UDS000543_3_20200318 (EN) UDS000543 20170629

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Heavy duty

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits:

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:		_	
carbon dioxide	124-38-9	TWA	9000 mg/m3
		STEL	mg/m3
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
National established exposure limits, United Kingdom			·
carbon dioxide	124-38-9	TWA	5000 ppm
		STEL	15000 ppm
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
National established exposure limits, Ireland		·	·
carbon dioxide	124-38-9	TWA	5000 ppm
		STEL	15000 ppm
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
		STEL	-

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation
-	Keep away from heat and sources of ignition
	Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equiped with organic gas/vapor cartridge (type A)
hands and skin :	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
eyes:	Wear safety eyewear according to EN 166.



Regulation EC No 1907/2006 Art.31

Creationdate: 18.03.20 Version: 3.0 Productname: AMBERKLENE ME20 Ref.Nr.: UDS000543 3 20200318 (EN) Replaces: UDS000543 20170629

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Appearance : physical state : Liquid under pressure.

Colorless. colour:

odour: Characteristic odor. : Ha Not applicable.

Boiling point/range: 140 °C Flash point: 41 °C

Not available. Evaporation rate:

Explosion limits: upper limit: 7.0 % lower limit: 0.6 %

Vapour pressure : Not available.

Relative density: 0.87 g/cm3 (@ 20°C). Solubility in water : Insoluble in water

Auto-ignition: > 200 °C Not available. Viscosity:

9.2. Other information

VOC = volatile organic compounds

866 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products



6/10

Regulation EC No 1907/2006 Art.31

Productname: AMBERKLENE ME20 Creationdate: 18.03.20 Version: 3.0 Ref.Nr.: UDS000543_3_20200318 (EN) Replaces: UDS000543_20170629

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	based on available data the classification criteria are not met
serious eye damage/irritation:	based on available data the classification criteria are not met
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	May cause respiratory irritation.
	May cause drowsiness or dizziness.
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation :	Irritating to respiratory system. Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis Repeated exposure may cause skin dryness or cracking.
Eye contact :	Irritating to eyes.

Toxicological data:

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 10000 mg/kg
Hydrocarbons, C9, aromatics	-	LD50 oral rat	3492 mg/kg
		LC50 inhal.rat	> 6.393 mg/l
		LD50 derm.rabit	> 3160 mg/kg
Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	LD50 oral rat	>5000 mg/kg
		LC50 inhal.rat	4951 mg/m3
		LD50 derm.rabit	>5000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity



Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater, Somerset, TA6 4DD
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Regulation EC No 1907/2006 Art.31

Productname: AMBERKLENE ME20 Ref.Nr.:

UDS000543 3 20200318 (EN)

Creationdate: Replaces:

18.03.20 Version: 3.0 UDS000543 20170629

Hazardous to the aquatic environment, chronic category 2 Toxic to aquatic life with long lasting effects.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	IC50 algae	> 100 mg/l
		LC50 fish	> 10000 mg/l
		EC50 daphnia	> 100 mg/l

12.2. Persistence and degradability

No information available

12.3. Bioaccumulative potential

No information available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No information available GWP (global warming potential): 0

SECTION 13: Disposal considerations

13.1. Waste treatment methods

SECTION 14: Transport information

14.1. UN number

UN-number: 1950

14.2. UN proper shipping name

Proper shipping name: **AEROSOLS**

14.3. Transport hazard class(es)



8 / 10

CRC Industries UK Limited

Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater, Somerset, TA6 4DD
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Regulation EC No 1907/2006 Art.31

Productname:

AMBERKLENE ME20

Ref.Nr.: UDS000543 3 20200318 (EN)

Creationdate:

Replaces:

18.03.20 Version : 3.0 UDS000543 20170629

Class:

2.1

ADR/RID - Classification code:

5F

14.4. Packing group

Packing group:

Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally

hazardous:

No

IMDG - Marine pollutant:

No

IATA/ICAO - Environmentally

No

hazardous:

INO

14.6. Special precautions for user

ADR/RID - Tunnelcode:

(D)

IMDG - Ems:

F-D, S-U

IATA/ICAO - PAX:

203

IATA/ICAO - CAO

203

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.

Regulation (EC) No 1907/2006 (REACH)

Regulation (EC) No 1272/2008 (CLP)

Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: -:-

H220 : Extremely flammable gas.

H226: Flammable liquid and vapour.

H280: Contains gas under pressure; may explode if heated.

H304: May be fatal if swallowed and enters airways.

H335 : May cause respiratory irritation. H336 : May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

REVISIONS IN CHAPTRE: Classification according to Regulation (EC) No 1272/2008



9 / 10

CRC Industries UK Limited

Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Regulation EC No 1907/2006 Art.31

Productname: AMBERKLENE ME20 Creationdate: 18.03.20 Version: 3.0 Ref.Nr.: Replaces: UDS000543 20170629 UDS000543 3 20200318 (EN)

Labelling according to Regulation (EC) No 1272/2008

TWA = time weight average acronyms and synonyms:

STEL = short time exposure limit VOC = volatile organic compounds PBT = persistant bioaccumulative toxic vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks,no part of these documents may be reproduced by any process without written permission from CRC.

