


| | |
|-------------|-----------------|
| CUSTOMER | MCM |
| PRODUCT NO. | 24-120** series |




SIDE:A

SIDE:B

| | | | | | | |
|---------------|----------------|----------|----------|----------|----------|----------------|
| CUSTOMER P/N | 24-12050 | 24-12051 | 24-12052 | 24-12053 | 24-12054 | 24-12055 |
| L±T(MM) | 460±10 | 920±10 | 1830±20 | 3660±20 | 7620±40 | 15240±100 |
| Tie(MM) | 60MM | 80MM | 110MM | 130MM | 160MM | PE film 600MM |
| Winding ø(MM) | 100±15 | | 120±15 | | 140±15 | 170±15 |
| MCM Nylon bag | 200*270*0.06MM | | | | | 270*350*0.06MM |

NOTE:

(1).Cable Spec: SLV Series AUDIO/VIDEO Interconnect Cable[(10/0.12BC)*2C(WHITE/RED)+S(32/0.10BC)]
 Jacket Material:PVC OD:4.0mm
 Cable Colour: Cool Grey 11C
 Cable Printing:SLV Series AUDIO/VIDEO Interconnect Cable www.stellarlabs.com




- 24-12051 3FT Bar Code:8 82459 00865 9
- 24-12052 6FT Bar Code:8 82459 00866 6
- 24-12053 12FT Bar Code:8 82459 00867 3
- 24-12054 25FT Bar Code:8 82459 00868 0
- 24-12055 50FT Bar Code:8 82459 00869 7

(2).Connector A: 3.5mm Male Solder Type
 INSULATION:Black
 CONTACTS:Nickel Plated

(3).Connector B: 3.5mm Male Solder Type
 INSULATION:Black
 CONTACTS:Nickel Plated

| | | | |
|---------------|-------|---------------|--|
| <u>SIDE:A</u> | | <u>SIDE:B</u> | |
| ø3.5 PLUG | | ø3.5 PLUG | |
| 1 | WHITE | 1 | |
| 2 | RED | 2 | |
| 3 | F | 3 | |



Heat sealing

PACKING : (8)

(4).Over Mold: PVC-45P-Cool Grey 11C

(5).Parameter Settings: CT-8681FA

1. Conductive Resistance:1.0Ω
2. Insulative Resistance:5MΩ (Min.)
3. Hi-Pot:300V/AC、DC , 1.5mA/I , 50Hz , 0.03s

(6).100% OPEN, SHORT&MISWIRE TEST;

(7).ALL MATERIALS MUST BE IN LINE WITH RoHS.

(8).Packing:Nylon bag+label

PIN OUT: (5)

| | | |
|-----|-------------|------------|
| 0 | NEW | 2014/04/04 |
| REV | DESCRIPTION | DATE |

| | | | | | | | |
|---|----------|---|-----------|---------|----------|------------------|--|
| GENERAL TOLERANCES (UNLESS SPECIFIED) | | MCM Electronics www.mcmelectronics.com | | | | AUDIO CABLE | |
| LENGTH: X. ±1 .X ±0.2 .XX ±0.10 ANGLE: X° . ±1° .X° ±0° 30' | | | | | | DC3.5 Stereo M/M | |
| UNIT:mm | REV:0/A | | | NAME | | | |
| DRAWING | XIAODENG | 2014/04/04 | S. P. NO. | HT-5762 | DWG. NO. | | |
| CHECK | | | P. O. NO. | | | | |
| APPROVE | | | SIZE | | PAGE | 1/1 | |