

T9 Circline Plus

FC32/830
0001963

Product features



PRODUCT OVERVIEW

Product name	FC32/830
Technology	Fluorescent
Watt (Rated) (W)	32
Lamp shape	Ring
Type	T9 Circline Plus
Cap/Base	G10q
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940725
E-number Norway	3845363
Luminous flux (lm)	2100
Colour temperature (K)	3000
Light colour	Warm White
Colour Code	830
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Photobiological Risk Group	Not applicable
Wattage (W)	32
Product Voltage (V)	84
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	12000
Product EAN number	5410288019635

DATA TABLE

General data

Product name	FC32/830
Technology	Fluorescent
Watt (Rated) (W)	32
Lamp shape	Ring

T9 Circline Plus

FC32/830

0001963

Type	T9 Circline Plus
Cap/Base	G10q
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940725
E-number Norway	3845363

Optical data

Luminous flux (lm)	2100
Luminous flux (Rated) (lm)	2100
Ambient temperature for maximum luminous flux (°C)	25
Colour temperature (K)	3000
Light colour	Warm White
Colour Code	830
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Adjustable chromaticity	N
Photobiological Risk Group	Not applicable
Rated lumen maint. factor (%) at 4000 h 50Hz	78
Rated lumen maint. factor (%) at 6000 h 50Hz	77
Rated lumen maint. factor (%) at 8000 h 50Hz	76
Rated lumen maint. factor (%) at 12000 h 50Hz	74

Electrical data

Wattage (W)	32
Watt (Rated) - High frequency (W)	32
Current (A)	0.45
Product Voltage (V)	84
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Lamp Energy Label (class)	G
kWh per 1000 hours burning time	35

Lifetime data

Average life (Nominal) (h)	12000
Average life (Rated) (h)	12000
Rated survival factor (%) at 2000 h 50Hz	99
Rated survival factor (%) at 4000 h 50Hz	97
Rated survival factor (%) at 6000 h 50Hz	92
Rated survival factor (%) at 8000 h 50Hz	85

T9 Circline Plus

FC32/830
0001963

Rated survival factor (%) at 12000 h 50Hz	50
---	----

Physical data

Nominal Product Height (mm)	29
Nominal Product Diameter (mm)	299
Max. Length base to base (mm) - A	299
Length base to pin Min-Max (mm) - B	299
Max. Lamp Diameter (mm) - D	29
Weight (kg)	0.186


Packaging

Single packaging type	Carton
Product EAN number	5410288019635
Packaging single length / height (cm)	30.5
Packaging single width (cm)	30.5
Packaging single depth (cm)	3.1
DUN14 (outer)	15410288019632
Units per outer package	12
Packaging outer length / height (cm)	44.4
Packaging outer width (cm)	32.1
Packaging outer depth (cm)	32.4


Safety data

Lamp mercury content (mg)	3.5
Breakage cleaning instructions	Applicable
Special purpose lamp	No
Suitable for household illumination	Yes

PHOTOMETRY



TECHNICAL DRAWINGS



T9 Circline Plus


FC32/830

0001963



SYLVANIA

0001963



32
kWh/1000h




2019/2015

T9 Circline Plus
FC32/830
0001963



0001963



32
kWh/1000h



2019/2015