

LED inspection lamp with additional UV test light

With angled head, length 150 mm

ATORN[®]

Application

for illuminating and finding scratches, dirt or leaks

Version

- with two LEDs – can be switched with two separate switches.
- 1. switching: CREE LED with three stages of true-colour, warm white light at 25, 50 and 100%
- 2. switching: UV LED (black light 395 nm)
- bendable lamp head, strong magnet in the lamp base
- Protection class IP 54



Delivery

Battery included

Art. No.	56801 120
Length	150 mm
Luminous flux	300 lm
Lighting range	66 m
Material	Aluminium
Colour	Dark grey
Type of rechargeable battery/battery	Alkali
Number of rechargeable batteries/batteries	3
Rechargeable battery/battery designation	1.5 V Mignon AA

EAN-Code

4050293634648