

## Carbide sabre saw blades S555 CHM Endurance for heavy metal

Tooth pitch: 3 mm, blade length: 100 mm, 1 pieces

**BOSCH**

### Application:

Suitable for cutting high-strength steel and the toughest materials.

### Version:

- Carbide technology, even tooth spacing
- Teeth welded to highly elastic steel body using hard metal technology
- Wide body (25 mm) and high blade thickness (1.25 mm) allow precise cutting
- Specially designed for maximum durability with high-strength steels

### Advantage:

- For effortless cutting and an ultimate blade service life



<b>Art. no.</b>	<b>71135 630</b>
<b>Model</b>	S 555 CHM
<b>Manufacturer Article Number</b>	2608653179
<b>Cutting material</b>	Carbide
<b>Saw blade design</b>	Tungsten carbide-tipped (strip)
<b>Length</b>	100 mm
<b>Teeth spacing</b>	3 mm
<b>Cut</b>	Straight cut
<b>Applications</b>	Sheet metals (3-15 mm), Closed profiles, Solid profiles (Ø 10-100 mm), Medium-strength to strength sheet metals (2-10 mm), Steel tubes
<b>Included in delivery</b>	1 piece

### EAN-Code

3165140876605