

PHILIPS

Lighting



HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 250 L33-A2-TS 230V 50Hz

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

General Information	
Application Code	L33-A2-TS
Design	HD2-151
Lamp Type	SON/MH
Number Of Lamps	1 piece/unit

Operating and Electrical	
Input Voltage	230 V
Input Frequency	50 Hz
Power Factor 100% Load (Nom)	0.85
Mains Voltage Performance (AC)	-8%+6%
Mains Voltage Safety (AC)	-10%+10%
Input Current With PF Correction	1.4 A
Input Current Without PF Correction	3 A
Power Factor Without PF Compensation (Nom)	0.4
Power Losses (Nom)	25.4 W

Wiring	
Wire Striplength	6.0 mm

Ballast Contact Wire Cross Section	2.5 mm ²
Connector Type	Screw

System characteristics	
Capacitor	32µF/250V
Rated Ballast-Lamp Power	250 W
Recommended Ignitor	for SON lamps ignitor SND 58 (913700185166) or series digital SUD40 (913700193591)

Temperature	
T-Storage (Max)	130 °C
T-Storage (Min)	-30 °C
T-Winding (Max)	130 °C
Delta-T Normal Conditions	75 °C

Approval and Application	
Active Temperature Protection	Yes
Approval Marks	CE marking ENEC certificate

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Product Data

Full product code	871869674108500
Order product name	BSN 250 L33-A2-TS 230V 50Hz
EAN/UPC - Product	8718696741085
Order code	913700753126
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	6
Material Nr. (12NC)	913700753126
Net Weight (Piece)	2.800 kg

Dimensional drawing

Product	A1	A2	B1	C1	D1
BSN 250 L33-A2-TS 230V 50Hz	151 mm	132 mm	81 mm	66 mm	6.2 mm

BSN 250 L33-A2-TS 230V 50Hz

