


TECHNICAL DATASHEET

Update : 26/02/2019

INTERNAL CARBIDE BORING BAR 95° SCLCR/L - 06



Characteristics

Ref.	EAN	Diameter mm	Head length mm	Type of assembly	Type of tool tip attachment	Min reaming diameter mm
855321	3660338107535	8	125	Right	E08 SCLCR 06	11
855322	3660338107542	10	125	Right	E10 SCLCR 06	13
855323	3660338107559	12	150	Right	E12 SCLCR 06	16
855324	3660338107566	8	125	Left	E08 SCLCL 06	11
855325	3660338107573	10	125	Left	E10 SCLCL 06	13
855326	3660338107580	12	150	Left	E12 SCLCL 06	16