Thermal Solutions

BOARD LEVEL POWER SEMICONDUCTOR HEAT SINKS

634 SERIES

Slim Profile Unidirectional Fin Vertical Mount Heat Sink

TO-220 and TO-218


TO-220

		Standard P/N		Height Above Footprint PC Board Dimensions		Weight	
		Plain Pin	Without Pin	in. (mm)	in. (mm)	lbs. (grams)	
		634-10ABEP	634-10AB	1.000 (25.4)	0.640 (16.26) x 0.640 (16.26)	0.016 (7.48	
	1 74	634-15ABEP	634-15AB	1.500 (38.1)	0.640 (16.26) x 0.640 (16.26)	0.025 (11.21)	
		634-20ABEP	634-20AB	2.000 (50.8)	0.640 (16.26) x 0.640 (16.26)	0.033 (14.95)	

Material: Aluminum, Black Anodized.

These slim profile unidirectional fin heat sinks offer users two assembly alternatives for vertically mounting TO-220 and TO-218 components. Models are available with or without wave-

solderable pins on 0.40 in. (10.2) centers, making them ideal for a variety of applications where quick assembly is needed and space is at a premium.





637 SERIES High-Efficiency Heat Sinks For Vertical Board Mounting

	Height Above		Thermal Performance at Typical Load				
Standard P/N	PC Board "A" in. (mm)	Maximum Footprint in. (mm)	Natural Convection	Forced Convection	Weight Ibs. (grams)		
637-10ABEP	1.000 (25.4)	1.375 (34.9) x 0.500 (12.7)	76°C@6W	5.8° C/W @ 200 LFM	0.023 (10.43)		
637-15ABEP	1.500 (38.1)	1.375 (34.9) x 0.500 (12.7)	65°C@6w	5.5° C/W @ 200 LFM	0.035 (15.88)		
637-20ABEP	2.000 (50.8)	1.375 (34.9) x 0.500 (12.7)	55°C @ 6W	4.7°C/W @ 200 LFM	0.050 (22.68		
637-25ABEP	2.500 (63.5)	1.375 (34.9) x 0.500 (12.7)	48°C @ 6W	4.2°C/W @ 200 LFM	0.062 (28.12)		

Material: Aluminum, Black Anodized

board space occupied must be minimized. Refer to the Accessory products section for thermal interface materials, thermal compounds, and other accessories products.







BOARD LEVEL POWER SEMICONDUCTOR HEAT SINKS


No.

667 SERIES Labor-Saving SpeedClip[™] Heat Sinks for Vertical Board Mounting

Standa Standoff Pin	ard P/N Plain Pin	Height Above PC Board "A" in. (mm)	Maximum Footprint in. (mm)	Thermal Perfor Natural Convection	rmance at Typical Load Forced Convection	Weight Ibs (grams)
667-10ABESP	667-10ABPP	1.000 (25.4)	1.375 (34.9) x 0.500 (12.7)	76°C @ 6W	5.8°C/W @ 200 LFM	0.0240 (11.0)
667-15ABESP	667-15ABPP	1.500 (38.1)	1.375 (34.9) x 0.500 (12.7)	66°C @ 6W	5.5°C/W @ 200 LFM	0.0340 (15.6)
667-20ABESP	667-20ABPP	2.000 (50.8)	1.375 (34.9) x 0.500 (12.7)	58°C @ 6W	4.7°C/W @ 200 LFM	0.0460 (21.0)
667-25ABESP	667-25ABPP	2.500 (63.5)	1.375 (34.9) x 0.500 (12.7)	48°C @ 6W	4.2°C/W @ 200 LFM	0.0580 (26.2)

Wave-solderable pins. Material: Aluminum, Black Anodized

Excellent performance, choice of wave-solderable plain pins (PP-Type) or wave-solderable hex-shaped standoff pins (SP-Type), and reduced assembly cost. Note: Order 330 SC or 285 SC SpeedClip™ separately.





626 & 627 SERIES High-Efficiency Heat Sinks for Vertical Board Mounting

626 AND 627 SERIES


TO-218, TO-220


TO-220

9	Standard P/N	Standard P/N	Height Above PC Board "A" in. (mm)	Maximum Footprint in. (mm)	Thermal Performance at Typical Load Natural Forced Convection Convection		
	626-10ABEP	627-10ABP	1.000 (25.4)	1.375 (34.9) x .500 (12.7)	76°C @ 6W	5.8°C/W @ 200 LFM	
	626-15ABEP	627-15ABP	1.500 (38.1)	1.375 (34.9) x .500 (12.7)	65°C @ 6W	5.5°C/W @ 200 LFM	
	626-20ABEP	627-20ABP	2.000 (50.8)	1.375 (34.9) x .500 (12.7)	55°C @ 6W	4.7°C/W @ 200 LFM	
	626-25ABEP	627-25ABP	2.500 (63-5)	1.375 (34.9) x .500 (12.7)	48°C @ 6W	4.2°C/M @ 200 LFM	


Wave-solderable pins. Material: Aluminum, Black Anodized

MECHANICAL DIMENSIONS









Series	Type Device	Hole Diameter "B"	Hole Height "C"	Webb Width "D"	Notch Width "E"	Extrusion Profile
625	TO-218	.144 (3.7)	.850 (21.6)	.660 (16.8)	.540 (13.7)	8420
627	TO-220	. 128 (3.3)	.720 (18.3)	.625 (15.9)	.437 (11.1)	5183

Dimensions: in. (mm)

ME WAKEFIELD Thermal Solutions

TO-220

BOARD LEVEL POWER SEMICONDUCTOR HEAT SINKS




647 SERIES

High-Performance Heat Sinks for Vertical Board Mounting

	Height Above		Thermal Performance at Typical Load			
Standard P/N	PC Board "A" in. (mm)	Maximum Footprint in. (mm)	Natural Convection	Forced Convection	Weight Ibs. (grams)	
647-10ABEP	1.000 (25.4)	1.650 (41.9) x 1.000 (25.4)	42°C @ 6W	3.8° C/W @ 200 LFM	0.055 (24.95)	
647-15ABEP	1.500 (38.1)	1.650 (41.9) x 1.000 (25.4)	37°C @ 6W	3.5° C/W @ 200 LFM	0.075 (34.02)	
647-175ABEP	1.750 (44.5)	1.650 (41.9) x 1.000 (25.4)	34°C @ 6W	3.3° C/W @ 200 LFM	0.090 (40.82)	
647-20ABEP	2.000 (50.8)	1.650 (41.9) x 1.000 (25.4)	31°C @ 6W	3.1°C/W @ 200 LFM	0.104 (47.17)	
647-25ABEP	2.500 (63.5)	1.650 (̀41.9)́ x 1.000 (̀25.4)́	25°C @ 6W	2.8°C/W @ 200 LFM	0.125 (56.70)	

Material: Aluminum, Black Anodized

Wave-solderable pins on 1 in. centers for vertical mounting of larger devices on printed circuit boards. Maximum semiconductor package width: 0.625 (15.9). Refer to the Accessory Products section for thermal interface materials, 126 Series silicone-free thermal compounds, and other accessories products.



Dimensions: in. (mm)


657 SERIES

High-Performance Heat Sinks for Vertical Board Mounting

TO-220, TO-247, TO-218

	Height Above	Maximum	Thermal Perform	ance at Typical Load	
Standard P/N	PC Board "A" in. (mm)	Footprint in. (mm)	Natural Convection	Forced Convection	Weight Ibs (grams)
657-10ABEP	1.000 (25.4)	1.650 (41.9) x 1.000 (25.4)	41°C @ 6W	3.7°C/W @ 200 LFM	0.0515 (23.36)
657-15ABEP	1.500 (38.1)	1.650 (41.9) x 1.000 (25.4)	38°C @ 6W	3.3°C/W @ 200 LFM	0.0760 (34.60)
657-20ABEP	2.000 (50.8)	1.650 (41.9) x 1.000 (25.4)	32°C @ 6W	2.9°C/W @ 200 LFM	0.1030 (47.00)
657-25ABEP	2.500 (63.5)	1.650 (41.9) x 1.000 (25.4)	25°C @ 6W	2.7°C/W @ 200 LFM	0.1250 (57.00)


Wave-solderable pins. Material: Aluminum. Black Anodized





POWER DAMENTICS (NATE)


BOARD LEVEL POWER SEMICONDUCTOR HEAT SINKS




Dimensions: in. (mm)

High-Performance Heat Sinks with SpeedClips™ for Vertical Board Mounting 657 SERIES TO-220, TO-247, TO-218 Height Above Maximum Thermal Performance at Typical Load Standard PC Board "A' Footprint Natural Forced in. (mm) P/N in. (mm) Convection Convection 1.650 (41.9) x 1.000 (25.4) 41°C @ 6W 3.7°C/W @ 200 LFM 657-10ABEPSC 1.000 (25.4) 657-15ABEPSC 1.500 (38.1) 1.650 (41.9) x 1.000 (25.4) 38°C @ 6W 3.3°C/W @ 200 LFM 657-20ABEPSC 2.000 (50.8) 1.650 (41.9) x 1.000 (25.4) 32°C @ 6W 2.9°C/W @ 200 LFM 2.7°C/W @ 200 LFM 657-25ABEPSC 2.500 (63.5) 1.650 (41.9) x 1.000 (25.4) 25°C @ 6W

Wave-solderable pins. Material: Aluminum, Black Anodized



High-Performance, High-Power Heat Sinks for Vertical Board Mounting **677 SERIES** TO-218, TO-220, TO-247 15-LEAD Multiwatt **Height Above** Maximum Thermal Performance at Typical Load PC Board "A Footprint Standard Natural Forced in. (mm) P/N in. (mm) Convection Convection 1.000 (25.4) 1.650 (41.9) x 1.000 (25.4) 3.1°C/W @ 200 LFM 677-10ABEP 52°C @ 6W 677-15ABEP 1.500 (38.1) 1.650 (41.9) x 1.000 (25.4) 46°C @ 6W 2.8°C/W @ 200 LFM 2.5°C/W @ 200 LFM 677-20ABEP 2.000 (50.8) 1.650 (41.9) x 1.000 (25.4) 40°C @ 6W 677-25ABEP 2.500 (63.5) 35°C @ 6W 2.2°C/W @ 200 LFM 1.650 (41.9) x 1.000 (25.4) Wave-solderable pins. Material: Aluminum, Black Anodized





BOARD LEVEL POWER SEMICONDUCTOR HEAT SINKS




ТО-3, ТО-66, ТО-220

		Height Above		Thermal Perforn	nance at Typical Load	Semiconductor	
1	Standard P/N	PC Board in. (mm)	Outline Dimensions in. (mm)	Natural Convection	Forced Convection	Mounting Hole Pattern	Weight Ibs. (grams)
8) - E	690-3B	1.310 (33.3)	1.860 (47.2)-sq	44°C @ 7.5W	2.0° C/W @ 400 LFM	(1) TO-3	0.0700 (31.75)
	690-66B	1.310 (33.3)	1.860 (47.2)-sq	44°C @ 7.5W	2.0°C/W @ 400 LFM	(1) TO-66	0.0700 (31.75)
	690-220B	1.310 (33.3)	1.860 (47.2)-sq	44°C @ 7.5W	2.0° C/W @ 400 LFM	(2) TO-220	0.0700 (31.75)

Material: Aluminum, Black Anodized

These low-cost heat sinks provide the most power dissipation at the lowest unit cost and are available in three standard types to mount and cool one TO-3 or TO-66 metal power semiconductor type or two plastic package TO-220 power semiconductor types. For higher power

semiconductors, the 690 Series can dissipate up to 20 watts while maintaining a mounting surface temperature rise above ambient air temperature of no more than 91°C.





680 SERIES

Maximum Efficiency Omnidirectional Heat Sinks


ТО-3, ТО-220

Standard P/N	Height Above PC Board "A" in. (mm)	Horizontal Mounting Footprint Dimensions in. (mm)	Thermal Perform Natural Convection	nance at Typical Load Forced Convection	Semiconductor Mounting Hole Pattern	Weight Ibs. (grams)
680-5A	0.500 (12.7)	1.810 (46.0)-sq	70°C @ 7.5W	3.0° C/W @ 400 LFM	(1) TO-3	0.0700 (31.75)
680-75A	0.750 (19.1)	1.810 (46.0)-sq	58°C @ 7.5W	2.4°C/W @ 400 LFM	(1) TO-3	0.0900 (40.82)
680-10A	1.000 (25.4)	1.810 (46.0)-sq	52°C @ 7.5W	2.0°C/W @ 400 LFM	(1) TO-3	0.0980 (44.45)
680-125A	1.250 (31.8)	1.810 (46.0)-sq	45°C @ 7.5W	1.5°C/W @ 400 LFM	(1) TO-3	0.1100 (49.90)
680-5220	0.500 (12.7)	1.810 (46.0)-sq	70°C @ 7.5W	3.0° C/W @ 400 LFM	(2) TO-220	0.0700 (31.75)
680-75220	0.750 (19.1)	1.810 (46.0)-sq	58°C @ 7.5W	2.4°C/W @ 400 LFM	(2) TO-220	0.0900 (40.82)
680-10220	1.000 (25.4)	1.810 (46.0)-sq	52°C @ 7.5W	2.0° C/W @ 400 LFM	(2) TO-220	0.0980 (44.45)
680-125220	1.250 (31.8)	1.810 (46.0)-sq	45°C @ 7.5W	1.5°C/W @ 400 LFM	(2) TO-220	0.1100 (49.90)

Material: Aluminum, Black Anodized

Achieve optimum natural convection cooling per unit volume occupied above the printed circuit board for TO-3 (one semiconductor package per heat sink) or for two TO-220 style cases, when this low-cost heat sink is used. Any mounting attitude will provide free circulation of air in

natural convection applications. These 680 Series heat sinks can also be specified without any semiconductor mounting hole pattern by specifying suffix "K" (Example: 680-5K).





DO-4/DO-5 Diodes

TO-3

BOARD LEVEL POWER SEMICONDUCTOR HEAT SINKS




Low-Height Heat Sinks 601 & 603 SERIES

Footprint Mounting Thermal Performance at Typical Load Standard Dimensions Hole Dia. Natural Weight Height Forced P/N in. (mm) in. (mm) Convection Convection in. (mm) lbs. (grams) 601E 2.000 (50.8) x 1.250 (31.8) 0.562 (14.3) 0.200 (5.1) 52°C @ 5.0W 4.5° C/W @ 175 LFM 0.0500 (22.68) 601F 2.000 (50.8) x 1.250 (31.8) 0.270 (6.9) 52°C@5.0W 4.5° C/W @ 175 LFM 0.0500 (22.68) 0.562 (14.3) 601K 2.000 (50.8) x 1.250 (31.8) 0.562 (14.3) None 52°C @ 5.0W 4.5° C/W @ 175 LFM 0.0500 (22.68) 603K 2.000 (50.8) x 2.000 (50.8) 0.562 (14.3) None 41°C @ 5.0W 4.0° C/W @ 175 LFM 0.0810 (36.74)

Material: Aluminum Alloy, Black Anodized

Use these low-height heat sinks on printed circuit board applications for TO-66 power semiconductors and DO-4 and DO-5 diodes, where close board-to-board spacing and efficient heat dissipation are required. The 601 and 603 Series may also be attached to enclosure panels or brackets using isolation hardware where necessary.



4	<u>e in</u>	
1	- A	

	Outline		Mounting	Thermal Perfo	rmance at Typical Load	
Standard	Dimensions	Height	Hole	Natural	Forced	Weight
P/N	in. (mm)	in. (mm)	Pattern	Convection	Convection	lbs. (grams)
641A	4.125 (104.8) x 3.000 (76.2)	1.000 (25.4)	(1) TO-3	36°C @ 15W	0.9° C/W @ 250 LFM	0.2900 (131.54)
641K	4.125 (104.8) x 3.000 (76.2)	1.000 (25.4)	None	36°C @ 15W	0.9°C/W @ 250 LFM	0.2900 (131.54)

Maximum Performance Natural Convection Heat Sink for all Metal-Case Semiconductors

Available with a standard TO-3 mounting hole pattern predrilled for cost-effective mounting in limited-height applications, the 641 Series provides maximum performance in natural convection with an optimized heat sink surface area. The 641K type with an open channel area of

641 SERIES

1.300 in. (33.0) and no predrilled mounting holes can be adapted to meet mounting requirements for most metal case power semiconductor types. Material: Aluminum Alloy, Black Anodized

